


| SYMBOL | DIMENSIONS | | |
|---|---|---|---|
| | MIN. | NOM. | MAX. |
| A | - | - | 1.2 |
| A1 | 0.25 | - | - |
| D | 11 BSC | | |
| E | 9 BSC | | |
| Øb | 0.4 | 0.45 | 0.5 |
| eE | 0.8 BSC | | |
| eD | 0.8 BSC | | |
| SD | 0.4 BSC | | |
| SE | 0.4 BSC | | |

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensioning and tolerancing methods per ASME Y14.5M-1994.