


| SYMBOL | DIMENSIONS | | |
|---|---|---|---|
| | MIN | NOM | MAX |
| A | - | - | 0.8 |
| A1 | 0 | - | 0.05 |
| D | 7 BSC | | |
| E | 7 BSC | | |
| b | 0.18 | 0.25 | 0.3 |
| D2 | 4.4 BSC | | |
| E2 | 4.4 BSC | | |
| e | 0.5 BSC | | |
| L | 0.45 | 0.5 | 0.55 |

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensioning and tolerancing conforms to ASME Y14.5-1994.