



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.8
A1	0	-	0.05
D	7 BSC		
E	7 BSC		
b	0.18	0.25	0.3
D2	4.65 BSC		
E2	4.65 BSC		
e	0.5 BSC		
L	0.45	0.5	0.55

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensioning and tolerancing conforms to ASME Y14.5-1994.