

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.8
A1	0	-	0.05
D	9 BSC		
E	9 BSC		
b	0.2	0.25	0.3
D2	7.2 BSC		
E2	7.2 BSC		
e	0.5 BSC		
L	0.35	0.4	0.45

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensioning and tolerancing conforms to ASME Y14.5M-1994.