

Bottom view



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.55
A1	0.175	-	-
D	1.706 BSC		
E	1.472 BSC		
Øb	0.231	0.261	0.291
eE	0.4 BSC		
eD	0.4 BSC		
SD	0.2 BSC		
SE	0 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]