



| SYMBOL | DIMENSIONS | | |
|---|---|---|---|
| | MIN | NOM | MAX |
| A | - | - | 0.534 |
| A1 | 0.164 | - | 0.224 |
| D | 2.69 BSC | | |
| E | 2.31 BSC | | |
| Øb | 0.24 | 0.27 | 0.3 |
| eD | 0.4 BSC | | |
| eE | 0.4 BSC | | |
| SD/SE | 0.2 / 0 BSC | | |

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensions and tolerances methods per ASME Y14.5-2009.