





| SYMBOL | DIMENSIONS | | |
|---|---|---|---|
| | MIN | NOM | MAX |
| A | - | - | 0.6 |
| A1 | 0.16 | - | - |
| D | 3.019 BSC | | |
| E | 2.509 BSC | | |
| Øb | 0.23 | 0.27 | 0.32 |
| eD | 0.4 BSC | | |
| eE | 0.4 BSC | | |
| SD | 0.055 BSC | | |
| SE | 0.2 BSC | | |
| f1 | 0.255 BSC | | |
| f2 | 0.255 BSC | | |

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]