



Bottom view



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.69
A1	0.21	0.24	0.27
A2	0.07 BSC		
A3	0.025 BSC		
D	4.2 BSC		
E	4.2 BSC		
Øb	0.285	0.315	0.345
eD	0.5 BSC		
eE	0.5 BSC		
SD / SE	0.25 BSC		

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensioning and tolerances methods per ASME Y14.5-2009.