






Bottom view



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.327
A1	0.08	-	-
D	2.6238 BSC		
E	3.216 BSC		
Øb	0.22	0.23	0.24
eD	0.4 BSC		
eE	0.4 BSC		
SD	0.2 BSC		
SE	0 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]