

SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	0.387	0.427	0.467
A1	0.122	-	0.182
D	3.676 BSC		
E	3.19 BSC		
Øb	0.188	0.218	0.248
eD	0.303 BSC		
eE	0.35 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]