



Bottom view



All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]

SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	1
A1	0.15	-	-
D	10 BSC		
E	10 BSC		
Øb	0.21	0.26	0.31
eD	0.4 BSC		
eE	0.4 BSC		