CoolMOS® Power Transistor

Features

- Lowest figure-of-merit $R_{ON}xQ_g$
- Ultra low gate charge
- Extreme dv/dt rated
- High peak current capability
- Qualified according to JEDEC[1] for target applications
- Pb-free lead plating; RoHS compliant

Product Summary

V_{DS} @ $T_{j,max}$	650	V
$R_{DS(on),max}$	0.199	Ω
$Q_{g,typ}$	32	nC

PG-TO262



CoolMOS CP is specially designed for:

- Hard switching topologies, for Server and Telecom



Type	Package	Ordering Code	Marking
IPI60R199CP	PG-TO262	SP000103248	6R199P

Maximum ratings, at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	T_C=25 °C	16	A
		T_C=100 °C	10	
Pulsed drain current[2]	$I_{D,pulse}$	T_C=25 °C	51	
Avalanche energy, single pulse	E_{AS}	I_D=6.6 A, V_{DD}=50 V	436	mJ
Avalanche energy, repetitive t_{AR}[2),3)]	E_{AR}	I_D=6.6 A, V_{DD}=50 V	0.66	
Avalanche current, repetitive t_{AR}[2),3)]	I_{AR}		6.6	A
MOSFET dv/dt ruggedness	dv/dt	V_{DS}=0...480 V	50	V/ns
Gate source voltage	V_{GS}	static	±20	V
		AC (f>1 Hz)	±30	
Power dissipation	P_{tot}	T_C=25 °C	139	W
Operating and storage temperature	T_j, T_{stg}		-55 ... 150	°C

Maximum ratings, at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous diode forward current	I_S	T_C=25 °C	9.9	A
Diode pulse current[2]	$I_{S,pulse}$		51	
Reverse diode dv/dt[4]	dv/dt		15	V/ns

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal characteristics						
Thermal resistance, junction - case	R_{thJC}		-	-	0.9	K/W
Thermal resistance, junction - ambient	R_{thJA}	leaded	-	-	62	
Soldering temperature, wavesoldering only allowed at leads	T_{sold}	1.6 mm (0.063 in.) from case for 10 s	-	-	260	°C

Electrical characteristics, at T_j=25 °C, unless otherwise specified

Static characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0 V, I_D=250 µA	600	-	-	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=0.66 mA	2.5	3	3.5	
Zero gate voltage drain current	I_{DSS}	V_{DS}=600 V, V_{GS}=0 V, T_j=25 °C	-	-	1	µA
		V_{DS}=600 V, V_{GS}=0 V, T_j=150 °C	-	10	-	
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	-	-	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=10 V, I_D=9.9 A, T_j=25 °C	-	0.18	0.199	Ω
		V_{GS}=10 V, I_D=9.9 A, T_j=150 °C	-	0.49	-	
Gate resistance	R_G	f=1 MHz, open drain	-	2	-	Ω

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Dynamic characteristics						
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=100 V, f=1 MHz	-	1520	-	pF
Output capacitance	C_{oss}		-	72	-	
Effective output capacitance, energy related[5)]	$C_{o(er)}$	V_{GS}=0 V, V_{DS}=0 V to 480 V	-	69	-	
Effective output capacitance, time related[6)]	$C_{o(tr)}$		-	180	-	
Turn-on delay time	$t_{d(on)}$	V_{DD}=400 V, V_{GS}=10 V, I_D=9.9 A, R_G=3.3 Ω	-	10	-	ns
Rise time	t_r		-	5	-	
Turn-off delay time	$t_{d(off)}$		-	50	-	
Fall time	t_f		-	5	-	
Gate Charge Characteristics						
Gate to source charge	Q_{gs}	V_{DD}=400 V, I_D=9.9 A, V_{GS}=0 to 10 V	-	8	-	nC
Gate to drain charge	Q_{gd}		-	11	-	
Gate charge total	Q_g		-	32	43	
Gate plateau voltage	$V_{plateau}$		-	5.0	-	V
Reverse Diode						
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=9.9 A, T_j=25 °C	-	0.9	1.2	V
Reverse recovery time	t_{rr}	V_R=400 V, I_F=I_S, di_F/dt=100 A/µs	-	340	-	ns
Reverse recovery charge	Q_{rr}		-	5.5	-	µC
Peak reverse recovery current	I_{rrm}		-	33	-	A

[1)] J-STD20 and JESD22

[2)] Pulse width t_p limited by $T_{j,max}$

[3)] Repetitive avalanche causes additional power losses that can be calculated as P_{AV}=E_{AR}*f.

[4)] I_{SD}≤I_D, di/dt≤200A/µs, V_{DClink}=400V, V_{peak}<$V_{(BR)DSS}$, T_j<T_{jmax}, identical low side and high side switch.

[5)] $C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[6)] $C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

1 Power dissipation

$P_{tot}=f(T_C)$



2 Safe operating area

$I_D=f(V_{DS})$; $T_C=25$ °C; $D=0$

parameter: t_p



3 Max. transient thermal impedance

$Z_{thJC}=f(t_P)$

parameter: $D=t_p/T$



4 Typ. output characteristics

$I_D=f(V_{DS})$; $T_j=25$ °C

parameter: V_{GS}



5 Typ. output characteristics

I_D=f(V_{DS}); T_j=150 °C

parameter: V_{GS}



6 Typ. drain-source on-state resistance

$R_{DS(on)}$=f(I_D); T_j=150 °C

parameter: V_{GS}



7 Drain-source on-state resistance

$R_{DS(on)}$=f(T_j); I_D=9.9 A; V_{GS}=10 V



8 Typ. transfer characteristics

I_D=f(V_{GS}); |V_{DS}|>2|I_D|$R_{DS(on)max}$

parameter: T_j



9 Typ. gate charge

V_{GS}=f(Q_{gate}); I_D=9.9 A pulsed

parameter: V_{DD}



10 Forward characteristics of reverse diode

I_F=f(V_{SD})

parameter: T_j



11 Avalanche energy

E_{AS}=f(T_j); I_D=6.6 A; V_{DD}=50 V



12 Drain-source breakdown voltage

$V_{BR(DSS)}$=f(T_j); I_D=0.25 mA



13 Typ. capacitances

C=f(V_{DS}); V_{GS}=0 V; f=1 MHz



14 Typ. Coss stored energy

E_{oss}=f(V_{DS})



Definition of diode switching characteristics



6 Package Outlines



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.300	4.572	0.169	0.180
A1	2.150	2.718	0.085	0.107
b	0.650	0.864	0.026	0.034
b1	0.950	1.093	0.037	0.043
b2	0.950	1.400	0.037	0.055
b3	0.650	1.118	0.026	0.044
c	0.330	0.600	0.013	0.024
c1	1.170	1.400	0.046	0.055
D	8.509	9.450	0.335	0.372
D1	6.900	-	0.272	-
E	9.700	10.363	0.382	0.408
E1	6.500	8.600	0.256	0.339
e	2.540		0.100	
e1	5.080		0.200	
N	3		3	
L	13.000	14.000	0.512	0.551
L1	-	4.800	-	0.189
L2	-	1.727	-	0.068

REFERENCE
Z8B00003325

SCALE 0 2.5 0 2.5 5mm

EUROPEAN PROJECTION

ISSUE DATE
05-05-2006

REVISION
03

Figure 1 Outline PG-TO 262, dimensions in mm/inches

Revision History

IPI60R199CP

Revision: 2017-08-11, Rev. 2.3

Previous Revision		
Revision	Date	Subjects (major changes since last revision)
2.3	2017-08-11	Revised package drawing on Page 9

We Listen to Your Comments
Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:
erratum@infineon.com

Published by
Infineon Technologies AG
81726 München, Germany

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics (“Beschaffenheitsgarantie”) .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.
In addition, any information given in this document is subject to customer’s compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer’s products and any use of the product of Infineon Technologies in customer’s applications.
The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer’s technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information
For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (**www.infineon.com**).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.