


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1
A1	0.25	-	-
D	11 BSC		
E	9 BSC		
$\varnothing b$	0.4	0.45	0.5
eE	0.8 BSC		
eD	0.8 BSC		
SD	0.4 BSC		
SE	0.4 BSC		

All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []
 Dimensioning and tolerancing methods per ASME Y14.5M-1994.