



All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.79
A1	0.179	0.199	0.219
D	5 BSC		
E	8.2 BSC		
Øb	0.241	0.271	0.301
eD	0.4 BSC		
eE	0.4 BSC		
SD	0.159		
SE	0.042		