



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.53
A1	0.14	0.17	0.2
D	3.72	3.76	3.8
E	4.39	4.43	4.47
$\text{Ø}b$	0.18	0.23	0.28
e	0.35 BSC		
f1	0.21 BSC		
f2	0.4 BSC		
f3	0.23 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

All dimensions and tolerances conform to ASME Y14.5M-1994.