



All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensions and tolerances methods per ASME Y14.5-2009.

SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.43
A1	0.06	0.09	0.12
A2	0.3 BSC		
D	4.51 BSC		
E	3.91 BSC		
$\varnothing b$	0.17	0.2	0.23
eD	0.4 BSC		
eE	0.4 BSC		
SD/SE	0.2		