

Product brief

2EDN MOSFET EiceDRIVER[™] family Rugged, cool and fast, dual-channel low-side 4 A/5 A driver ICs

EiceDRIVER[™] 2EDN family overview

Dual-channel driver ICs are the crucial link between control ICs and powerful MOSFET and GaN switching devices driver ICs enable high system level efficiencies, excellent power density and consistent system robustness.

EiceDRIVER™ 2EDN family: Fast, precise, strong and compatible

- > Highly efficient SMPS enabled by 5 ns short slew rates and 10 ns propagation delay precision for fast MOSFET and GaN switching
- > Numerous deployment options due to two 4 A/5 A channels. 1 ns channel-to-channel accuracy to use two channels in parallel
- > Industry standard packages and pinout ease system design upgrades

EiceDRIVER™ 2EDN family: The new reference in ruggedness and low power dissipation

- > 4 V and 8 V UVLO (Under Voltage Lock Out) options for instant MOSFET protection under abnormal conditions
- > -10 V robustness of control and enable inputs provides crucial safety margin when driving pulse transformers or driving MOSFETs in TO-220 and TO-247 packages
- > 5 A reverse output current robustness eliminates the need for Schottky switching diodes and reduces bill-of-material
- > Cool driver ICs from true rail-to-rail low impedance output stages

Product features

- > 5 A souce/sink current
- > 5 ns rise/fall times
- > <10 ns propagation delay precision</p>
- > True rail-to-rail low impedance output stages
- > 4 V and 8 V UVLO options
 > 19 ns propagation delay for both control and enable inputs
- > -10 V robustness of control and enable inputs
- > 5 A reverse output current robustness
- > 2 independent channels
- > Excellent 1 ns channel-to-channel accuracy
- Industry standard pinout and packages

- Product benefits
- > Fast Miller plateau transition
- Precise timing
- Low power dissipation in Driver IC
- Fast and reliable MOSFET turn-off, independent of control IC
- > Increased GND-bounce robustness
- Saves switching diodes
- > Option to increase drive current by truly concurrent switching of 2 channels
- Straight forward design upgrades

Applications

- > Server
- > Telecom
- > DC-DC converters
- > Bricks
- > Power tools
- > Industrial SMPS
- > Motor control
- > Solar

System benefits


- > High power efficiency
- in hard switching PFC with SiC Diode
 in half-bridges and synchronous rectifications
- > Cooler driver IC operation
- > Higher MOSFET drive capability
- Instant MOSFET protection under abnormal operation
- > Crucial safety margin to drive pulse transformer
- Increases power density
 BOM savings
- > One IC covering many applications
- Short time to market



2EDN MOSFET EiceDRIVER™ family

Rugged, cool and fast, 2-channel low-side 5 A driver ICs


Application overview 800 W 130 kHz switched mode power supply



Product portfolio

Package		UVLO	Inputs	Product name	Orderable part number
	DSO 8-pin	4 V	Direct	2EDN7524F	2EDN7524FXTMA1
			Inverted	2EDN7523F	2EDN7523FXTMA1
			Direct	2EDN7424F	2EDN7424FXTMA1
		8 V	Direct	2EDN8524F	2EDN8524FXTMA1
			Inverted	2EDN8523F	2EDN8523FXTMA1
	TSSOP 8-pin	4 V	Direct	2EDN7524R	2EDN7524RXUMA1
			Inverted	2EDN7523R	2EDN7523RXUMA1
			Direct	2EDN7424R	2EDN7424RXUMA1
		8 V	Direct	2EDN8524R	2EDN8524RXUMA1
			Inverted	2EDN8523R	2EDN8523RXUMA1
	WSON 8-pin	4 V	Direct	2EDN7524G	2EDN7524GXTMA1
			Inverted	2EDN7523G	2EDN7523GXTMA1

Industry standard pinout configuration





For more information visit: www.infineon.com/2edn

Published by Infineon Technologies Austria AG 9500 Villach, Austria

© 2019 Infineon Technologies AG. All Rights Reserved.

Please note!

THIS DOCUMENT IS FOR INFORMATION PURPOSES ONLY AND ANY INFORMATION GIVEN HEREIN SHALL IN NO EVENT BE REGARDED AS A WARRANTY, GUARANTEE OR DESCRIPTION OF ANY FUNCTIONALITY, CONDITIONS AND/OR QUALITY OF OUR PRODUCTS OR ANY SUITABILITY FOR A PARTICULAR PURPOSE. WITH REGARD TO THE TECHNICAL SPECIFICATIONS OF OUR PRODUCTS, WE KINDLY ASK YOU TO REFER TO THE RELEVANT PRODUCT DATA SHEETS PROVIDED BY US. OUR CUSTOMERS AND THEIR TECHNICAL DEPARTMENTS ARE REQUIRED TO EVALUATE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED APPLICATION.

WE RESERVE THE RIGHT TO CHANGE THIS DOCUMENT AND/OR THE INFORMATION GIVEN HEREIN AT ANY TIME.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.