


SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.52
A1	0.122	0.152	0.182
D	1.351 BSC		
E	1.376 BSC		
n	9		
$\varnothing b$	0.188	0.218	0.248
eD	0.4 BSC		
eE	0.4 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []