


All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

| SYMBOL | DIMENSIONS |       |       |
|--------|------------|-------|-------|
|        | MIN.       | NOM.  | MAX.  |
| A      | -          | -     | 0.794 |
| A1     | 0.182      | 0.202 | 0.222 |
| A2     | 0.547      | 0.569 | 0.591 |
| D      | 4.226 BSC  |       |       |
| E      | 4.924 BSC  |       |       |
| Øb     | 0.238      | 0.268 | 0.298 |
| eD     | 0.385      | 0.4   | 0.415 |
| eE     | 0.385      | 0.4   | 0.415 |
| SD     | 0.121 BSC  |       |       |
| SE     | 0.147 BSC  |       |       |