



Bottom view



All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.489
A1	0.169	-	-
D	2.39 BSC		
E	1.59 BSC		
$\varnothing b$	0.235	0.265	0.295
eD	0.4 BSC		
eE	0.4 BSC		
SD/SE	0.2 BSC		