Cool MOS™ Power Transistor

V_{DS}	600	V
$R_{DS(on)}$	0.38	Ω
I_D	11	A

Feature

- New revolutionary high voltage technology
- Ultra low gate charge
- Periodic avalanche rated
- Extreme d*v*/d*t* rated
- Ultra low effective capacitances
- Improved transconductance
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC[0)] for target applications

PG-TO262 PG-TO220



Type	Package	Ordering Code	Marking
SPP11N60S5	PG-TO220	Q67040-S4198	11N60S5
SPI11N60S5	PG-TO262	Q67040-S4338	11N60S5



Maximum Ratings

Parameter	Symbol	Value	Unit
Continuous drain current T_C = 25 °C T_C = 100 °C	I_D	 11 7	A
Pulsed drain current, t_p limited by T_{jmax}	$I_{D\ puls}$	22	
Avalanche energy, single pulse I_D = 5.5 A, V_{DD} = 50 V	E_{AS}	340	mJ
Avalanche energy, repetitive t_{AR} limited by T_{jmax}[1)] I_D = 11 A, V_{DD} = 50 V	E_{AR}	0.6	
Avalanche current, repetitive t_{AR} limited by T_{jmax}	I_{AR}	11	A
Gate source voltage	V_{GS}	±20	V
Gate source voltage AC (f >1Hz)	V_{GS}	±30	
Power dissipation, T_C = 25°C	P_{tot}	125	W
Operating and storage temperature	T_j, T_{stg}	-55... +150	°C

Maximum Ratings

Parameter	Symbol	Value	Unit
Drain Source voltage slope V_{DS} = 480 V, I_D = 11 A, T_j = 125 °C	dv/dt	20	V/ns

Thermal Characteristics

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	-	-	1	K/W
Thermal resistance, junction - ambient, leaded	R_{thJA}	-	-	62	
SMD version, device on PCB: @ min. footprint @ 6 cm^2 cooling area [2)]	R_{thJA}	 - -	 - 35	 62 -	
Soldering temperature, wavesoldering 1.6 mm (0.063 in.) from case for 10s	T_{sold}	-	-	260	°C

Electrical Characteristics, at Tj=25°C unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0V, I_D=0.25mA	600	-	-	V
Drain-Source avalanche breakdown voltage	$V_{(BR)DS}$	V_{GS}=0V, I_D=11A	-	700	-	
Gate threshold voltage	$V_{GS(th)}$	I_D=500µA, V_{GS}=V_{DS}	3.5	4.5	5.5	
Zero gate voltage drain current	I_{DSS}	V_{DS}=600V, V_{GS}=0V, T_j=25°C, T_j=150°C	 - -	 - -	 25 250	µA
Gate-source leakage current	I_{GSS}	V_{GS}=20V, V_{DS}=0V	-	-	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=10V, I_D=7A, T_j=25°C T_j=150°C	 - -	 0.34 0.92	 0.38 -	Ω
Gate input resistance	R_G	f=1MHz, open Drain	-	29	-	

Electrical Characteristics , at T_j = 25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Characteristics						
Transconductance	g_{fs}	$V_{DS}\geq 2*I_D*R_{DS(on)max}$, I_D=7A	-	6	-	S
Input capacitance	C_{iss}	V_{GS}=0V, V_{DS}=25V, f=1MHz	-	1460	-	pF
Output capacitance	C_{oss}		-	610	-	
Reverse transfer capacitance	C_{rss}		-	21	-	
Effective output capacitance,[3] energy related	$C_{o(er)}$	V_{GS}=0V, V_{DS}=0V to 480V	-	45	-	pF
Effective output capacitance,[4] time related	$C_{o(tr)}$		-	85	-	
Turn-on delay time	$t_{d(on)}$	V_{DD}=350V, V_{GS}=0/10V, I_D=11A, R_G=6.8Ω	-	130	-	ns
Rise time	t_r		-	35	-	
Turn-off delay time	$t_{d(off)}$		-	150	225	
Fall time	t_f		-	20	30	

Gate Charge Characteristics

Gate to source charge	Q_{gs}	V_{DD}=350V, I_D=11A	-	10.5	-	nC
Gate to drain charge	Q_{gd}		-	24	-	
Gate charge total	Q_g	V_{DD}=350V, I_D=11A, V_{GS}=0 to 10V	-	41.5	54	
Gate plateau voltage	$V_{(plateau)}$	V_{DD}=350V, I_D=11A	-	8	-	V

[0] J-STD20 and JESD22

[1] Repetitve avalanche causes additional power losses that can be calculated as $P_{AV}=E_{AR}*f$.

[2] Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical without blown air.

[3] $C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[4] $C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

Electrical Characteristics, at T_j = 25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Inverse diode continuous forward current	I_S	T_C=25°C	-	-	11	A
Inverse diode direct current, pulsed	I_{SM}		-	-	22	
Inverse diode forward voltage	V_{SD}	V_{GS}=0V, I_F=I_S	-	1	1.2	V
Reverse recovery time	t_{rr}	V_R=350V, I_F=I_S ,	-	650	1105	ns
Reverse recovery charge	Q_{rr}	di_F/dt=100A/µs	-	7.9	-	µC

Typical Transient Thermal Characteristics

Symbol	Value	Unit	Symbol	Value	Unit
	typ.			typ.	
Thermal resistance			Thermal capacitance		
R_{th1}	0.015	K/W	C_{th1}	0.0001878	Ws/K
R_{th2}	0.03		C_{th2}	0.0007106	
R_{th3}	0.056		C_{th3}	0.000988	
R_{th4}	0.197		C_{th4}	0.002791	
R_{th5}	0.216		C_{th5}	0.007285	
R_{th6}	0.083		C_{th6}	0.063	



1 Power dissipation

$P_{tot} = f(T_C)$



2 Safe operating area

$I_D = f(V_{DS})$

parameter : $D = 0$, T_C=25°C



3 Transient thermal impedance

$Z_{thJC} = f(t_p)$

parameter: $D = t_p/T$



4 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=25°C

parameter: t_p = 10 µs, V_{GS}



5 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=150°C

parameter: t_p = 10 µs, V_{GS}



6 Typ. drain-source on resistance

$R_{DS(on)}=f(I_D)$

parameter: T_j=150°C, V_{GS}



7 Drain-source on-state resistance

$R_{DS(on)} = f(T_j)$

parameter : I_D = 7 A, V_{GS} = 10 V



8 Typ. transfer characteristics

$I_D = f(V_{GS})$; $V_{DS} \geq 2 \times I_D \times R_{DS(on)max}$

parameter: t_p = 10 µs



9 Typ. gate charge

$V_{GS} = f\ (Q_{Gate})$

parameter: I_D = 11 A pulsed



10 Forward characteristics of body diode

$I_F = f\ (V_{SD})$

parameter: T_j , tp = 10 µs



11 Avalanche SOA

$I_{AR} = f\ (t_{AR})$

par.: $T_j \leq 150$ °C



12 Avalanche energy

$E_{AS} = f\ (T_j)$

par.: I_D = 5.5 A, V_{DD} = 50 V



13 Drain-source breakdown voltage

$V_{(BR)DSS} = f(T_j)$



14 Avalanche power losses

$P_{AR} = f(f)$

parameter: E_{AR}=0.6mJ



15 Typ. capacitances

$C = f(V_{DS})$

parameter: V_{GS}=0V, f=1 MHz



16 Typ. C_{oss} stored energy

$E_{oss}=f(V_{DS})$



Definition of diodes switching characteristics



PG-TO220-3-1, PG-TO220-3-21



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.57	0.169	0.180
A1	1.17	1.40	0.046	0.055
A2	2.15	2.72	0.085	0.107
b	0.65	0.86	0.026	0.034
b1	0.95	1.40	0.037	0.055
b2	0.95	1.15	0.037	0.045
b3	0.65	1.15	0.026	0.045
c	0.33	0.60	0.013	0.024
D	14.81	15.95	0.583	0.628
D1	8.51	9.45	0.335	0.372
D2	12.19	13.10	0.480	0.516
E	9.70	10.36	0.382	0.408
E1	6.50	8.60	0.256	0.339
e	2.54		0.100	
e1	5.08		0.200	
N	3		3	
H1	5.90	6.90	0.232	0.272
L	13.00	14.00	0.512	0.551
L1	-	4.80	-	0.189
øP	3.60	3.89	0.142	0.153
Q	2.60	3.00	0.102	0.118

DOCUMENT NO.	Z8B00003318
SCALE	0 2.5 0 2.5 5mm
EUROPEAN PROJECTION	
ISSUE DATE	23-08-2007
REVISION	05

PG-TO262-3-1, PG-TO262-3-21 (I²-PAK)



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.300	4.572	0.169	0.180
A1	2.150	2.718	0.085	0.107
b	0.650	0.864	0.026	0.034
b1	0.635	1.400	0.025	0.055
c	0.330	0.600	0.013	0.024
c1	1.170	1.400	0.046	0.055
D	8.509	9.450	0.335	0.372
D1	6.900	-	0.272	-
E	9.700	10.363	0.382	0.408
E1	6.500	8.600	0.256	0.339
e	2.540		0.100	
e1	5.080		0.200	
N	3		3	
L	13.000	14.000	0.512	0.551
L1	-	4.800	-	0.189
L2	-	1.727	-	0.068

REFERENCE
JEDEC TO262

0
2.5
0 2.5
5mm

EUROPEAN PROJECTION

ISSUE DATE
05-05-2006

FILE
TO262_1

Published by
Infineon Technologies AG
81726 Munich, Germany

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information
For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.