



SIDC14D120E6

Fast switching diode chip in EMCON-Technology

FEATURES:

- 1200V EMCON technology 130 µm chip
- soft, fast switching
- low reverse recovery charge
- small temperature coefficient

This chip is used for:

EUPEC power modules and discrete devices



Applications:

SMPS, resonant applications, drives

Chip Type	V_R	I _F	Die Size	Package	Ordering Code
SIDC14D120E6	1200V	15A	3.8 x 3.8 mm ²	sawn on foil	Q67050-A4123- A001

MECHANICAL PARAMETER:

<u></u>				
3.8 x 3.8				
14.44 / 9.8	mm ²			
3.08 x 3.08	<u> </u>			
130	μm			
150	mm			
180	deg			
1018 pcs				
Photoimide				
3200 nm AlSiCu				
1400 nm Ni Ag –system suitable for epoxy and soft solder die bonding				
electrically conductive glue or solder				
AI, ≤500μm				
Ø 0.65mm ; max 1.2mm				
store in original container, in dry nitrogen, < 6 month at an ambient temperature of 23°C				
	14.44 / 9.8 3.08 x 3.08 130 150 180 1018 pcs Photoimide 3200 nm AlSiCu 1400 nm Ni Ag —system suitable for epoxy and soft solder die bon electrically conductive glue or solder Al, ≤500µm Ø 0.65mm; max 1.2mm store in original container, in dry nitroge			



SIDC14D120E6

Maximum Ratings

Parameter	Symbol	Condition	Value	Unit
Repetitive peak reverse voltage	V_{RRM}		1200	V
Continuous forward current limited by	I _F		15	
T _{jmax}				A
Single pulse forward current (depending on wire bond configuration)	I _{FSM}	t_P = 10 ms sinusoidal	tbd	
Maximum repetitive forward current			30	
limited by T _{jmax}	I _{FRM}		30	
Operating junction and storage temperature	$T_{\rm j}$, $T_{ m stg}$		-55+150	°C

Static Electrical Characteristics (tested on chip), T_j =25 °C, unless otherwise specified


Parameter	Symbol	Cond	Value			Unit		
raiailietei	Syllibol	Cona	itions	min.	nin. Typ. max.			
Reverse leakage current	I_{R}	V _R =1200V	<i>T_j</i> =25 °C			27	μΑ	
Cathode-Anode breakdown Voltage	V _{Br}	$I_R=1 mA$	<i>T_j</i> =25°C	1200			V	
Forward voltage drop	V _F	I _F =15A	<i>T_j</i> =25°C		1.9		V	

Dynamic Electrical Characteristics, at $T_i = 25$ °C, unless otherwise specified, tested at component

Parameter	Symbol	Conditions		Value			Unit
	Syllibol			min.	Тур.	max.	7 01111
Reverse recovery time	t _{rr1}	I _F =15A	$T_j = 25$ °C		tbd		
	t _{rr2}	di/dt=390A/ms $V_R=600V$	$T_j = 125$ °C				ns
Peak recovery current	I _{RRM1}	$I_F=15A$ $di/dt=390A/ms$ $V_R=600V$	$T_j = 25$ °C		10.9		Α
	I _{RRM2}		$T_j = 125$ °C		14.5		A
Reverse recovery charge	Q _{rr1}	$I_F=15A$ di/dt=390A/ms $V_R=600V$	<i>T_j</i> =25 °C		1.45		u.C
	_		T _j =125°C		3.23		μC
Peak rate of fall of reverse recovery current	di _{rr1} /dt	$I_F=15A$ di/dt=390A/ms $V_R=600V$	T _j =25°C		tbd		A/μs
	di _{rr2} /dt		T _j =125°C				
Softness	S1	$I_F=15A$	<i>T_j</i> =25 °C		tbd		1
	S2	di/dt=390A/ms $V_R=600V$	T _j =125°C				<u> </u>



SIDC14D120E6





Preliminary

SIDC14D120E6

FURTHER ELECTRICAL CHARACTERISTICS:

This chip data sheet refers to the device data sheet line infine on technologies / EUPEC today t

Description:

AQL 0,65 for visual inspection according to failure catalog

Electrostatic Discharge Sensitive Device according to MIL-STD 883

Test-Normen Villach/Prüffeld

Published by Infineon Technologies AG Bereich Kommunikation St.-Martin-Strasse 53 D-81541 München © Infineon Technologies AG 2000 All Rights Reserved.

Attention please!

The information herein is given to describe certain components and shall not be considered as warranted characteristics.

Terms of delivery and rights to technical change reserved.

We hereby disclaim any and all warranties, including but not limited to warranties of non-infringement, regarding circuits, descriptions and charts stated herein.

Infineon Technologies is an approved CECC manufacturer.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office in Germany or our Infineon Technologies Representatives world-wide (see address list).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and / or maintain and sustain and / or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.