

# Value Optimized Hall Effect Switch for Industrial and Consumer Applications High Precision Hall Effect Switch

### **About this document**

#### **Overview**

The TLV4906L is a high precision Hall Effect Switch with highly accurate switching thresholds for ambient operating temperatures up to 85°C.



#### **Features**

- 2.7 V to 18 V supply voltage operation.
- Operation from unregulated power supply.
- High sensitivity and high stability of the magnetic switching points.
- High resistance to mechanical stress by active error compensation.
- Reverse battery protection (-18 V).
- Superior temperature stability.
- Low jitter (typically 1 μs).
- High ESD performance (± 4 kV HBM).
- Digital output signal (open-drain).
- Not suitable for automotive applications

#### **Target applications**

The TLV4906L is ideally suited for all industrial and consumer applications that require a high precision switching thresholds for position sensing. It can be used for example for: security systems, alignment control, push buttons, keyboards, key switches, machine tools, etc.

Product name	Product type	Ordering code	Package
TLV4906L	Hall Effect Switch	SP000604324	PG-SSO-3-2

### Value Optimized Hall Effect Switch for Industrial and Consumer ApplicationsHigh Precision Hall Effect Switch Table of contents



## **Table of contents**

	About this document
	Table of contents
1	Functional description
1.1	General
1.2	Pin configuration
1.3	Pin description
1.4	Block diagram
1.5	Operating modes and states
1.6	Functional block description
2	Specification
2.1	Application circuit
2.2	Absolute maximum ratings
2.3	Operating range
2.4	Electrical characteristics
3	Package information
3.1	TLV4906L Package outline
4	Revision history
	Disclaimer



1 Functional description

## 1 Functional description

#### 1.1 General

Precise magnetic switching thresholds and high temperature stability are achieved by active compensation circuits and chopper techniques on chip. Offset voltages generated by temperature-induced stress or overmolding are canceled so that high accuracy is achieved. The IC has an open collector output stage with 20 mA current sink capability. A wide operating voltage range from 2.7 V to 18 V with reverse polarity protection down to -18 V makes the TLV4906L suitable for a wide range of applications. A magnetic south pole with a field strength above Bop turns the output transistor on (output voltage low) and for a magnetic field below Brp the output transistor is switched off (output voltage high).

## 1.2 Pin configuration




Figure 1 Pin configuration and sensitive area (Top view, figure not to scale)

## 1.3 Pin description

### Table 1 Pin Definitions for the PG-SSO-3-2 package

Pin No.	Name	Function
1	$V_{S}$	Supply Voltage
2	GND	Ground
3	Q	Output



1 Functional description

## 1.4 Block diagram




Figure 2 TLV4906L Block Diagram

## 1.5 Operating modes and states

#### Field direction and definition

Positive magnetic fields correspond to the south pole of the magnet targeting the branded side of the package.




Figure 3 Definition of the magnetic field direction

## Value Optimized Hall Effect Switch for Industrial and Consumer ApplicationsHigh Precision Hall Effect Switch



1 Functional description




Figure 4 Output signal

## 1.6 Functional block description

The chopped Hall Effect Switch comprises a Hall probe, a bias generator, compensation circuits, an oscillator and an output transistor. The bias generator provides currents to the Hall probe and the active circuits. Compensation circuits stabilize response of the IC over temperature and reduce the impact of process variations. The Active Error Compensation rejects offsets in the signal path and reduces the impact of mechanical stress in the package caused by molding, soldering and thermal effects. The chopper technique together with the threshold generator and the comparator ensure high accurate magnetic switching points.

### Value Optimized Hall Effect Switch for Industrial and Consumer ApplicationsHigh Precision Hall Effect Switch 2 Specification



## **2** Specification

## 2.1 Application circuit




Figure 5 Application circuit

It is recommended to use a resistor of 200  $\Omega$  in the supply line for current limitation in the case of an overvoltage pulse. Two capacitors of 4.7 nF enhance the EMC performance. The pull-up of 1.2 k $\Omega$  limits the current through the output transistor.

## 2.2 Absolute maximum ratings

Stress above the maximum values listed in this section may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect the reliability of the device. Exceeding only one of these values may cause irreversible damage to the device.

Table 2 Absolute maximum ratings

Parameter	Symbol		Values			Note/Test
		Min.	Тур.	Max.		Condition
Maximum Ambient Temperature	$T_{A}$	-40	_	125	°C	
Maximum Junction Temperature	TJ	-40	_	150	°C	
Supply Voltage	$V_{S}$	-18	_	18	٧	
Supply current through protection device	Is	-50	_	50	mA	
Output Voltage	V <sub>OUT</sub>	-0.7	_	18	V	
Storage Temperature	$T_{S}$	-40	_	150	°C	
Magnetic flux density	В	-	_	unlimit ed	mT	
ESD Robustness HBM: 1.5 kΩ, 100 pF	V <sub>ESD,HBM</sub> <sup>(1)</sup>	-	-	4	kV	

#### (1) According to EIA/JESD22-A114-E

## Value Optimized Hall Effect Switch for Industrial and Consumer ApplicationsHigh Precision Hall Effect Switch 2 Specification



#### **Operating range** 2.3

The following operating conditions must not be exceeded in order to ensure correct operation of the TLV4906L. All parameters specified in the following sections refer to these operating conditions unless otherwise mentioned.

Table 3 **Operating range** 

Parameter	Symbol		Values			Note/Test
		Min.	Тур.	Max.		Condition
Supply Voltage	V <sub>S</sub>	2.7	_	18	V	
Output Voltage	$V_{Q}$	-0.7	_	18	V	
Output Current	$I_{\mathrm{Q}}$	0	_	20	mA	
Maximum Ambient Temperature	T <sub>A</sub>	-40	-	85	°C	

### Value Optimized Hall Effect Switch for Industrial and Consumer ApplicationsHigh Precision Hall Effect Switch 2 Specification



2.4 Electrical characteristics

Product characteristics include the spread of values guaranteed within the specified voltage and ambient temperature range. typical characteristics are the median of the production (at  $V_S = 12 \text{ V}$  and  $T_A = 25 ^{\circ}\text{C}$ ).

Table 4 Electrical characteristics

Parameter	Symbol		Values			Note or Test
		Min.	Тур.	Max.		Condition
Supply Current	Is	2	4	6	mA	V <sub>S</sub> = 2.7 V 18 V
Reverse Current	I <sub>SR</sub>	0	0.2	1	mA	V <sub>S</sub> = -18 V
Output Saturation Voltage	$V_{QSAT}$	-	0.3	0.6	V	I <sub>Q</sub> = 20 mA
Output leakage current	IQLEAK	-	0.05	10	μΑ	V <sub>Q</sub> = 18 V
Output fall time <sup>(1)</sup>	$t_{f}$	_	0.02	1	μs	$R_L = 1.2 \text{ k}\Omega, C_L =$
Output rise time(1)	t <sub>r</sub>	-	0.4	1	μs	50 pF
Chopper frequency	$f_{OSC}$	_	320	_	kHz	
Switching frequency	$f_{SW}$	0	_	15 <sup>(2)</sup>	kHz	
Delay time <sup>(3)</sup>	t <sub>d</sub>	-	13	_	μs	
Output jitter <sup>(4)</sup>	$t_{\mathrm{QJ}}$	-	1	-	μs <sub>RMS</sub>	Typical value for a 1 kHz square wave signal
Power-on Time <sup>(5)</sup>	$t_{PON}$	-	13	_	μs	V <sub>S</sub> > 2.7 V
Thermal Resistance junction to ambient <sup>(6)</sup>	R <sub>thJA</sub>	-	-	190	K/W	TLV4906L

- (1) See Figure 6
- (2) To operate the sensor at maximum switching frequency, the value of the magnetic signal amplitude must be 1.4 times higher than the static fields. This is due to the -3 dB corner frequency of the low pass filter in the signal path.
- (3) Systematic delay between magnetic threshold reached and output.
- (4) Jitter is the unpredictable deviation of the output switching delay.
- (5) Time from applying  $V_S > 2.7 \text{ V}$  to the sensor until the output state is valid.
- (6) Relationship between junction and ambient temperature:  $T_J = T_{amb} + R_{thja}$ .  $(V_S . I_S + V_{QS} . I_Q)$ .

## Value Optimized Hall Effect Switch for Industrial and Consumer **ApplicationsHigh Precision Hall Effect Switch**2 Specification






Figure 6 **Timing diagram** 

Table 5 Magnetic characteristics(1)

Parameter	Symbol		Values			Note/Test
		Min.	Тур.	Max.		Condition
Operate point	B <sub>OP</sub>	6.2	10.0	13.9	mT	
Release point	$B_{RP}$	4.7	8.5	12.3	mT	
Hysteresis	B <sub>HYS</sub>	0.7	1.5	3.0	mT	(2)
Temperature compensation of magnetic thresholds	TC	-	-350	_	ppm/°	
Repeatability of magnetic thresholds <sup>(3)</sup> B <sub>REP</sub> is equivalent to the noise constant.	$B_{REP}$	-	20	_	μT <sub>RMS</sub>	typical value for ΔB/Δt > 12 mT/ms

<sup>(1)</sup> (2) (3) Over all operating conditions.

At 25°C.



## 3 Package information

## 3.1 TLV4906L Package outline




Figure 7 Marking of the TLV4906L and distance of the chip to the upper side

## Value Optimized Hall Effect Switch for Industrial and Consumer ApplicationsHigh Precision Hall Effect Switch 3 Package information






Figure 8 PG-SSO-3-2 Package outline

## Value Optimized Hall Effect Switch for Industrial and Consumer ApplicationsHigh Precision Hall Effect Switch 4 Revision history



## 4 Revision history

Revision History				
Page Subjects (major changes since last revision)				
Revision Histo	ry: 2020-08, Rev. 1.2			
Previous Revis	ions: 1.1			
9 Edited figure 7 (optional: data matrix code)				

#### Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2020-08 Published by Infineon Technologies AG 81726 Munich, Germany

© 2020 Infineon Technologies AG All Rights Reserved.

Do you have a question about any aspect of this document?

 ${\bf Email: erratum@infineon.com}$ 

Document reference IFX-mok1599123596500

#### IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

#### WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.