

Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

Cypress Semiconductor Reliability Qualification Report

QTP# Q100820, 162110 Version *B

S27KL0641

**Qualification of: S27KL0641, 64M HyperRAM, 3.0 Volt-Only in VAA024
(8 x 6 x 1mm) 24 Ball, Fine Pitch Ball Grid Array Package (FBGA)**

FOR ANY QUESTIONS ON THIS REPORT, PLEASE CONTACT
reliability@cypress.com or via a CYLINK CRM CASE

Prepared By:

Eng Keat Ng
Reliability Engineer

Reviewed By:

Francis Classe
Reliability Manager

Approved By:

Don Darling
Reliability Director

I.A. Product and Package Information

Product Description: S27KL0641 Cypress Division: Memory Product Division
64M HyperRAM, 3.0 Volt-Only

Package:	VAA024	QTP:	Q100820	
Description:	(8 x 6 x 1mm) 24 Ball, Fine Pitch Ball Grid Array Package (FBGA)			Flammability: O2 Index:
Assembly:	Cypress Thailand	Molding Compound:	ShinEtsu KMC 3580LVA	UL-V0 >28
Electrical Test:	Cypress Thailand	Theta Ja / Psi Jt:	51 °C/W / 5 °C/W	
Substrate/Leadframe:	Laminate Substrate	Die Attachment:	Sumitomo CRM-1577DB	
Lead Finish:	96.5Sn3.0Ag0.5Cu Spheres	Bond Wire:	Copper	
Comments:				

Est. Field Temperature:	55 °C	Life Test Temperature:	125 °C
Est. DC Field Current:	20 mA	Life Test Dynamic Current:	35 mA
Est. Field Voltage:	3.0 V	Life Test Voltage:	3.7 V
Est. Field Power Dissipation:	60 mWatts	Est. Stress Power Dissipation:	129.5 mWatts
Est. Field Tj:	58.0 °C	Est. Stress Tj:	131.6 °C

Die:	11036A	Die Size:	2.02 x 2.91 mm
Process:	63nm	Fab:	PSC (ISSI)
Type:	HYPERRAM	Density:	64M

I.B. Product and Package Information

Product Description: S27KL0641

Cypress Division: Memory Product Division

64M HyperRAM, 3.0 Volt-Only

Package:	VAA024	QTP:	162110	
Description:	(8 x 6 x 1mm) 24 Ball, Fine Pitch Ball Grid Array Package (FBGA)			Flammability: O2 Index:
Assembly:	Cypress Thailand	Molding Compound:	ShinEtsu KMC 3580LVA	UL-V0 >28
Electrical Test:	Cypress Thailand	Theta Ja / Psi Jt:	51 °C/W / 5 °C/W	
Substrate/Leadframe:	Laminate Substrate	Die Attachment:	Sumitomo CRM-1577DB	
Lead Finish:	96.5Sn3.0Ag0.5Cu Spheres	Bond Wire:	Gold	
Comments:				

Est. Field Temperature:	55 °C	Life Test Temperature:	125 °C
Est. DC Field Current:	20 mA	Life Test Dynamic Current:	35 mA
Est. Field Voltage:	3.0 V	Life Test Voltage:	3.7 V
Est. Field Power Dissipation:	60 mWatts	Est. Stress Power Dissipation:	129.5 mWatts
Est. Field Tj:	58.0 °C	Est. Stress Tj:	131.6 °C

Die:	11036A	Die Size:	2.02 x 2.91 mm
Process:	63nm	Fab:	PSC (ISSI)
Type:	HYPERRAM	Density:	64M

II. Summary of Stress Test Results

Stress Test	Stress Condition	Package Type	Sample Size	Num. of Lots	Num. of Fails	Failure Rate %	Comments
Data From Qualification Q100820, 162110:							
ESD CDM	N/A	VAA024 ¹	15	1		Passed 1.0kV	
	N/A	VAA024 ²	15	1		Passed 1.0kV	
ESD HBM	(100pF, 1500 Ohms)	VAA024 ¹	108	1		Passed 2.0kV	
Preconditioning	(PC2/260°C, +0°C/-5°C)	VAA024 ¹	154	1		Passed Jedec L3	
	(PC2/260°C, +0°C/-5°C)	VAA024 ²	154	1		Passed Jedec L3	
Precon+Temp Cycle	(PC2/260°C, -40°C/150°C)	VAA024 ¹	75	1	0	0.00	1000 cycles
	(PC2/260°C, -40°C/150°C)	VAA024 ²	77	1	0	0.00	500 cycles
Precon+HAST	(PC2/260°C, Biased, 110°C/85% RH)	VAA024 ¹	77	1	0	0.00	264 hours
	(PC2/260°C, Biased, 110°C/85% RH)	VAA024 ²	77	1	0	0.00	96 hours

Generic Reference Data:

ELFR	(3.7V, 125°C)	³	3750	3	0	0.00	48 hours
HTOL (EL)	(3.7V, 125°C)	³	77	1	0	0.00	168 hours
HTOL (IL)	(3.7V, 125°C)	³	231	3	0	0.00	1000 hours
High Temp Bake	(150°C)	³	135	3	0	0.00	1000 hours
	(200°C)	FAE025 ⁴	231	3	0	0.00	500 hours
	(150°C)	FAE025 ⁴	230	3	0	0.00	1000 hours
ESD CDM	N/A	³	3	1	Passed 750V		
	N/A	FAE025 ⁴	45	3	Passed 1.0kV		
	N/A	VAA024 ⁵	15	1	Passed 1.0kV		
ESD HBM	(100pF, 1500 Ohms)	³	5	1	Passed 2.0kV		
	(100pF, 1500 Ohms)	VAA024 ⁵	14	1	Passed 2.0kV		
Latch Up	(+/- 100mA)	³	12	2	Passed		
	(+/- 140mA)	VAA024 ⁵	9	1	Passed		
Preconditioning	(PC2/260°C, +0°C/-5°C)	FAE025 ⁴	1001	7	Passed Jedec L3		
Precon+Temp Cycle	(PC2/260°C, -40°C/150°C)	FAE025 ⁴	231	3	0	0.00	1000 cycles
Precon+Temp Cycle (Ext.)	(PC2/260°C, -40°C/150°C)	FAE025 ⁴	216	3	0	0.00	2000 cycles
Precon+HAST	(PC2/260°C, Biased, 110°C/85% RH)	FAE025 ⁴	537	7	0	0.00	264 hours
Precon+HAST (Ext.)	(PC2/260°C, Biased, 110°C/85% RH)	FAE025 ⁴	494	7	0	0.00	528 hours
Precon+uHAST	(PC2/260°C, Unbiased, 130°C/85% RH)	FAE025 ⁴	231	3	0	0.00	96 hours
	(PC2/260°C, Unbiased, 130°C/85% RH)	FAE025 ⁴	231	3	0	0.00	192 hours

- Notes / Justification:
- 1) Results from Qual Q100820, S27KL0641, 63nm HYPERRAM in 24 Ball FBGA (8 x 6 x 1mm)
 - 2) Results from Qual 162110, S27KL0641, 63nm HYPERRAM in 24 Ball FBGA (8 x 6 x 1mm)
 - 3) Results from Qual ISSI HYPERRAM 11036A Supplier Data, S27KL0641 in 0 (0 x 0 x 0mm) - 11036A ISSI Supplier Data
 - 4) Results from Qual Q100747, S27KL0641 in 25 Ball FBGA (8 x 6 x 1.15mm) - Same Product in FAE025
 - 5) Results from Qual 160808, S27KL0641 in 24 Ball FBGA (8 x 6 x 1mm) - Same Product with Mask Set B in VAA024 package

Preconditioning Flows: PC2 (JEDEC L3): Bake 125°C, 24hr => Soak @ 30°C/60%RH, 192hr => 3x Reflow

Reliability Tests Performed per Specification Requirements

Stress	Condition	Specification Reference
ELFR	(3.7V, 125°C)	JESD22-A108 / AEC-Q100-008
ESD CDM	N/A	JS002 / AEC-Q100-011
ESD HBM	(100pF, 1500 Ohms)	JS001 / AEC-Q100-002
High Temp Bake	(150°C)	JESD22-A103
High Temp Bake	(200°C)	JESD22-A103
HTOL (EL)	(3.7V, 125°C)	JESD22-A108
HTOL (IL)	(3.7V, 125°C)	JESD22-A108
Latch Up	(+/- 100mA)	JESD78 / AEC Q100-004
Latch Up	(+/- 140mA)	JESD78 / AEC Q100-004
Precon+HAST	(PC2/260°C, Biased, 110°C/85% RH)	JESD22-A110
Precon+HAST (Ext.)	(PC2/260°C, Biased, 110°C/85% RH)	JESD22-A110
Precon+Temp Cycle	(PC2/260°C, -40°C/150°C)	JESD22-A104
Precon+Temp Cycle (Ext.)	(PC2/260°C, -40°C/150°C)	JESD22-A104
Precon+uHAST	(PC2/260°C, Unbiased, 130°C/85% RH)	JESD22-A118
Preconditioning	(PC2/260°C, +0°C/-5°C)	J-STD-020

III. Revision History

Document Number: 002-15850

Document Title: Q100820 & QTP#162110 : Qualification of S27KL0641 in VAA024 Package (Both Copper and Au Wire)

Rev.	Issue Date	ECN#	Originator	Description
**	8/4/2016	5391620	EKNG	Initial Release.
*A	12/28/2016	5567859	EKNG	Updated the Thermal Parameter
*B	5/2/2017	5723431	EKNG	Corrected the FAE025 reference data

Trademarks and Notice

The contents of this document are subject to change without notice. This document may contain information on a Cypress product under development by Cypress. Cypress reserves the right to change or discontinue work on any product without notice. The information in this document is provided as is without warranty or guarantee of any kind as to its accuracy, completeness, operability, fitness for particular purpose, merchantability, non-infringement of third-party rights, or any other warranty, express, implied, or statutory. Cypress assumes no liability for any damages of any kind arising out of the use of the information in this document.

Copyright © 2016-2017 Cypress Inc. All rights reserved.