

uIO-Stick v2

User guide

Z8F80464029

About this document

Scope and purpose

This user guide helps you to get started with the uIO-Stick v2. The uIO-Stick v2 acts as an interface between the PC and EvalBoards of the MOTIX™ MCU and LITIX™ Interior series of devices.

This user guide provides additional information about the layout, interfaces and the pinout of the uIO-Stick v2.

Intended audience

This document is for everyone who works with the uIO-Stick v2.

Important notice

“Evaluation Boards and Reference Boards” shall mean products embedded on a printed circuit board (PCB) for demonstration and/or evaluation purposes, which include, without limitation, demonstration, reference and evaluation boards, kits and design (collectively referred to as “Reference Board”).

Environmental conditions have been considered in the design of the Evaluation Boards and Reference Boards provided by Infineon Technologies. The design of the Evaluation Boards and Reference Boards has been tested by Infineon Technologies only as described in this document. The design is not qualified in terms of safety requirements, manufacturing and operation over the entire operating temperature range or lifetime.

The Evaluation Boards and Reference Boards provided by Infineon Technologies are subject to functional testing only under typical load conditions. Evaluation Boards and Reference Boards are not subject to the same procedures as regular products regarding returned material analysis (RMA), process change notification (PCN) and product discontinuation (PD).

Evaluation Boards and Reference Boards are not commercialized products, and are solely intended for evaluation and testing purposes. In particular, they shall not be used for reliability testing or production. The Evaluation Boards and Reference Boards may therefore not comply with CE or similar standards (including but not limited to the EMC Directive 2004/EC/108 and the EMC Act) and may not fulfill other requirements of the country in which they are operated by the customer. The customer shall ensure that all Evaluation Boards and Reference Boards will be handled in a way which is compliant with the relevant requirements and standards of the country in which they are operated.

The Evaluation Boards and Reference Boards as well as the information provided in this document are addressed only to qualified and skilled technical staff, for laboratory usage, and shall be used and managed according to the terms and conditions set forth in this document and in other related documentation supplied with the respective Evaluation Board or Reference Board.

It is the responsibility of the customer’s technical departments to evaluate the suitability of the Evaluation Boards and Reference Boards for the intended application, and to evaluate the completeness and correctness of the information provided in this document with respect to such application.

The customer is obliged to ensure that the use of the Evaluation Boards and Reference Boards does not cause any harm to persons or third party property.

The Evaluation Boards and Reference Boards and any information in this document is provided "as is" and Infineon Technologies disclaims any warranties, express or implied, including but not limited to warranties of non-infringement of third party rights and implied warranties of fitness for any purpose, or for merchantability.

Infineon Technologies shall not be responsible for any damages resulting from the use of the Evaluation Boards and Reference Boards and/or from any information provided in this document. The customer is obliged to defend, indemnify and hold Infineon Technologies harmless from and against any claims or damages arising out of or resulting from any use thereof.

Infineon Technologies reserves the right to modify this document and/or any information provided herein at any time without further notice.

Safety precautions

Note: Please note the following warnings regarding the hazards associated with development systems.

Table 1 Safety precautions

	Caution: The heat sink and device surfaces of the evaluation or reference board may become hot during testing. Hence, necessary precautions are required while handling the board. Failure to comply may cause injury.
	Caution: Only personnel familiar with the drive, power electronics and associated machinery should plan, install, commission and subsequently service the system. Failure to comply may result in personal injury and/or equipment damage.
	Caution: The evaluation or reference board contains parts and assemblies sensitive to electrostatic discharge (ESD). Electrostatic control precautions are required when installing, testing, servicing or repairing the assembly. Component damage may result if ESD control procedures are not followed. If you are not familiar with electrostatic control procedures, refer to the applicable ESD protection handbooks and guidelines.
	Caution: A drive that is incorrectly applied or installed can lead to component damage or reduction in product lifetime. Wiring or application errors such as under-sizing the motor, supplying an incorrect or inadequate DC supply, or excessive ambient temperatures may result in system malfunction.
	Caution: The evaluation or reference board is shipped with packing materials that need to be removed prior to installation. Failure to remove all packing materials that are unnecessary for system installation may result in overheating or abnormal operating conditions.

Table of contents

	About this document	1
	Important notice	2
	Safety precautions	3
	Table of contents	4
1	Overview	5
1.1	Description	5
1.2	Block diagram	5
2	Hardware connection	7
3	Comparison of uIO-Stick and uIO-Stick v2	8
4	Software	9
5	Acronyms	10
	Revision history	11
	Disclaimer	12

1 Overview

1.1 Description

The uIO-Stick v2 is an interface device for controlling EvalBoards of the MOTIX™ MCU and LITIX™ Interior devices during run time through a PC.

It offers a USB connection to the PC, and several different functionalities, for example SPI, CAN, and GPIOs.

The uIO-Stick v2 registers as an HID on the PC, so no driver installation is needed.



Figure 1 **uIO-Stick v2**

1.2 Block diagram

The uIO-Stick v2 contains an XMC4200 microcontroller which provides the necessary hardware interface and handles the protocols. LIN and CAN are implemented as true physical layers (using transceivers), while the digital lines (SPI, GPIOs) provide a 3.3 V or 5 V digital level (configurable by software - default 3.3V). In addition, a boost converter is implemented to generate a 12 V supply for the target device and the integrated LIN transceiver.




Figure 2 uIO-Stick v2 block diagram

2 Hardware connection

2 Hardware connection

The uIO-Stick v2 can be connected to the user PC via USB. For this purpose, it has a micro-USB socket. A micro-USB cable is not included in the packaging.

For connection to an embedded device, the uIO-Stick offers several different interfaces available on a 16-pin header. The connector cable, included in the packaging, fits to the 16-pin connector on the EvalBoards of the target devices. The following figure and table describe the pinout of the 16-pin connector.




Figure 3 uIO-Stick v2 pinout - image

Table 2 Pinout of uIO-Stick v2

Pin 15: SPI MOSI	Pin 13: SPI MISO	Pin 11: SPI CLK	Pin 9: SPI CS	Pin 7: Reset	Pin 5: LIN	Pin 3: CANL	Pin 1: CANH
Pin 16: Analog In	Pin 14: GPIO0	Pin 12: GPIO1, TXD	Pin 10: GPIO2, RXD	Pin 8: GPIO3	Pin 6: VS	Pin 4: 5 V (output)	Pin 2: GND

Additional remarks:

- Pin 2 - GND: the common ground connection to the target system
- Pin 5 - LIN: can be directly connected to a LIN network; is the LIN bus connection to the LIN transceiver implemented in the uIO-Stick v2
- Pin 6 - VS: can either be driven from the implemented boost converter on the uIO-Stick v2 (+12 V) or can be overridden by an external supply, for example the supply of the target device. This pin is also used to internally drive the LIN transceiver available on the uIO-Stick v2
- Pin 7 - Target Reset: intended to drive the reset input of the target device
- Pin 16 - Analog input for measuring up to 18 V

3 Comparison of uIO-Stick and uIO-Stick v2

The following table gives a comparison between uIO-Stick and uIO-Stick v2.

Table 3

Feature	uIO-Stick	uIO-Stick v2
Connection to PC	USB-A plug	Micro-USB socket
Connection to target device	16-pin socket	16-pin socket
Interface UART	Not available	Available
Interface RS232	Available	Not available
Interface CAN	Not available	Available
Interface LIN	Available	Available
Interface Reset line	Available	Available
Interface SPI	Available	Available
Interface GND	Available	Available
Interface 5 V	Available	Available
Interface 12 V	Available	Available
Interface 4 GPIOs	Available	Available
Interface Analog Input	Available	Available
Logical level 3.3 V and 5 V (SW selectable)	Available	Available

4 Software

For detailed information about software supported by uIO-Stick v2, please visit www.infineon.com/uio-v2.

5 Acronyms

The following acronyms and terms are used within this document.

Table 4 Acronyms

Acronyms	Name
CAN	Controller area network
CANH	Controller area network high
CANL	Controller area network low
CLK	Clock
CS	Chip select
GND	Ground
GPIO	General-purpose input/output
HID	Human interface device
LIN	Local interconnect network
MISO	Master in, slave out
MOSI	Master out, slave in
RXD	Receive data
SPI	Serial peripheral interface
SW	Software
TXD	Transmit data
USB	Universal serial bus
UART	Universal asynchronous receiver-transmitter
VS	Supply voltage

Revision history

Document version	Date of release	Description of changes
Rev. 1.05	2026-06-24	Minor text edits
Rev. 1.00	2023-05-30	Initial document release

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2026-06-24

Published by

**Infineon Technologies AG
81726 Munich, Germany**

© 2026 Infineon Technologies AG

All Rights Reserved.

**Do you have a question about any
aspect of this document?**

Email: erratum@infineon.com

**Document reference
IFX-hfd1673535012883**

Important notice

Products which may also include samples and may be comprised of hardware or software or both ("Product(s)") are sold or provided and delivered by Infineon Technologies AG and its affiliates ("Infineon") subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

For the avoidance of doubt, Infineon disclaims all warranties of non-infringement of third-party rights and implied warranties such as warranties of fitness for a specific use/purpose or merchantability. Infineon shall not be responsible for any information with respect to samples, the application or customer's specific use of any Product or for any examples or typical values given in this document.

If this document is marked as 'Preliminary', 'Target', 'Draft' or 'Proposal', Infineon reserves the right to change all information given in this document at any time without notice. Subject to the development and release of a Product for series supply by Infineon, the technical specifications of the Product are set forth in the relevant datasheet provided by Infineon without such marking.

The data contained in this document is exclusively intended for technically qualified and skilled customer representatives. It is the responsibility of the customer to evaluate the suitability of the Product for the intended application and the customer's specific use and to verify all relevant technical data contained in this document in the intended application and the customer's specific use. The customer is responsible for properly designing, programming, and testing the functionality and safety of the intended application, as well as complying with any legal requirements related to its use.

Unless otherwise explicitly approved by Infineon, Products may not be used in any application where a failure of the Products or any consequences of the use thereof can reasonably be expected to result in personal injury.

However, the foregoing shall not prevent the customer from using any Product in such fields of use that Infineon has explicitly designed and sold it for, provided that the overall responsibility for the application lies with the customer. Infineon expressly reserves the right to use its content for commercial text and data mining (TDM) according to applicable laws, e.g. Section 44b of the German Copyright Act (UrhG). If the Product includes security features:

Because no computing device can be absolutely secure, and despite security measures implemented in the Product, Infineon does not guarantee that the Product will be free from intrusion, data theft or loss, or other breaches ("Security Breaches"), and Infineon shall have no liability arising out of any Security Breaches.

If this document includes or references software:

The software is owned by Infineon under the intellectual property laws and treaties of the United States, Germany, and other countries worldwide. All rights reserved. Therefore, you may use the software only as provided in the software license agreement accompanying the software.

If no software license agreement applies, Infineon hereby grants you a personal, non-exclusive, non-transferable license (without the right to sublicense) under its intellectual property rights in the software (a) for software provided in source code form, to modify and reproduce the software solely for use with Infineon hardware products, only internally within your organization, and (b) to distribute the software in binary code form externally to end users, solely for use on Infineon hardware products. Any other use, reproduction, modification, translation, or compilation of the software is prohibited.

For further information on the Product, technology, delivery terms and conditions, and prices, please contact your nearest Infineon office or visit www.infineon.com.