

BRIGHTLANE™ 88Q5072 secure multi-gig automotive switch with integrated 100BASE-T1 PHY


11-port automotive Ethernet switch with advanced security & support for TSN

Infineon's first generation high-port count automotive BRIGHTLANE™ Ethernet switch, 88Q5072, is an 11-port Ethernet gigabit capacity switch that is fully compliant with IEEE802.3 automotive standard delivering high performance with low power consumption.

The 11-port Ethernet switch offers 7 integrated IEEE 100BASE-T1 PHYs, of which 6 are fixed as 100BASE-T1 ports, and 7th port is configurable as 1x IEEE 100BASE-TX PHY, 2x Multi-Speed SerDes (1/2.5/5 Gbps) or SGMII port, 1x RGMII or MII/RMII/GMII, 1xPCIe or SerDes. The switch offers local and remote management capabilities, providing easy access and configuration of the device.

This switch includes a high-performance Arm® Cortex® M7 CPU with dedicated on-chip memory to support AVB protocols such as Precision Time Protocol (PTP) and security firewall to protect from external malicious attacks. The switch employs advanced routing engine to support gigabit routing of the incoming packets without the CPU intervention. It offers highest level of security with Deep Packet Inspection (DPI) techniques, Denial of Service (DoS) engine and trusted boot functionality to secure the vehicle networks.

BRIGHTLANE™ 88Q5072 block diagram



PRODUCT BRIEF

Key features

Features

Processor

Benefits

- Integrated Arm® Cortex®-M7 CPU, 350 MHz with 1 MB SRAM

I/O interfaces

- 6x IEEE 100BASE-T1
- 1x IEEE 100BASE-T1 or 100BASE-TX
- 1x multi-speed SerDes (1/2.5/5 Gbps) or SGMII port
- 1x RGMII or MII/RMII/GMII ports
- 1x PCIe (Gen 3x1, 8Gbps) or SerDes(1/2.5Gbps)
- 2x SMI
 - Master interface to connect to external PHYs or additional switches
 - Slave interface to manage the switch
- Configurable GPIOs
- QSPI with configurable frequencies (19.2–83.3MHz)
- TWSI master interface
- JTAG interface for debugging

Package characteristics

- 17 mm x 17 mm, 356-pin ball array TFBGA, 0.8 mm pitch

EEPROM

- Slave interface with loader to configure the switch (32 kb–512 kb)

Target applications

- Central gateway
- In-vehicle infotainment
- Advanced Driver Assistance Systems (ADAS)
- Body domain controller

Published by
Infineon Technologies AG
Am Campeon 1-15, 85579 Neubiberg
Germany

© 2025 Infineon Technologies AG
All rights reserved.

Public

Date: 08/2025

Important notice

Products are sold or provided and delivered by Infineon Technologies AG and its affiliates (“Infineon”) subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

To the fullest extent permissible pursuant to applicable law, with respect to any information given in this document or in any associated documentation, Infineon disclaims all warranties and liabilities of any kind, whether express or implied, including but not limited to any warranties of merchantability, suitability of the products for the intended application or the specific use, or non-infringement of third-party rights.

Subject to the development and release of the products for series supply by Infineon, the technical specifications of the products are set forth in the relevant final data sheet provided by Infineon and, if any, agreed and signed specifications. Infineon's customers are required to evaluate the suitability of the products for the intended application or specific use.

The information given in this document is subject to change by Infineon at any time without notice.



Scan QR code and explore offering
www.infineon.com