

Product Brief

New 60V OptiMOS™5 in SSO8 and S3O8

A new product family targeting 12V and 24V applications

Infineon introduces its new 60V OptiMOS™5 power MOS front end technology in two leadless packages, the 5x6 mm² SSO8 (PG-TDSON-8) and 3x3 mm² S3O8 (PG-TSDSON-8) with highest quality level and robustness for automotive applications.

The new 60V technology OptiMOS™5 delivers more power and a leading performance. It offers reduced conduction losses and is optimized for drives and power conversion applications. Additionally, it provides an improved EMC behavior with the C_{iss} and C_{oss} being reduced by 70 percent, compared to the previous technology.

The SSO8 (PG-TDSON-8) package offers up to 41 A continuous current ratings, which is 20 percent higher than the standard DPAK at almost half of its footprint area. The footprint area of SSO8 is 33 mm² while the DPAK's is 65 mm². Moreover, the new generation of the SSO8 package enables superior switching performance and EMI behavior due to very low package inductance ($\approx 4x$ lower package inductivity vs traditional packages e.g. DPAK, D2PAK) by using the new copper-clip inter-contact technology.

The S3O8 (PG-TSDSON-8) package is suitable for very compact and robust automotive system solutions. The footprint of this package is less than 11mm² providing high current capability of up to 40A. Additionally, this package provides reduced package inductances and package parasitic as well as an improved solder contact area.

The new 60V product family is suitable for several 12V and 24V automotive applications, especially DC/DC, LED lighting, Wireless charging and all CAV (Commercial, construction and Agricultural Vehicles with a 24V board net) applications.

Key features

- > Lower package resistance and inductance
- > Small 5x6 mm² footprint of the leadless SSO8 package (PG-TDSON-8)
- > Small 3x3 mm² footprint of the leadless S3O8 package (PG-TSDSON-8)
- > Excellent thermal performance

Key benefits

- > Extended automotive qualification (beyond AEC-Q101)
- > Excellent thermal performance in compact form factor
- > Low gate charge and Qrr for reduced switching losses
- > 20% higher current capability (SSO8 vs. DPAK)

Key applications


- DCDC
- LED lighting
- Wireless charging
- ADAS
- CAV (24V) applications



New 60V OptiMOS™5 in SSO8 and S3O8

A new product family targeting 12V and 24V applications

Full LED headlamps



Product Table

Product Name	RDSon	ID	Package
IAUZ40N06S5L050	5.0mΩ	40A	PG-TSDSON-8
IAUC41N06S5N102	10.2mΩ	41A	PG-TDSON-8

Published by
Infineon Technologies AG
85579 Neuburg, Germany

© 2020 Infineon Technologies AG.
All Rights Reserved.

Please note!

THIS DOCUMENT IS FOR INFORMATION PURPOSES ONLY AND ANY INFORMATION GIVEN HEREIN SHALL IN NO EVENT BE REGARDED AS A WARRANTY, GUARANTEE OR DESCRIPTION OF ANY FUNCTIONALITY, CONDITIONS AND/OR QUALITY OF OUR PRODUCTS OR ANY SUITABILITY FOR A PARTICULAR PURPOSE. WITH REGARD TO THE TECHNICAL SPECIFICATIONS OF OUR PRODUCTS, WE KINDLY ASK YOU TO REFER TO THE RELEVANT PRODUCT DATA SHEETS PROVIDED BY US. OUR CUSTOMERS AND THEIR TECHNICAL DEPARTMENTS ARE REQUIRED TO EVALUATE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED APPLICATION.

WE RESERVE THE RIGHT TO CHANGE THIS DOCUMENT AND/OR THE INFORMATION GIVEN HEREIN AT ANY TIME.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life endangering applications, including but not limited to medical, nuclear, military, life critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.