

PSoC™ Automotive Multitouch Gen6L for sliders


Shorter time-to-market with superior touch performance and user experience

PSoC™ Automotive Multitouch [Gen6L](#) is a touch controller family leveraging Infineon Technologies AG's **10 years of experience in the touch controller** sector. The register-configurable methodology provides tried and tested algorithms developed over > 200 man years of Automotive firmware development.

A capacitive slider detects changes in capacitance to determine the location of one or more fingers on the surface of the slider. A typical slider system consists of the capacitive slider sensor, an FPC bonded to the sensor, and the touch controller mounted on the FPC or PCB. The touch controller then connects to a host processor. Users can interact with the displayed user interface through finger movements and gestures on the surface of the slider.

[CYAT6165X](#) is a capacitive slider controller with the sensing and processing technology to resolve the locations and report the positions of up to ten fingers on the slider. The touch controller converts an array of sensor capacitances into an array of digital values, which are processed by touch-detection and position-resolution algorithms in the controller. These algorithms determine the location and signal magnitude of each finger on the slider.

Block diagram



Key features

- Automotive Electronics Council (AEC) Q100 qualified
- MISRA-C / IATF 16949 compliant
- Touch controller:
 - 32-bit Arm® Cortex® CPU
 - Register-configurable
 - Noise-suppression technologies for display and EMI:
 - Auto armor technology
 - Spread-spectrum scanning
 - Effective 20 V drive
 - Display synchronization
- Water rejection and wet-finger tracking using dual sense capability
- Automatic glove mode switching
- Low-power wake-up options
- Field upgrades via bootloader
- Slider sensor self-test
- Manufacturing Test Kit (MTK)
- Performance (config dependent):
 - Up to 48 sense pins or 135 intersections (45 RX and 3 TX)
 - Ten touches at up to 250 Hz
 - Gloves (or overlay) up to 5 mm
 - TX frequency up to 350 kHz
 - 9 mW average power
 - 11 µW typical Deep Sleep power
- Communication:
 - I2C up to 400 kbps
 - SPI up to 8 Mbps
- Packages:
 - 56L QFN WF 8 × 8 × 1 mm
 - 64LD TQFP 10 × 10 × 1.4 mm
- Ambient temperature range:
 - Automotive-A: –40°C to 85°C
 - Automotive-S: –40°C to 105°C

PRODUCT BRIEF

Infineon provides:

- Application firmware
- Design guidance for the sensor and FPC
- Touchscreen sensor MTK

The Automotive Multitouch solutions are fully tested in an automated way (robot tests) against all specified performance parameters as well as EMI/EMC-compliance, ESD, and environment change tests. The validation reports are available to shorten development cycles.

Infineon Technologies AG’s auto armor technology meets the Automotive Electromagnetic Compatibility (EMC) requirements by preventing false touches caused by EMI from other electronic systems using advanced algorithms, including TX frequency spreading (also

reducing electromagnetic emissions up to 30%) and Automatic Frequency Hopping (AFH).

Gen6L provides a seamless integration of a capacitive wake-up button, which is capable of operating at <50 µA, allowing an increased power budget for other system components. Gen6L enables the implementation of both slider and wake-up button functionality using a single integrated device, reducing board space and costs.

PSoC™ Automotive Gen6L delivers a perfect user experience on touchscreens, trackpads, and sliders with a shorter development cycle. Gen6L meets the Automotive EMC requirements and supports low-power wake-up buttons, force touch, cut outs, and non-rectangular shapes for touchscreens.

Product	Target	Product status	Sense pins	Buttons	Low-power wake	Thick glove / overlay	Package
CYAT61659-64AS48	Slider	Active and preferred	48	Yes	Yes	Yes	64LD TQFP
CYAT61659-56LWS41	Slider	Active and preferred	41	Yes	Yes	Yes	64LD TQFP
See the datasheet for more options							

Published by
Infineon Technologies AG
Am Campeon 1-15, 85579 Neubiberg
Germany

© 2024 Infineon Technologies AG
All rights reserved.

Public

Document number:
002-39850 Rev. *A
Date: 07/2024

Please note!
This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information
For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings
Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.



Scan QR code and explore offering
www.infineon.com