


# EDT3 Diode for Automotive Applications

## Diode

### Quality Requirement Category: Automotive

#### Features

- 750V Emitter Controlled Diode technology
- Soft, fast switching
- Low reverse recovery charge
- Improved commutation behavior for reduced IGBT turn-on losses
- Small temperature coefficient
- 185°C maximum junction temperature



#### Applications

- Drives

#### Description

- Recommended for power modules

#### Product Validation

- Technology qualified for Automotive Applications. Product validation according to AEC-Q101.

#### Key Performance Parameters

Chip Type	$V_{RRM}$	$I_{Fn}$	Die Size	Package
IDC66D75H8A	750V	430A	66 mm <sup>2</sup>	Sawn on foil

## **Table of Contents**

<b>Features .....</b>	<b>1</b>
<b>Applications.....</b>	<b>1</b>
<b>Description .....</b>	<b>1</b>
<b>Product Validation.....</b>	<b>1</b>
<b>Key Performance Parameters .....</b>	<b>1</b>
<b>Table of Contents .....</b>	<b>2</b>
<b>1 Parameters and Characteristics.....</b>	<b>3</b>
<b>2 Further Electrical Characteristics .....</b>	<b>4</b>
<b>3 Chip Drawing.....</b>	<b>5</b>
<b>4 Bare Die Product Specifics .....</b>	<b>6</b>
<b>Revision History .....</b>	<b>6</b>

## 1 Parameters and Characteristics

**Table 1 Mechanical Parameters**

Raster size	5.64 x 11.81	mm <sup>2</sup>
Area total	66	mm <sup>2</sup>
Anode pad size	See chip drawing	
Silicon thickness	68	μm
Wafer size	200	mm
Maximum possible chips per wafer	390	
Passivation frontside	Photoimide	
Pad metal	AlSiCu	
Backside metal	Ni Ag system	
Die bond <sup>1</sup>	Soft Solder	
Frontside interconnect <sup>1</sup>	Wire bond: Al, ≤ 500 μm	
Reject ink dot size	Inkless	
Storage environment (<6 months)	For original and sealed MBB bags <sup>2</sup>	Ambient atmosphere air, temperature 17°C – 25°C

**Table 2 Maximum Ratings<sup>3</sup>**

Parameter	Symbol	Conditions	Value	Unit
Maximum reverse voltage	$V_{RRM}$	$25^{\circ}\text{C} \leq T_{vj} \leq 185^{\circ}\text{C}$	750	V
		$T_{vj} = -40^{\circ}\text{C}^4$	710	
Continuous forward current, limited by $T_{vj\ max}$	$I_F$		_5	A
Pulsed forward current, $t_p$ limited by $T_{vj\ max}$	$I_{F,pulse}$		1290	A
Virtual junction temperature	$T_{vj}$		-40 ... +185	°C
Safe operating area	SOA	$I_{F,max} = 860\text{A}, V_{R,max} = V_{RRM}, -40^{\circ}\text{C} \leq T_{vj} \leq 185^{\circ}\text{C}$		

<sup>1</sup> Depending on customer specific assembly process

<sup>2</sup> [https://www.infineon.com/dgdl/Storage\\_of\\_Products\\_Supplied\\_by\\_Infineon\\_Technologie.pdf?fileId=5546d461641369bf01643b95d8500011](https://www.infineon.com/dgdl/Storage_of_Products_Supplied_by_Infineon_Technologie.pdf?fileId=5546d461641369bf01643b95d8500011)

<sup>3</sup> Not subject to production test - verified by design/characterization.

<sup>4</sup>  $V_{RRM}$  increases linearly between -40°C and 25°C.

<sup>5</sup> Depending on thermal properties of assembly.

**Table 3 Static Characteristics (Tested on Wafer),  $T_{vj}=25^{\circ}\text{C}$**

Parameter	Symbol	Conditions	Value			Unit
			min.	typ.	max.	
Forward voltage drop	$V_F$	$I_F = 86\text{A}$	-	1.35	1.5	V
Reverse leakage current	$I_R$	$V_R = 750\text{V}$	-	-	100	$\mu\text{A}$

**Table 4 Electrical Characteristics<sup>1</sup>**


Parameter	Symbol	Conditions	Value			Unit	
			min.	typ.	max.		
		$I_F = 430\text{A}$	$T_{vj} = 25^{\circ}\text{C}$	-	2.00	2.3	V
			$T_{vj} = 185^{\circ}\text{C}$	-	1.70	-	

## 2 Further Electrical Characteristics

Note: Switching characteristics and thermal properties are dependent on module design and mounting technology and can therefore not be specified for a bare die.

<sup>1</sup> Not subject to production test - verified by design/characterization.

### 3 Chip Drawing



## **4 Bare Die Product Specifics**

Note: Test coverage at wafer level for diodes cannot cover the full range of customer application conditions. Therefore it is the responsibility of the customer to test all performance characteristics, which are relevant for their specific application, at the package level, including SOA.

### **Description**

- AQL 0.1 for visual inspection according to failure catalogue

### **Revision History**

<b>Document version</b>	<b>Date of release</b>	<b>Description of changes</b>
V1.00	20 <sup>th</sup> of January 2026	Initial Datasheet

#### Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2026-January-20**

**Published by**

**Infineon Technologies AG**

**81726 München, Germany**

**© 2026 Infineon Technologies AG.**

**All Rights Reserved.**

**Do you have a question about this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

Error! Unknown document property name.

#### IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

#### WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.