

XENSIV™ DrillTriggerV2

Add on for 3D magnetic 2GO kits

User Guide

About this document

Scope and purpose

The purpose of this document is to outline the functionality and configuration of the XENSIV™ DrillTriggerV2. It explains the assembly and setup of the hardware as well as the GUI and its options.

Intended audience

This document is designed for customers who have purchased the DrillTriggerV2 Add on.



Table of contents

About this document..... 1

Table of contents..... 2

1 What you need 3

2 How to assemble 4

3 GUI 5

3.1 Search for the software in the Infineon Developer Center and install it5

3.2 Open the software, select the COM port of the 2Go kit.....5

3.3 Select the app for the DrillTriggerV26

3.4 DrillTriggerV2 app options6

Revision history..... 7

Disclaimer..... 8

1 What you need

1 What you need




Figure 1 XENSIV™ DrillTriggerV2 – needed components

2 How to assemble




Figure 2 XENSIV™ DrillTriggerV2 - assembly

3 GUI

3.1 Search for the software in the Infineon Developer Center and install it




Figure 3 XENSIV™ DrillTriggerV2 – TLx493D software installation

3.2 Open the software, select the COM port of the 2Go kit




Figure 4 XENSIV™ DrillTriggerV2 – TLx493D software port selection

3.3 Select the app for the DrillTriggerV2




Figure 5 XENSIV™ DrillTriggerV2 – TLx493D software app selection

3.4 DrillTriggerV2 app options




Figure 6 XENSIV™ DrillTriggerV2 – TLx493D software app options

Revision history

Document revision	Date	Description of changes
Revision 1.0	2024-08-02	Initial release

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition August 2024

Published by

Infineon Technologies AG

81726 Munich, Germany

**© 2024 Infineon Technologies AG.
All Rights Reserved.**

Do you have a question about this document?

Email:

erratum@infineon.com

Document reference

User guide number

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.