

Important notice on ams-OSRAM documents



As part of the acquisition of the non-optical analog/mixed-signal sensor portfolio from ams-OSRAM by Infineon, Infineon is in the process of rebranding all relevant documents. Due to the large volume of documents, this process will be completed in phases. In the interim, we are providing access to legacy ams-OSRAM documents under the terms of a trademark license agreement.

The attached document is a legacy ams-OSRAM document and has not been rebranded to reflect the acquisition by Infineon.

Please note that:

Infineon Technologies AG is the owner and provider of the document and the products/services described therein, effective from 1 July 2026, the date of “closing”.

All terms and conditions, including but not limited to warranties, liabilities, and intellectual property rights, are now governed by Infineon's policies and agreements.

All products described in these documents retain their original qualifications and certifications. Infineon confirms that no changes will be made to the products that would affect their compliance with relevant standards, regulations, or certifications.

Contact:

Infineon Technologies AG
Am Campeon 1-15
85579 Neubiberg
Germany

© 2026 Infineon Technologies AG
All Rights Reserved.
Email: erratum@infineon.com

amun AS5911

Datasheet

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

ams-osram.com

© All rights reserved

amun OSRAM

Table of contents

- 1 General description 3
 - 1.1 Key benefits & features..... 4
 - 1.2 Applications 4
 - 1.3 Block diagram 5
- 2 Package drawings & markings 6
- 3 Revision information 8
- 4 Legal information 9

AS5911 256-channel low noise current-to-digital converter

1 General description

The AS5911 is an ultra-low noise, 256-channel low power current to digital converter that enables the readout of photodiodes of a CT detector with highest sensitivity. The output currents of 256 photodiodes are converted simultaneously into digital without any dead time resulting in no charge loss on the inputs. The AS5911 combines current-to-voltage integration and A/D conversion for 256-channels in one device. The ADC architecture with its low-noise integrators, coarse quantizer, sample-and-hold and fine quantizer guarantee lowest input related noise of maximum 0.29 fC (low noise mode) at an input current range of 0.5 μ A. The input current range of the ADC is selectable between 0.5 μ A and 1 μ A.

The AS5911 supports two supply concepts: a single analog and true ground supply, in both modes the photodiodes are zero biased for ultra-low dark current of the photodiode. In true ground mode, the AS5911 operates at ± 1.5 V dual analog supply while in single supply mode only a single analog supply of +3.0 V is needed. The device detects automatically the chosen supply concept. No external components are required for supply decoupling. To reduce PCB area and simplify the assembly process, decoupling capacitors for supply and reference voltages are integrated in the 14 x 14 mm² FBGA package. The on-chip LDOs, reference voltages and a temperature sensor minimize the external component requirements and reduces the bill of material.

Full-scale range, integration time and power mode are configurable over a SPI-compatible serial interface as well as the digital output modes of the LVDS interface. In low power mode, the power dissipation can be minimized down to 1.25 mW per channel for reduced self-heating of the CT detector. The adjustable integration time down to 51 μ s allow very high frame rates. The operating range of AS5911 is specified from 0 °C to 85 °C.

1.1 Key benefits & features

The benefits and features of AS5911, 256-channel low noise current-to-digital converter are listed below:

Table 1: Added value of using AS5911

Benefits	Features
256-channel in 14 x 14 mm ² FBGA package.	No external components required. Integrated capacitors for supply and reference decoupling
Ultra-low noise of 0.29 fC at 0.5 μ A input current in low noise mode.	No charge loss. Continuous charge integration due to zero dead time of ADC architecture.
Lowest power dissipation of 1.25 mW per channel in low power mode	Selectable full-scale range of 0.5 μ A in low range and 1 μ A in high range.
Adjustable integration time down to 51 μ s (20 kSPS) at 20-bit resolution. Up to 26-bit at integration times of 1 ms.	Adjustable full-scale range, integration time and power consumption via SPI interface as well as adjustable output modes via LVDS.
Zero biased photodiodes (true ground concept) for ultra-low dark currents.	Selectable power supply concept between dual ± 1.5 V analog supply (true ground concept) or single +3.0 V analog supply.
Integral Linearity of $\pm 0.080\%$ of reading and ± 0.2 ppm of full-scale range (all channels active).	On-chip LDOs, voltage references and temperature sensor.
Automatic zero offset calibration, input charge calibration and linearity calibration.	Built-in diagnostic modes for testing full detector signal chain.


1.2 Applications

- Medical, industrial and security CT scanner data acquisition.
- Photodiode sensors.
- Multi-channel sensors with current output.
- DAS (Data Acquisition System) for current input.

1.3 Block diagram


The functional blocks of this device are shown below:

Figure 1: Functional blocks of AS5911 for true ground concept



2 Package drawings & markings

Figure 2: FBGA400 package outline drawing of AS5911



- (1) All dimensions are in millimeters. Angles in degrees.
- (2) Dimensioning and tolerancing conform to ASME Y14.5M-1994.
- (3) Maximum solder ball diameter measured parallel to datum C. Post reflow diameter.
- (4) Datum C and seating plane are defined by the spherical crowns of the solder balls.
- (5) This package contains no lead (Pb).
- (6) This drawing is subject to change without notice.

Figure 3: FBGA400 package marking/code of AS5911



3 Revision information

Document status	Product status	Definition
Product Preview	Pre-development	Information in this datasheet is based on product ideas in the planning phase of development. All specifications are design goals without any warranty and are subject to change without notice
Preliminary Datasheet	Pre-production	Information in this datasheet is based on products in the design, validation or qualification phase of development. The performance and parameters shown in this document are preliminary without any warranty and are subject to change without notice
Datasheet	Production	Information in this datasheet is based on products in ramp-up to full production or full production which conform to specifications in accordance with the terms of ams-OSRAM AG standard warranty as given in the General Terms of Trade

Other definitions

Draft / Preliminary:
The draft / preliminary status of a document indicates that the content is still under internal review and subject to change without notice. ams-OSRAM AG does not give any warranties as to the accuracy or completeness of information included in a draft / preliminary version of a document and shall have no liability for the consequences of use of such information.

Short datasheet:
A short datasheet is intended for quick reference only, it is an extract from a full datasheet with the same product number(s) and title. For detailed and full information always see the relevant full datasheet. In case of any inconsistency or conflict with the short datasheet, the full datasheet shall prevail.

Changes from previous released version to current revision v2-00

Page

This short datasheet is derived from v2-00 of full datasheet.

- Page and figure numbers for the previous version may differ from page and figure numbers in the current revision.
- Correction of typographical errors is not explicitly mentioned.

4 Legal information

Copyright & disclaimer

Copyright ams-OSRAM AG, Tobelbader Strasse 30, 8141 Premstaetten, Austria-Europe. Trademarks Registered. All rights reserved. The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner.

Devices sold by ams-OSRAM AG are covered by the warranty and patent indemnification provisions appearing in its General Terms of Trade. ams-OSRAM AG makes no warranty, express, statutory, implied, or by description regarding the information set forth herein. ams-OSRAM AG reserves the right to change specifications and prices at any time and without notice. Therefore, prior to designing this product into a system, it is necessary to check with ams-OSRAM AG for current information. This product is intended for use in commercial applications. Applications requiring extended temperature range, unusual environmental requirements, or high reliability applications, such as military, medical life-support or life-sustaining equipment are specifically not recommended without additional processing by ams-OSRAM AG for each application. This product is provided by ams-OSRAM AG "AS IS" and any express or implied warranties, including, but not limited to the implied warranties of merchantability and fitness for a particular purpose are disclaimed.

ams-OSRAM AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data herein. No obligation or liability to recipient or any third party shall arise or flow out of ams-OSRAM AG rendering of technical or other services.

Product and functional safety devices/applications or medical devices/applications:

ams-OSRAM AG components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices. ams-OSRAM AG products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using ams-OSRAM AG components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of ams-OSRAM AG immediately and ams-OSRAM AG and buyer and /or customer will analyze and coordinate the customer-specific request between ams-OSRAM AG and buyer and/or customer.

ams OSRAM semiconductor RoHS compliance statement

RoHS compliant: The term RoHS compliant means that ams-OSRAM AG semiconductor products fully comply with current RoHS directives. Our semiconductor products do not contain any chemicals for all 6 substance categories plus additional 4 substance categories (per amendment EU 2015/863), including the requirement that lead not exceed 0.1% by weight in homogeneous materials.

Important information: The information provided in this statement represents ams-OSRAM AG knowledge and belief as of the date that it is provided. ams-OSRAM AG bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. ams-OSRAM AG has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. ams-OSRAM AG and ams-OSRAM AG suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

Headquarters

ams-OSRAM AG
Tobelbader Strasse 30
8141 Premstaetten
Austria, Europe
Tel: +43 (0) 3136 500 0

Please visit our website at ams-osram.com
For information about our products go to [Products](#)
For technical support use our [Technical Support Form](#)
For feedback about this document use [Document Feedback](#)
For sales offices and branches go to [Sales Offices / Branches](#)
For distributors and sales representatives go to [Channel Partners](#)