

IRHLNM77110(2N7609U8), IRHLNMC77110

PD-97326E

Radiation Hardened Logic Level Power MOSFET
Surface Mount (SMD-0.2)
100V, 6.5A, N-channel, R7 Technology

Features


- 5V CMOS and TTL compatible
- Fast switching
- Single event effect (SEE) hardened
- Low total gate charge
- Simple drive requirements
- Hermetically sealed
- Ceramic package
- Surface mount
- Light weight
- ESD rating: Class 1A per MIL-STD-750, Method 1020

Potential Applications

- Isolated DC-DC converters
- Motor drives
- Electric propulsion
- Thermal management

Product Summary

- **BV_{DSS}** : 100V
- **I_D** : 6.5A
- **$R_{DS(on), max}$** : 0.29 Ω
- **Q_G** : 11nC



Product Validation

Qualified to IR HiRel's S-level screening flow which is equivalent to MIL-PRF-19500

Description

IR HiRel R7 Logic Level Power MOSFETs provide simple solution to interfacing CMOS and TTL control circuits to power devices in space and other radiation environments. The threshold voltage remains within acceptable operating limits over the full operating temperature and post radiation. This is achieved while maintaining single event gate rupture and single event burnout immunity. The device is ideal when used to interface directly with most logic gates, linear IC's, micro-controllers, and other device types that operate from a 3.3-5V source. It may also be used to increase the output current of a PWM, voltage comparator or an operational amplifier where the logic level drive signal is available.

IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)

Ordering Information

Ordering Information

Table 1 **Ordering options**

Part number	Package	Screening Level	TID Level
IRHLNM77110	SMD-0.2	COTS	100 krad(Si)
IRHLNM73110	SMD-0.2	COTS	300 krad(Si)
IRHLNM77110SCS	SMD-0.2	S-Level	100 krad(Si)
IRHLNM73110SCS	SMD-0.2	S-Level	300 krad(Si)
IRHLNM77110SCV	SMD-0.2	TXV-level	100 krad(Si)
IRHLNMC77110	SMD-0.2 with ceramic lid	COTS	100 krad(Si)
IRHLNMC73110	SMD-0.2 with ceramic lid	COTS	300 krad(Si)
IRHLNMC77110SCS	SMD-0.2 with ceramic lid	S-level	100 krad(Si)
IRHLNMC73110SCS	SMD-0.2 with ceramic lid	S-level	300 krad(Si)

Table of contents

Table of contents

Features	1
Potential Applications.....	1
Product Validation	1
Description	1
Ordering Information	2
Table of contents	3
1 Absolute Maximum Ratings	4
2 Device Characteristics	5
2.1 Electrical Characteristics (Pre-Irradiation).....	5
2.2 Source-Drain Diode Ratings and Characteristics (Pre-Irradiation)	6
2.3 Thermal Characteristics	6
2.4 Radiation Characteristics	6
2.4.1 Electrical Characteristics — Post Total Dose Irradiation	6
2.4.2 Single Event Effects — Safe Operating Area	7
3 Electrical Characteristics Curves (Pre-irradiation)	8
4 Test Circuits (Pre-irradiation)	12
5 Package Outline	13
Revision history.....	14

Absolute Maximum Ratings

1 Absolute Maximum Ratings

Table 2 Absolute Maximum Ratings (Pre-Irradiation)

Symbol	Parameter	Value	Unit
$I_{D1} @ V_{GS} = 4.5V, T_C = 25^{\circ}C$	Continuous Drain Current	6.5	A
$I_{D2} @ V_{GS} = 4.5V, T_C = 100^{\circ}C$	Continuous Drain Current	4.1	A
$I_{DM} @ T_C = 25^{\circ}C$	Pulsed Drain Current ¹	26	A
$P_D @ T_C = 25^{\circ}C$	Maximum Power Dissipation	23.2	W
	Linear Derating Factor	0.18	W/ $^{\circ}C$
V_{GS}	Gate-to-Source Voltage	± 10	V
E_{AS}	Single Pulse Avalanche Energy ²	21	mJ
I_{AR}	Avalanche Current ¹	6.5	A
E_{AR}	Repetitive Avalanche Energy ¹	2.32	mJ
dv/dt	Peak Diode Reverse Recovery ³	4.3	V/ns
T_J T_{STG}	Operating Junction and Storage Temperature Range	-55 to +150	$^{\circ}C$
	Lead Temperature	300 (for 5s)	
	Weight	0.25 (Typical)	g

¹ Repetitive Rating; Pulse width limited by maximum junction temperature.² $V_{DD} = 25V$, starting $T_J = 25^{\circ}C$, $L = 0.98mH$, Peak $I_L = 6.5A$, $V_{GS} = 10V$ ³ $I_{SD} \leq 6.5A$, $di/dt \leq 490A/\mu s$, $V_{DD} \leq 100V$, $T_J \leq 150^{\circ}C$

Device Characteristics

2 Device Characteristics

2.1 Electrical Characteristics (Pre-Irradiation)

Table 3 Static and Dynamic Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (Unless Otherwise Specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
BV_{DSS}	Drain-to-Source Breakdown Voltage	100	—	—	V	$V_{GS} = 0V, I_D = 250\mu A$
$\Delta BV_{DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	—	0.105	—	V/ $^\circ\text{C}$	Reference to 25°C , $I_D = 250\mu A$
$R_{DS(on)}$	Static Drain-to-Source On-State Resistance	—	—	0.29	Ω	$V_{GS} = 4.5V, I_{D2} = 4.1A^1$
$V_{GS(th)}$	Gate Threshold Voltage	1.0	—	2.0	V	$V_{DS} = V_{GS}, I_D = 250\mu A$
$\Delta V_{GS(th)}/\Delta T_J$	Gate Threshold Voltage Coefficient	—	-6.0	—	mV/ $^\circ\text{C}$	
G_{fs}	Forward Transconductance	3.5	—	—	S	$V_{DS} = 15V, I_{D2} = 4.1A^1$
I_{DSS}	Zero Gate Voltage Drain Current	—	—	1.0	μA	$V_{DS} = 80V, V_{GS} = 0V$
		—	—	10		$V_{DS} = 80V, V_{GS} = 0V, T_J = 125^\circ\text{C}$
I_{GSS}	Gate-to-Source Leakage Forward	—	—	100	nA	$V_{GS} = 10V$
	Gate-to-Source Leakage Reverse	—	—	-100		$V_{GS} = -10V$
Q_G	Total Gate Charge	—	—	11	nC	$I_{D1} = 6.5A$
Q_{GS}	Gate-to-Source Charge	—	—	4.0		$V_{DS} = 50V$
Q_{GD}	Gate-to-Drain ('Miller') Charge	—	—	6.0		$V_{GS} = 4.5V$
$t_{d(on)}$	Turn-On Delay Time	—	—	18	ns	$I_{D1} = 6.5A^{**}$ $V_{DD} = 50V$ $R_G = 7.5\Omega$ $V_{GS} = 5.0V$
t_r	Rise Time	—	—	75		
$t_{d(off)}$	Turn-Off Delay Time	—	—	50		
t_f	Fall Time	—	—	12		
$L_s + L_D$	Total Inductance	—	6.8	—	nH	Measured from center of Drain pad to center of Source pad
C_{iss}	Input Capacitance	—	572	—	pF	$V_{GS} = 0V$
C_{oss}	Output Capacitance	—	124	—		$V_{DS} = 20V$
C_{rss}	Reverse Transfer Capacitance	—	1.6	—		$f = 1.0MHz$
R_G	Gate Resistance	—	10.5	—	Ω	$f = 1.0MHz$, open drain

** Switching speed maximum limits are based on manufacturing test equipment and capability.

¹ Pulse width $\leq 300\mu s$; Duty Cycle $\leq 2\%$

Device Characteristics

2.2 Source-Drain Diode Ratings and Characteristics (Pre-Irradiation)

Table 4 Source-Drain Diode Characteristics

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
I _S	Continuous Source Current (Body Diode)	—	—	6.5	A	
I _{SM}	Pulsed Source Current (Body Diode) ¹	—	—	26	A	
V _{SD}	Diode Forward Voltage	—	—	1.2	V	T _J = 25°C, I _S = 6.5A, V _{GS} = 0V ²
t _{rr}	Reverse Recovery Time	—	—	215	ns	T _J = 25°C, I _F = 6.5A, V _{DD} ≤ 25V di/dt = 100A/μs
Q _{rr}	Reverse Recovery Charge	—	703	—	nC	
t _{on}	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by L _S +L _D)				

2.3 Thermal Characteristics

Table 5 Thermal Resistance

Symbol	Parameter	Min.	Typ.	Max.	Unit
$R_{\theta JC}$	Junction-to-Case	—	—	5.4	$^\circ\text{C}/\text{W}$

2.4 Radiation Characteristics

IR HiRel radiation hardened MOSFETs are tested to verify their radiation hardness capability. The hardness assurance program at IR HiRel is comprised of two radiation environments. Every manufacturing lot is tested for total ionizing dose (per notes 3 and 4) using the TO-3 package. Both pre- and post-irradiation performance are tested and specified using the same drive circuitry and test conditions in order to provide a direct comparison.

2.4.1 Electrical Characteristics — Post Total Dose Irradiation

Table 6 Electrical Characteristics @ $T_J = 25^\circ\text{C}$, Post Total Dose Irradiation ^{3, 4}

Symbol	Parameter	Up to 300 krad (Si) ⁵		Unit	Test Conditions
		Min.	Max.		
BV_{DSS}	Drain-to-Source Breakdown Voltage	100	—	V	$V_{GS} = 0\text{V}$, $I_D = 250\mu\text{A}$
$V_{GS(th)}$	Gate Threshold Voltage	1.0	2.0	V	$V_{DS} = V_{GS}$, $I_D = 250\mu\text{A}$
I_{GSS}	Gate-to-Source Leakage Forward	—	100	nA	$V_{GS} = 10\text{V}$
	Gate-to-Source Leakage Reverse	—	-100		$V_{GS} = -10\text{V}$
I_{DSS}	Zero Gate Voltage Drain Current	—	1.0	μA	$V_{DS} = 80\text{V}$, $V_{GS} = 0\text{V}$
$R_{DS(on)}$	Static Drain-to-Source On-State Resistance (TO-3) ²	—	0.26	Ω	$V_{GS} = 4.5\text{V}$, $I_{D2} = 4.1\text{A}$
$R_{DS(on)}$	Static Drain-to-Source On-State Resistance (SMD-0.2) ²	—	0.29	Ω	$V_{GS} = 4.5\text{V}$, $I_{D2} = 4.1\text{A}$
V_{SD}	Diode Forward Voltage	—	1.2	V	$V_{GS} = 0\text{V}$, $I_F = 6.5\text{A}$

¹ Repetitive Rating; Pulse width limited by maximum junction temperature.

² Pulse width $\leq 300\mu\text{s}$; Duty Cycle $\leq 2\%$

³ Total Dose Irradiation with V_{GS} Bias. $V_{GS} = 10\text{V}$ applied and $V_{DS} = 0$ during irradiation per MIL-STD-750, Method 1019, condition A.

⁴ Total Dose Irradiation with V_{DS} Bias. $V_{DS} = 80\text{V}$ applied and $V_{GS} = 0$ during irradiation per MIL-STD-750, Method 1019, condition A.

⁵ Part numbers IRHLNM77110, IRHLNM73110, IRHLNMC77110 and IRHLNMC73110

IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)

Device Characteristics

2.4.2 Single Event Effects — Safe Operating Area

IR HiRel radiation hardened MOSFETs have been characterized in heavy ion environment for Single Event Effects (SEE). Single Event Effects characterization is illustrated in Fig. 1 and Table 7.

Table 7 Worst Case Single Event Effects Safe Operating Area

LET (MeV·cm ² /mg)	Energy (MeV)	Range (μm)	V _{DS} (V)					
			V _{GS} = 0V	V _{GS} = -2V	V _{GS} = -4V	V _{GS} = -5V	V _{GS} = -6V	V _{GS} = -7V
38 ± 5%	300 ± 7.5%	38 ± 7.5%	100	100	100	100	100	100
62 ± 5%	355 ± 7.5%	33 ± 7.5%	100	100	100	100	100	—
85 ± 5%	380 ± 10%	29 ± 7.5%	100	100	100	100	—	—




Figure 1 Worst Case Single Event Effect, Safe Operating Area

IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)

Electrical Characteristics Curves (Pre-irradiation)

3 Electrical Characteristics Curves (Pre-irradiation)




Figure 2 Typical Output Characteristics




Figure 3 Typical Output Characteristics




Figure 4 Typical Transfer Characteristics




Figure 5 Normalized On-Resistance Vs. Temperature

IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)

Electrical Characteristics Curves (Pre-irradiation)




Figure 6 Typical On-Resistance Vs. Gate Voltage




Figure 7 Typical On-Resistance Vs. Drain Current




Figure 8 Typical Drain-to-Source Breakdown Voltage Vs. Temperature




Figure 9 Typical Threshold Voltage Vs. Temperature

IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)

Electrical Characteristics Curves (Pre-irradiation)




Figure 10 Typical Capacitance Vs. Drain-to-Source Voltage

Figure 11 Typical Gate Charge Vs. Gate-to-Source Voltage




Figure 12 Typical Source-Drain Current Vs. Diode Forward Voltage

Figure 13 Maximum Drain Current Vs. Case Temperature

IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)

Electrical Characteristics Curves (Pre-irradiation)




Figure 14 Maximum Safe Operating Area

Figure 15 Maximum Avalanche Energy Vs. Junction Temperature




Figure 16 Maximum Effective Transient Thermal Impedance, Junction-to-Case

IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)

Test Circuits (Pre-irradiation)

4 Test Circuits (Pre-irradiation)




Figure 17 Gate Charge Test Circuit




Figure 18 Gate Charge Waveform




Figure 19 Unclamped Inductive Test Circuit




Figure 20 Unclamped Inductive Waveform




Figure 21 Switching Time Test Circuit




Figure 22 Switching Time Waveforms


IRHLNM77110(2N7609U8), IRHLNMC77110

Radiation Hardened Logic Level Power MOSFET Surface-Mount (SMD-0.2)


Package Outline

5 Package Outline

Note: For the most updated package outline, please see the website: [SMD-0.2 \(Metal Lid\)](#)



Note: For the most updated package outline, please see the website: [SMD-0.2 \(Ceramic Lid\)](#)



Revision history**Revision history**

Document version	Date of release	Description of changes
	10/05/2010	Datasheet (PD-97326)
Rev A	02/21/2012	Updated based on ECN-18330
Rev B	12/12/2014	Updated based on ECN-1120_03069
Rev C	02/10/2016	Added Ceramic package
Rev D	11/14/2018	Updated based on ECN-1120_06315
Rev E	09/13/2023	Updated based on ECN-1120_09632

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-09-13

Published by

**International Rectifier HiRel Products,
Inc.**

**An Infineon Technologies company
El Segundo, California 90245 USA**

**© 2023 Infineon Technologies AG.
All Rights Reserved.**

**Do you have a question about this
document?**

Email: erratum@infineon.com

Document reference

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest International Rectifier HiRel Products, Inc., an Infineon Technologies company, office.

International Rectifier HiRel Components may only be used in life-support devices or systems with the expressed written approval of International Rectifier HiRel Products, Inc., an Infineon Technologies company, if failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety and effectiveness of that device or system.

Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.