

# IRHNA67264 (JANSR2N7585U2)

PD-96990E

## Radiation Hardened Power MOSFET Surface Mount (SMD-2) 250V, 50A, N-channel, R6 Technology

### Features

- Single event effect (SEE) hardened (up to LET of 85 MeV·cm<sup>2</sup>/mg)
- Low R<sub>DS(on)</sub>
- Low total gate charge
- Simple drive requirements
- Hermetically sealed
- Ceramic package
- Light weight
- Surface mount
- ESD rating: Class 3A per MIL-STD-750, Method 1020

### Potential Applications

- DC-DC converter
- Motor drives

### Product Validation

Qualified to JANS screening flow according to MIL-PRF-19500 for space applications

### Description

IR HiRel R6 technology provides superior power MOSFETs for space applications. These devices have improved immunity to Single Event Effect (SEE) and have been characterized for useful performance with Linear Energy Transfer (LET) up to 85 MeV·cm<sup>2</sup>/mg. Their combination of low R<sub>DS(on)</sub> and fast switching times will allow for better performance in applications such as DC-DC converters or motor drives. These devices retain all of the well established advantages of MOSFETs such as voltage control, fast switching and temperature stability of electrical parameters.

### Ordering Information

**Table 1** Ordering options

| Part number   | Package | Screening Level | TID Level     |
|---------------|---------|-----------------|---------------|
| IRHNA67264    | SMD-2   | COTS            | 100 krad (Si) |
| IRHNA67264SCS | SMD-2   | S-Level         | 100 krad (Si) |
| JANSR2N7585U2 | SMD-2   | JANS            | 100 krad (Si) |
| IRHNA63264    | SMD-2   | COTS            | 300 krad (Si) |
| JANSF2N7585U2 | SMD-2   | JANS            | 300 krad (Si) |

### Product Summary

- **Part number:** IRHNA67264 (JANSR2N7585U2), IRHNA63264 (JANSR2N7585U2)
- **REF:** MIL-PRF-19500/760
- **Radiation level:** 100 krad (Si), 300 krad (Si)
- **R<sub>DS(on), max</sub>:** 40mΩ



**Table of contents**

**Table of contents**

|  |           |
|--|-----------|
| <b>Features .....</b>  | <b>1</b>  |
| <b>Potential Applications.....</b>   | <b>1</b>  |
| <b>Product Validation.....</b>   | <b>1</b>  |
| <b>Description .....</b>   | <b>1</b>  |
| <b>Ordering Information.....</b>   | <b>1</b>  |
| <b>Table of contents.....</b>  | <b>2</b>  |
| <b>1 Absolute Maximum Ratings .....</b>                                    | <b>3</b>  |
| <b>2 Device Characteristics .....</b>                                      | <b>4</b>  |
| 2.1 Electrical Characteristics (Pre-Irradiation).....                      | 4         |
| 2.2 Source-Drain Diode Ratings and Characteristics (Pre-Irradiation) ..... | 5         |
| 2.3 Thermal Characteristics .....  | 5         |
| 2.4 Radiation Characteristics.....   | 5         |
| 2.4.1 Electrical Characteristics — Post Total Dose Irradiation .....       | 5         |
| 2.4.2 Single Event Effects — Safe Operating Area.....                      | 6         |
| <b>3 Electrical Characteristics Curves (Pre-irradiation) .....</b>         | <b>7</b>  |
| <b>4 Test Circuits (Pre-irradiation) .....</b>                             | <b>11</b> |
| <b>5 Package Outline.....</b>  | <b>12</b> |
| <b>Revision history.....</b>   | <b>13</b> |

**Absolute Maximum Ratings**

**1 Absolute Maximum Ratings**

**Table 2 Absolute Maximum Ratings (Pre-Irradiation)**

| Symbol                                     | Parameter   | Value         | Unit |
|--|---|---------------|------|
| $I_{D1} @ V_{GS} = 12V, T_C = 25^\circ C$  | Continuous Drain Current                            | 50            | A    |
| $I_{D2} @ V_{GS} = 12V, T_C = 100^\circ C$ | Continuous Drain Current                            | 31.5          | A    |
| $I_{DM} @ T_C = 25^\circ C$                | Pulsed Drain Current <sup>1</sup>                   | 200           | A    |
| $P_D @ T_C = 25^\circ C$                   | Maximum Power Dissipation                           | 250           | W    |
|  | Linear Derating Factor                              | 2.0           | W/°C |
| $V_{GS}$                                   | Gate-to-Source Voltage                              | ± 20          | V    |
| $E_{AS}$                                   | Single Pulse Avalanche Energy <sup>2</sup>          | 240           | mJ   |
| $I_{AR}$                                   | Avalanche Current <sup>1</sup>                      | 50            | A    |
| $E_{AR}$                                   | Repetitive Avalanche Energy <sup>1</sup>            | 25            | mJ   |
| dv/dt                                      | Peak Diode Reverse Recovery <sup>3</sup>            | 5.0           | V/ns |
| $T_J$<br>$T_{STG}$                         | Operating Junction and<br>Storage Temperature Range | -55 to +150   | °C   |
|  | Lead Temperature                                    | 300 ( for 5s) |      |
|  | Weight  | 3.3 (Typical) |      |

<sup>1</sup> Repetitive Rating; Pulse width limited by maximum junction temperature.

<sup>2</sup>  $V_{DD} = 50V$ , starting  $T_J = 25^\circ C$ ,  $L = 0.19mH$ , Peak  $I_L = 50A$ ,  $V_{GS} = 12V$

<sup>3</sup>  $I_{SD} \leq 50A$ ,  $di/dt \leq 900A/\mu s$ ,  $V_{DD} \leq 250V$ ,  $T_J \leq 150^\circ C$

**Device Characteristics**

**2 Device Characteristics**

**2.1 Electrical Characteristics (Pre-Irradiation)**

**Table 3 Static and Dynamic Electrical Characteristics @ T<sub>j</sub> = 25°C (Unless Otherwise Specified)**

| Symbol                         | Parameter                                  | Min. | Typ.  | Max. | Unit  | Test Conditions  |
|--------------------------------|--|------|-------|------|-------|--|
| $V_{DSS}$                      | Drain-to-Source Breakdown Voltage          | 250  | —     | —    | V     | $V_{GS} = 0V, I_D = 1.0mA$   |
| $\Delta BV_{DSS}/\Delta T_J$   | Breakdown Voltage Temp. Coefficient        | —    | 0.3   | —    | V/°C  | Reference to 25°C, $I_D = 1.0mA$   |
| $R_{DS(on)}$                   | Static Drain-to-Source On-State Resistance | —    | —     | 40   | mΩ    | $V_{GS} = 12V, I_{D2} = 31.5A^1$   |
| $V_{GS(th)}$                   | Gate Threshold Voltage                     | 2.0  | —     | 4.0  | V     | $V_{DS} = V_{GS}, I_D = 1mA$   |
| $\Delta V_{GS(th)}/\Delta T_J$ | Gate Threshold Voltage Coefficient         | —    | -10.1 | —    | mV/°C |  |
| $G_{fs}$                       | Forward Transconductance                   | 37   | —     | —    | S     | $V_{DS} = 15V, I_{D2} = 31.5A^1$   |
| $I_{DSS}$                      | Zero Gate Voltage Drain Current            | —    | —     | 10   | μA    | $V_{DS} = 200V, V_{GS} = 0V$   |
|                                |  | —    | —     | 25   |       | $V_{DS} = 200V, V_{GS} = 0V, T_J = 125°C$                                      |
| $I_{GSS}$                      | Gate-to-Source Leakage Forward             | —    | —     | 100  | nA    | $V_{GS} = 20V$   |
|                                | Gate-to-Source Leakage Reverse             | —    | —     | -100 |       | $V_{GS} = -20V$  |
| $Q_G$                          | Total Gate Charge                          | —    | —     | 220  | nC    | $I_{D1} = 50A$   |
| $Q_{GS}$                       | Gate-to-Source Charge                      | —    | —     | 50   |       | $V_{DS} = 125V$  |
| $Q_{GD}$                       | Gate-to-Drain ('Miller') Charge            | —    | —     | 70   |       | $V_{GS} = 12V$   |
| $t_{d(on)}$                    | Turn-On Delay Time                         | —    | —     | 50   | ns    | $I_{D1} = 50A^{**}$<br>$V_{DD} = 125V$<br>$R_G = 2.35\Omega$<br>$V_{GS} = 12V$ |
| $t_r$                          | Rise Time                                  | —    | —     | 150  |       |  |
| $t_{d(off)}$                   | Turn-Off Delay Time                        | —    | —     | 100  |       |  |
| $t_f$                          | Fall Time                                  | —    | —     | 50   |       |  |
| $L_s + L_D$                    | Total Inductance                           | —    | 2.8   | —    | nH    | Measured from center of Drain pad to center of Source pad                      |
| $C_{iss}$                      | Input Capacitance                          | —    | 6912  | —    | pF    | $V_{GS} = 0V$  |
| $C_{oss}$                      | Output Capacitance                         | —    | 940   | —    |       | $V_{DS} = 25V$   |
| $C_{rss}$                      | Reverse Transfer Capacitance               | —    | 10.8  | —    |       | $f = 1.0MHz$   |
| $R_G$                          | Gate Resistance                            | —    | 0.52  | —    | Ω     | $f = 1.0MHz, \text{open drain}$  |

\*\* Switching speed maximum limits are based on manufacturing test equipment and capability.

<sup>1</sup> Pulse width ≤ 300 μs; Duty Cycle ≤ 2%

**Device Characteristics**

**2.2 Source-Drain Diode Ratings and Characteristics (Pre-Irradiation)**

**Table 4 Source-Drain Diode Characteristics**

| Symbol   | Parameter                                       | Min.  | Typ. | Max. | Unit          | Test Conditions   |
|----------|---|---|------|------|---------------|---|
| $I_S$    | Continuous Source Current (Body Diode)          | —   | —    | 50   | A             |   |
| $I_{SM}$ | Pulsed Source Current (Body Diode) <sup>1</sup> | —   | —    | 200  | A             |   |
| $V_{SD}$ | Diode Forward Voltage                           | —   | —    | 1.2  | V             | $T_J = 25^\circ\text{C}$ , $I_S = 50\text{A}$ , $V_{GS} = 0\text{V}$ <sup>2</sup> |
| $t_{rr}$ | Reverse Recovery Time                           | —   | —    | 700  | ns            | $T_J = 25^\circ\text{C}$ , $I_F = 50\text{A}$ , $V_{DD} \leq 25\text{V}$          |
| $Q_{rr}$ | Reverse Recovery Charge                         | —   | —    | 15   | $\mu\text{C}$ | $di/dt = 100\text{A}/\mu\text{s}$ <sup>2</sup>                                    |
| $t_{on}$ | Forward Turn-On Time                            | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S+L_D$ ) |      |      |               |   |

**2.3 Thermal Characteristics**

**Table 5 Thermal Resistance**

| Symbol             | Parameter  | Min. | Typ. | Max. | Unit                      |
|--------------------|--|------|------|------|---------------------------|
| $R_{\theta JC}$    | Junction-to-Case   | —    | —    | 0.5  | $^\circ\text{C}/\text{W}$ |
| $R_{\theta J-PCB}$ | Junction-to-PC Board (Soldered to 2" sq copper clad board) | —    | 1.6  | —    |                           |

**2.4 Radiation Characteristics**

IR HiRel radiation hardened MOSFETs are tested to verify their radiation hardness capability. The hardness assurance program at IR HiRel is comprised of two radiation environments. Every manufacturing lot is tested for total ionizing dose (per notes 3 and 4) using the TO-3 package. Both pre- and post-irradiation performance are tested and specified using the same drive circuitry and test conditions in order to provide a direct comparison.

**2.4.1 Electrical Characteristics — Post Total Dose Irradiation**

**Table 6 Electrical Characteristics @  $T_J = 25^\circ\text{C}$ , Post Total Dose Irradiation<sup>3, 4</sup>**

| Symbol       | Parameter   | Up to 300 krad (Si) <sup>5</sup> |      | Unit          | Test Conditions                                 |
|--------------|---|----------------------------------|------|---------------|---|
|              |   | Min.                             | Max. |               |   |
| $BV_{DSS}$   | Drain-to-Source Breakdown Voltage                               | 250                              | —    | V             | $V_{GS} = 0\text{V}$ , $I_D = 1.0\text{mA}$     |
| $V_{GS(th)}$ | Gate Threshold Voltage  | 2.0                              | 4.0  | V             | $V_{DS} = V_{GS}$ , $I_D = 1.0\text{mA}$        |
| $I_{GSS}$    | Gate-to-Source Leakage Forward                                  | —                                | 100  | nA            | $V_{GS} = 20\text{V}$                           |
|              | Gate-to-Source Leakage Reverse                                  | —                                | -100 |               | $V_{GS} = -20\text{V}$                          |
| $I_{DSS}$    | Zero Gate Voltage Drain Current                                 | —                                | 10   | $\mu\text{A}$ | $V_{DS} = 200\text{V}$ , $V_{GS} = 0\text{V}$   |
| $R_{DS(on)}$ | Static Drain-to-Source On-State Resistance (TO-3) <sup>2</sup>  | —                                | 41   | m $\Omega$    | $V_{GS} = 12\text{V}$ , $I_{D2} = 31.5\text{A}$ |
| $R_{DS(on)}$ | Static Drain-to-Source On-State Resistance (SMD-2) <sup>2</sup> | —                                | 40   | m $\Omega$    | $V_{GS} = 12\text{V}$ , $I_{D2} = 31.5\text{A}$ |
| $V_{SD}$     | Diode Forward Voltage   | —                                | 1.2  | V             | $V_{GS} = 0\text{V}$ , $I_F = 50\text{A}$       |

<sup>1</sup> Repetitive Rating; Pulse width limited by maximum junction temperature.

<sup>2</sup> Pulse width  $\leq 300 \mu\text{s}$ ; Duty Cycle  $\leq 2\%$

<sup>3</sup> Total Dose Irradiation with  $V_{GS}$  Bias.  $V_{GS} = 12\text{V}$  applied and  $V_{DS} = 0$  during irradiation per MIL-STD-750, Method 1019, condition A.

<sup>4</sup> Total Dose Irradiation with  $V_{DS}$  Bias.  $V_{DS} = 200\text{V}$  applied and  $V_{GS} = 0$  during irradiation per MIL-STD-750, Method 1019, condition A.

<sup>5</sup> Part numbers IRHNA67264 (JANSR2N7585U2) and IRHNA63264 (JANSR2F7585U2)


**Device Characteristics**

**2.4.2 Single Event Effects — Safe Operating Area**

IR HiRel radiation hardened MOSFETs have been characterized in heavy ion environment for Single Event Effects (SEE). Single Event Effects characterization is illustrated in Fig. 1 and Table 7.

**Table 7 Typical Single Event Effects Safe Operating Area**


| LET<br>(MeV·cm <sup>2</sup> /mg) | Energy<br>(MeV) | Range<br>(μm) | V <sub>DS</sub> (V)  |                       |                        |                        |                        |
|----------------------------------|-----------------|---------------|----------------------|-----------------------|------------------------|------------------------|------------------------|
|                                  |                 |               | V <sub>GS</sub> = 0V | V <sub>GS</sub> = -5V | V <sub>GS</sub> = -10V | V <sub>GS</sub> = -15V | V <sub>GS</sub> = -20V |
| 50 ± 5%                          | 821 ± 5%        | 74.2 ± 5%     | 250                  | 250                   | 250                    | 250                    | 40                     |
| 59 ± 5%                          | 1040 ± 5%       | 79.7 ± 5%     | 225                  | 225                   | 225                    | 50                     | —                      |
| 85 ± 5%                          | 1908 ± 5%       | 101.2 ± 5%    | 75                   | 75                    | —                      | —                      | —                      |




**Figure 1 Typical Single Event Effect, Safe Operating Area**

**IRHNA67264 (JANSR2N7585U2)**  
**Radiation Hardened Power MOSFET (SMD-2)**  
**Electrical Characteristics Curves (Pre-irradiation)**


**3 Electrical Characteristics Curves (Pre-irradiation)**




**Figure 2 Typical Output Characteristics**



**Figure 3 Typical Output Characteristics**




**Figure 4 Typical Transfer Characteristics**




**Figure 5 Normalized On-Resistance Vs. Temperature**


**IRHNA67264 (JANSR2N7585U2)**  
**Radiation Hardened Power MOSFET (SMD-2)**  
**Electrical Characteristics Curves (Pre-irradiation)**




**Figure 6 Typical On-Resistance Vs Gate Voltage**



**Figure 7 Typical On-Resistance Vs Drain Current**




**Figure 8 Typical Drain-to-Source Breakdown Voltage Vs. Temperature**




**Figure 9 Typical Gate-to-Source Voltage Vs. Temperature**




**IRHNA67264 (JANSR2N7585U2)**  
**Radiation Hardened Power MOSFET (SMD-2)**  
**Electrical Characteristics Curves (Pre-irradiation)**




**Figure 10 Typical Capacitance Vs. Drain-to-Source Voltage**



**Figure 11 Gate-to-Source Voltage Vs. Typical Gate Charge**




**Figure 12 Typical Source-Drain Current Vs. Diode Forward Voltage**




**Figure 13 Maximum Drain Current Vs. Temperature**


**IRHNA67264 (JANSR2N7585U2)**  
**Radiation Hardened Power MOSFET (SMD-2)**  
**Electrical Characteristics Curves (Pre-irradiation)**



**Figure 14 Maximum Safe Operating Area**



**Figure 15 Maximum Avalanche Energy Vs. Junction Temperature**




**Figure 16 Maximum Effective Transient Thermal Impedance, Junction-to-Case**


**IRHNA67264 (JANSR2N7585U2)**  
**Radiation Hardened Power MOSFET (SMD-2)**

**Test Circuits (Pre-irradiation)**


**4 Test Circuits (Pre-irradiation)**




**Figure 17 Gate Charge Test Circuit**




**Figure 18 Gate Charge Waveform**




**Figure 19 Unclamped Inductive Test Circuit**



**Figure 20 Unclamped Inductive Waveform**



**Figure 21 Switching Time Test Circuit**




**Figure 22 Switching Time Waveforms**

**Package Outline**

**5 Package Outline**

**Note: For the most updated package outline, please see the website: [SMD-2](#)**



**IRHNA67264 (JANSR2N7585U2)**  
**Radiation Hardened Power MOSFET (SMD-2)**

**Revision history**

**Revision history**

| <b>Document version</b> | <b>Date of release</b> | <b>Description of changes</b>             |
|-------------------------|------------------------|---|
|                         | 06/28/2005             | Final datasheet with PD number (PD-96990) |
| Rev A                   | 12/22/2011             | Updated based on ECN-18135                |
| Rev B                   | 04/28/2017             | Updated based on ECN-1120_05333           |
| Rev C                   | 10/30/2018             | Updated based on ECN-1120_06367-3         |
| Rev D                   | 11/09/2020             | Updated based on ECN-1120_08235           |
| Rev E                   | 03/07/2022             | Updated based on ECN-1120_08906           |

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2022-03-07**

### Published by

**International Rectifier HiRel Products,  
Inc.**

**An Infineon Technologies company  
El Segundo, California 90245 USA**

**© 2022 Infineon Technologies AG.  
All Rights Reserved.**

**Do you have a question about this  
document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

## WARNINGS

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest International Rectifier HiRel Products, Inc., an Infineon Technologies company, office.

International Rectifier HiRel Components may only be used in life-support devices or systems with the expressed written approval of International Rectifier HiRel Products, Inc., an Infineon Technologies company, if failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety and effectiveness of that device or system.

Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.