

# IRHNA9064 (JANSR2N7424U)

PD-91447D

## Radiation Hardened Power MOSFET Surface Mount (SMD-2) -60V, P-channel, Rad Hard HEXFET™ Technology

### Features

- Single event effect (SEE) hardened
- Low  $R_{DS(on)}$
- Low total gate charge
- Proton tolerant
- Simple drive requirements
- Hermetically sealed
- Surface mount
- Light weight
- ESD rating: Class 3A per MIL-STD-750, Method 1020

### Product Summary

- $BV_{DSS}$ : -60V
- $I_D$ : -48A
- $R_{DS(on),max}$ : 45 mΩ
- $Q_{G,max}$ : 300nC
- **REF:** MIL-PRF-19500/655



### Potential Applications

- DC-DC converter
- Motor drives
- Electric propulsion

### Product Validation

Qualified to JANS screening flow according to MIL-PRF-19500 for space applications

### Description

IR HiRel rad hard HEXFET technology provides high performance power MOSFETs for space applications. This technology has over a decade of proven performance and reliability in satellite applications. These devices have been characterized for both Total Dose and Single Event Effects (SEE). The combination of low  $R_{DS(on)}$  and low gate charge reduces the power losses in switching applications such as DC to DC converters and motor control. These devices retain all of the well established advantages of MOSFETs such as voltage control, fast switching and temperature stability of electrical parameters.

### Ordering Information

**Table 1** Ordering options

Part number	Package	Screening Level	TID Level
IRHNA9064	SMD-2	COTS	100krad(Si)
JANSR2N7424U	SMD-2	JANS	100krad(Si)
JANTXVR2N7424U	SMD-2	JANTX	100krad(Si)
IRHNA93064	SMD-2	COTS	300krad(Si)
JANSF2N7424U	SMD-2	JANS	300krad(Si)

## Table of contents

## Table of contents

<b>Features .....</b>	<b>1</b>
<b>Potential Applications.....</b>	<b>1</b>
<b>Product Validation.....</b>	<b>1</b>
<b>Description .....</b>	<b>1</b>
<b>Ordering Information.....</b>	<b>1</b>
<b>Table of contents.....</b>	<b>2</b>
<b>1 Absolute Maximum Ratings .....</b>	<b>3</b>
<b>2 Device Characteristics .....</b>	<b>4</b>
2.1 Electrical Characteristics (Pre-Irradiation).....	4
2.2 Source-Drain Diode Ratings and Characteristics (Pre-Irradiation) .....	5
2.3 Thermal Characteristics .....	5
2.4 Radiation Characteristics.....	5
2.4.1 Electrical Characteristics — Post Total Dose Irradiation .....	5
2.4.2 Single Event Effects — Safe Operating Area .....	6
<b>3 Electrical Characteristics Curves (Pre-irradiation) .....</b>	<b>7</b>
<b>4 Test Circuits (Pre-irradiation) .....</b>	<b>10</b>
<b>5 Package Outline.....</b>	<b>11</b>
<b>Revision history.....</b>	<b>12</b>

## Absolute Maximum Ratings

## 1 Absolute Maximum Ratings

Table 2 Absolute Maximum Ratings (Pre-Irradiation)

Symbol	Parameter	Value	Unit
$I_{D1} @ V_{GS} = -12V, T_C = 25^{\circ}C$	Continuous Drain Current	-48	A
$I_{D2} @ V_{GS} = -12V, T_C = 100^{\circ}C$	Continuous Drain Current	-30	A
$I_{DM} @ T_C = 25^{\circ}C$	Pulsed Drain Current <sup>1</sup>	-192	A
$P_D @ T_C = 25^{\circ}C$	Maximum Power Dissipation	300	W
	Linear Derating Factor	2.4	W/ $^{\circ}C$
$V_{GS}$	Gate-to-Source Voltage	$\pm 20$	V
$E_{AS}$	Single Pulse Avalanche Energy <sup>2</sup>	500	mJ
$I_{AR}$	Avalanche Current <sup>1</sup>	-48	A
$E_{AR}$	Repetitive Avalanche Energy <sup>1</sup>	30	mJ
$dv/dt$	Peak Diode Reverse Recovery <sup>3</sup>	-4.4	V/ns
$T_J$ $T_{STG}$	Operating Junction and Storage Temperature Range	-55 to +150	$^{\circ}C$
	Package Mounting Surface Temperature	300 (for 5sec)	
	Weight	3.3 (Typical)	g

<sup>1</sup> Repetitive Rating; Pulse width limited by maximum junction temperature.<sup>2</sup>  $V_{DD} = -25V$ , starting  $T_J = 25^{\circ}C$ ,  $L = 0.43mH$ , Peak  $I_L = -48A$ ,  $V_{GS} = -12V$ <sup>3</sup>  $I_{SD} \leq -48A$ ,  $di/dt \leq -150A/\mu s$ ,  $V_{DD} \leq -60V$ ,  $T_J \leq 150^{\circ}C$

## Device Characteristics

## 2 Device Characteristics

## 2.1 Electrical Characteristics (Pre-Irradiation)

Table 3 Static and Dynamic Electrical Characteristics @  $T_j = 25^\circ\text{C}$  (Unless Otherwise Specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
$BV_{DSS}$	Drain-to-Source Breakdown Voltage	-60	—	—	V	$V_{GS} = 0V, I_D = -1.0mA$
$\Delta BV_{DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	—	-0.055	—	V/ $^\circ\text{C}$	Reference to $25^\circ\text{C}$ , $I_D = -1.0mA$
$R_{DS(on)}$	Static Drain-to-Source On-State Resistance	—	—	0.045	$\Omega$	$V_{GS} = -12V, I_{D2} = -30A^1$
		—	—	0.048		$V_{GS} = -12V, I_{D1} = -48A^1$
$V_{GS(th)}$	Gate Threshold Voltage	-2.0	—	-4.0	V	$V_{DS} = V_{GS}, I_D = -1.0mA$
$G_{fs}$	Forward Transconductance	18	—	—	S	$V_{DS} = -15V, I_{D2} = -30A^1$
$I_{DSS}$	Zero Gate Voltage Drain Current	—	—	-25	$\mu A$	$V_{DS} = -48V, V_{GS} = 0V$
		—	—	-250		$V_{DS} = -48V, V_{GS} = 0V, T_J = 125^\circ\text{C}$
$I_{GSS}$	Gate-to-Source Leakage Forward	—	—	-100	nA	$V_{GS} = -20V$
	Gate-to-Source Leakage Reverse	—	—	100		$V_{GS} = 20V$
$Q_G$	Total Gate Charge	—	—	300	nC	$I_{D1} = -48A$
$Q_{GS}$	Gate-to-Source Charge	—	—	70		$V_{DS} = -30V$
$Q_{GD}$	Gate-to-Drain ('Miller') Charge	—	—	91		$V_{GS} = -12V$
$t_{d(on)}$	Turn-On Delay Time	—	—	35	ns	$I_{D1} = -48A^{**}$ $V_{DD} = -30V$ $R_G = 2.35\Omega$ $V_{GS} = -12V$
$t_r$	Rise Time	—	—	150		
$t_{d(off)}$	Turn-Off Delay Time	—	—	200		
$t_f$	Fall Time	—	—	200		
$L_s + L_D$	Total Inductance	—	4.0	—	nH	Measured from Drain lead (6mm / 0.25 in from package) to Source lead (6mm/ 0.25 in from package) with Source wire internally bonded from Source pin to Drain pad
$C_{iss}$	Input Capacitance	—	6700	—	pF	$V_{GS} = 0V$ $V_{DS} = -25V$ $f = 1.0MHz$
$C_{oss}$	Output Capacitance	—	2800	—		
$C_{rss}$	Reverse Transfer Capacitance	—	920	—		

\*\* Switching speed maximum limits are based on manufacturing test equipment and capability.

<sup>1</sup> Pulse width  $\leq 300 \mu s$ ; Duty Cycle  $\leq 2\%$

## Device Characteristics

## 2.2 Source-Drain Diode Ratings and Characteristics (Pre-Irradiation)

Table 4 Source-Drain Diode Characteristics

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
I <sub>S</sub>	Continuous Source Current (Body Diode)	—	—	-48	A	
I <sub>SM</sub>	Pulsed Source Current (Body Diode) <sup>1</sup>	—	—	-192	A	
V <sub>SD</sub>	Diode Forward Voltage	—	—	-3.0	V	T <sub>J</sub> = 25°C, I <sub>S</sub> = -48A, V <sub>GS</sub> = 0V <sup>2</sup>
t <sub>rr</sub>	Reverse Recovery Time	—	—	270	ns	T <sub>J</sub> = 25°C, I <sub>F</sub> = -48A, V <sub>DD</sub> ≤ -50V di/dt = -100A/μs <sup>2</sup>
Q <sub>rr</sub>	Reverse Recovery Charge	—	1.7	—	μC	
t <sub>on</sub>	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by L <sub>S</sub> +L <sub>D</sub> )				

## 2.3 Thermal Characteristics

Table 5 Thermal Resistance

Symbol	Parameter	Min.	Typ.	Max.	Unit
$R_{\theta JC}$	Junction-to-Case	—	—	0.42	$^\circ\text{C}/\text{W}$
$R_{\theta J-PCB}$	Junction-to-PC board (Soldered to a 1" sq. copper-clad board)	—	1.6	—	

## 2.4 Radiation Characteristics

IR HiRel Radiation Hardened MOSFETs are tested to verify their radiation hardness capability. The hardness assurance program at IR HiRel is comprised of two radiation environments. Every manufacturing lot is tested for total ionizing dose (per notes 3 and 4) using the TO-3 package. Both pre- and post-irradiation performance are tested and specified using the same drive circuitry and test conditions in order to provide a direct comparison.

## 2.4.1 Electrical Characteristics — Post Total Dose Irradiation

Table 6 Electrical Characteristics @  $T_J = 25^\circ\text{C}$ , Post Total Dose Irradiation <sup>3, 4</sup>

Symbol	Parameter	100krad (Si) <sup>5</sup>		300krad (Si) <sup>6</sup>		Unit	Test Conditions
		Min.	Max.	Min.	Max.		
$BV_{DSS}$	Drain-to-Source Breakdown Voltage	-60	—	-60	—	V	$V_{GS} = 0\text{V}$ , $I_D = -1.0\text{mA}$
$V_{GS(th)}$	Gate Threshold Voltage	-2.0	-4.0	-2.0	-5.0	V	$V_{DS} = V_{GS}$ , $I_D = -1.0\text{mA}$
$I_{GSS}$	Gate-to-Source Leakage Forward	—	-100	—	-100	nA	$V_{GS} = -20\text{V}$
	Gate-to-Source Leakage Reverse	—	100	—	-100		$V_{GS} = 20\text{V}$
$I_{DSS}$	Zero Gate Voltage Drain Current	—	-25	—	-25	$\mu\text{A}$	$V_{DS} = -48\text{V}$ , $V_{GS} = 0\text{V}$
$R_{DS(on)}$	Static Drain-to-Source On-State Resistance (TO-3) <sup>2</sup>	—	0.045	—	0.045	$\Omega$	$V_{GS} = -12\text{V}$ , $I_{D2} = -30\text{A}$
$R_{DS(on)}$	Static Drain-to-Source On-State Resistance (SMD-2) <sup>2</sup>	—	0.045	—	0.045	$\Omega$	$V_{GS} = -12\text{V}$ , $I_{D2} = -30\text{A}$
$V_{SD}$	Diode Forward Voltage	—	-3.0	—	-3.0	V	$V_{GS} = 0\text{V}$ , $I_F = -48\text{A}$

<sup>1</sup> Repetitive Rating; Pulse width limited by maximum junction temperature.

<sup>2</sup> Pulse width  $\leq 300 \mu\text{s}$ ; Duty Cycle  $\leq 2\%$ 
<sup>3</sup> Total Dose Irradiation with  $V_{GS}$  Bias.  $V_{GS} = -12\text{V}$  applied and  $V_{DS} = 0$  during irradiation per MIL-STD-750, Method 1019, condition A.

<sup>4</sup> Total Dose Irradiation with  $V_{DS}$  Bias.  $V_{DS} = -48\text{V}$  applied and  $V_{GS} = 0$  during irradiation per MIL-STD-750, Method 1019, condition A.

<sup>5</sup> Part number(s): IRHNA9064 (JANSR2N7424U)

<sup>6</sup> Part numbers(s): IRHNA93064 (JANSF2N7424U)

**IRHNA9064 (JANSR2N7424U)**

**Radiation Hardened Power MOSFET Surface Mount (SMD-2)**


**Device Characteristics**

**2.4.2 Single Event Effects — Safe Operating Area**

IR HiRel radiation hardened MOSFETs have been characterized in heavy ion environment for Single Event Effects (SEE). Single Event Effects characterization is illustrated in Fig. 1 and Table 7.

**Table 7 Typical Single Event Effects Safe Operating Area**

Ion	LET (MeV/(mg/cm <sup>2</sup> ))	Energy (MeV)	Range (μm)	V <sub>DS</sub> (V)				
				V <sub>GS</sub> = 0V	V <sub>GS</sub> = 5V	V <sub>GS</sub> = 10V	V <sub>GS</sub> = 15V	V <sub>GS</sub> = 20V
Cu	28	285	43	-60	-60	-50	-35	—
Br	36.8	305	39	-55	-45	-35	-30	—
I	59.9	345	32.8	-40	-35	—	—	—



**Figure 1 Typical Single Event Effect, Safe Operating Area**

# IRHNA9064 (JANSR2N7424U)

## Radiation Hardened Power MOSFET Surface Mount (SMD-2)

### Electrical Characteristics Curves (Pre-irradiation)

### 3 Electrical Characteristics Curves (Pre-irradiation)




Figure 2 Typical Output Characteristics




Figure 3 Typical Output Characteristics




Figure 4 Typical Transfer Characteristics





Figure 5 Normalized On-Resistance Vs. Temperature


# IRHNA9064 (JANSR2N7424U)

## Radiation Hardened Power MOSFET Surface Mount (SMD-2)


### Electrical Characteristics Curves (Pre-irradiation)




**Figure 6** Typical Capacitance Vs. Drain-to-Source Voltage



**Figure 7** Gate-to-Source Voltage Vs. Typical Gate Charge



**Figure 8** Typical Source-Drain Current Vs. Diode Forward Voltage




**Figure 9** Maximum Safe Operating Area



# IRHNA9064 (JANSR2N7424U)


## Radiation Hardened Power MOSFET Surface Mount (SMD-2)

### Electrical Characteristics Curves (Pre-irradiation)



**Figure 10** Maximum Drain Current Vs. Case Temperature

**Figure 11** Maximum Avalanche Energy Vs. Junction Temperature




**Figure 12** Maximum Effective Transient Thermal Impedance, Junction-to-Case

# IRHNA9064 (JANSR2N7424U)


## Radiation Hardened Power MOSFET Surface Mount (SMD-2)

### Test Circuits (Pre-irradiation)


## 4 Test Circuits (Pre-irradiation)




**Figure 13 Gate Charge Test Circuit**




**Figure 14 Gate Charge Waveform**




**Figure 15 Unclamped Inductive Test Circuit**



**Figure 16 Unclamped Inductive Waveform**



**Figure 17 Switching Time Test Circuit**



**Figure 18 Switching Time Waveforms**


# IRHNA9064 (JANSR2N7424U)

## Radiation Hardened Power MOSFET Surface Mount (SMD-2)

### Package Outline

## 5 Package Outline

**Note:** For the most updated package outline, please see the website: [SMD-2](#)



**Revision history****Revision history**

Document version	Date of release	Description of changes
Rev A	08/25/1998	Datasheet (PD-91447A)
Rev B	01/14/2001	Updated Switching test condition $V_{GS} = 12V$ -page2
Rev C	02/18/2003	Updated typo $V_{GS} = 12V$ to $V_{GS} = -12V$
Rev D	05/27/2025	Updated based on ECN-Z8F80792255

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2025-05-27**

**Published by**

**International Rectifier HiRel Products,  
Inc.**

**An Infineon Technologies company  
El Segundo, California 90245 USA**

**© 2025 Infineon Technologies AG.  
All Rights Reserved.**

**Do you have a question about this  
document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

## WARNINGS

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest International Rectifier HiRel Products, Inc., an Infineon Technologies company, office.

International Rectifier HiRel Components may only be used in life-support devices or systems with the expressed written approval of International Rectifier HiRel Products, Inc., an Infineon Technologies company, if failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety and effectiveness of that device or system.

Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.