

BGSA406MN10

Ultra high RF voltage antenna tuning switch

Features

- Low R_{ON} resistance of $2.0\ \Omega$ at each port in ON state
- Low C_{OFF} capacitance of 110 fF at each port in OFF state
- High RF operating peak voltage handling of typical 80 V in OFF state
- MIPI RFFE 2.1 control interface
- Extremely fast switching time of typical $1.2\ \mu\text{s}$
- Single V_{IO} supply supporting both 1.2 V and 1.8 V
- 4 default USID addresses via external USID_SEL pin
- Extremely low current consumption of $20\ \mu\text{A}$ in ACTIVE mode
- Small form factor $0.95\ \text{mm} \times 1.3\ \text{mm}$ (MSL1, $260\ ^\circ\text{C}$ per JEDEC J-STD-020)



Potential applications

- Impedance, antenna and inductance tuning
- Tunable filters



Product validations

- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22.

Description

The BGSA406MN10 is a versatile shunt to ground 4xsingle-pole single-throw (4xSPST) RF antenna tuning switch. It is optimized for low C_{OFF} as well as low R_{ON} enabling applications up to 7.125 GHz. The BGSA406MN10 is ideal for antenna tuning application. This chip integrates on-chip CMOS logic and power supply regulation. Its digital control interface is compliant with MIPI2.1 RFFE specification and each switch throw can be programmed individually or all together in the same RFFE command frame. Up to 4 instantiations of the same device can be controlled using the same RFFE bus thanks to its 4 states USID_SEL pin unique feature.

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Ultra high RF voltage antenna tuning switch

Block diagram and ordering information




Figure 1 BGS4149M2MN10 Block diagram

Table 1 Ordering Information

Type	Marking	Package	Product name
BGS406MN10	A6	TSNP-10-9	BGS4 406MN10 E6327

The full datasheet for this product is available under NDA. For more technical information, please contact our Technical Assistance Center or your local Infineon representative.

Edition 2026-09-03

Published by
Infineon Technologies AG
81726 München, Germany

© 2026 Infineon Technologies AG.
All Rights Reserved.

Do you have a question about this document?
Email: erratum@infineon.com

Document reference: xxx

IMPORTANT NOTICE

Products which may also include samples and may be comprised of hardware or software or both ("Product(s)") are sold or provided and delivered by Infineon Technologies AG and its affiliates ("Infineon") subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

For the avoidance of doubt, Infineon disclaims all warranties of non-infringement of third-party rights and implied warranties such as warranties of fitness for a specific use/purpose or merchantability. Infineon shall not be responsible for any information with respect to samples, the application or customer's specific use of any Product or for any examples or typical values given in this document.

If this document is marked as 'Preliminary', 'Target', 'Draft' or 'Proposal', Infineon reserves the right to change all information given in this document at any time without notice. Subject to the development and release of a Product for series supply by Infineon, the technical specifications of the Product are set forth in the relevant datasheet provided by Infineon without such marking.

The data contained in this document is exclusively intended for technically qualified and skilled customer representatives. It is the responsibility of the customer to evaluate the suitability of the Product for the intended application and the customer's specific use and to verify all relevant technical data contained in this document in the intended application and the customer's specific use. The customer is responsible for properly designing, programming, and testing the functionality and safety of the intended application, as well as complying with any legal requirements related to its use.

Unless otherwise explicitly approved by Infineon, Products may not be used in any application where a failure of the Products or any consequences of the use thereof can reasonably be expected to result in personal injury.

However, the foregoing shall not prevent the customer from using any Product in such fields of use that Infineon has explicitly designed and sold it for, provided that the overall responsibility for the application lies with the customer. Infineon expressly reserves the right to use its content for commercial text and data mining (TDM) according to applicable laws, e.g. Section 44b of the German Copyright Act (UrhG).

If the Product includes security features:

Because no computing device can be absolutely secure, and despite security measures implemented in the Product, Infineon does not guarantee that the Product will be free from intrusion, data theft or loss, or other breaches ("Security Breaches"), and Infineon shall have no liability arising out of any Security Breaches.

If this document includes or references software:

The software is owned by Infineon under the intellectual property laws and treaties of the United States, Germany, and other countries worldwide. All rights reserved. Therefore, you may use the software only as provided in the software license agreement accompanying the software.

If no software license agreement applies, Infineon hereby grants you a personal, non-exclusive, non-transferable license (without the right to sublicense) under its intellectual property rights in the software (a) for software provided in source code form, to modify and reproduce the software solely for use with Infineon hardware products, only internally within your organization, and (b) to distribute the software in binary code form externally to end users, solely for use on Infineon hardware products. Any other use, reproduction, modification, translation, or compilation of the software is prohibited.

For further information on the Product, technology, delivery terms and conditions, and prices, please contact your nearest Infineon office or visit

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).