

12-phase Dual Loop Voltage Regulator

Features

- Digital controller assisted with high performance analog front ends with a fully programmable ARM® Cortex™ –M0 Processor
- Compliant with Intel™ VR13, VR13HC, and VR14 Server VR Vendor PWM Enabling Specification Rev 1.88 (October 2021)
- Compliant with Intel™ VR14.Cloud Rev 1.06 (Jan 2025) Advanced Telemetry Level 2 and Security Level 2
- Compliant with Intel™ IMVP9.1/9.2 VR Vendor PWM Enabling Specification Rev 1.0 (May 2023)
- Compliant with Intel™ SVID Protocol Spec Rev 1.95 (June 2023)
- Compliant with PMBus Rev 1.4 (January 2022) serial interface
 - Query voltage, current, temperature faults
 - Fault Response
 - Maximum supported bus speed 1 MHz
 - Support 1.8/3.3 V operation
 - Support PAGE_PLUS_WRITE/PAGE_PLUS_READ
- Compliant with PMBus Part III - AVSBus Rev 1.4 (January 2022)
- Compliant with PMBus Level 2 Secure Device Specification Rev 2.02 (May 2023)
- Output voltage regulation range
 - 0.25 V to 1.52 V (5 mV/step)
 - 0.5 V to 3.04 V (10 mV/step)
 - 0.05 V to 3.1 V (1 mV/step)
- Digitally controlled phasing for full flexibility in both loop configuration and phase firing order
- Digital current emulation for TLVR inductor support
- Configurable autonomous phase add/drop
- Automatic phase detection at start-up
- Supports start-up into pre-bias voltage
- Integrated power stage current sense
- Differential output voltage sense
- Fast current balancing with current-mode control
- Digitally programmable PID (Proportional, Integral, Differential) loop compensation
- Digitally programmable loadline slope
- Digital temperature compensation
- Direct input (+12 V) voltage and current sense
- Extensive fault detection and protection capability
 - IUVP, OUVF & OOVF (fixed and tracking)
 - OCP instantaneous (total current)
 - Multiple OTP thresholds
 - Peak phase current pulse limiting
 - Negative current limit protection
 - TLVR secondary Open/Short detection
 - Blackbox recording before system shutdown
- Internal non-volatile memory (NVM) to store multiple custom configurations
- RoHS compliant and Halogen free 48-lead QFN plastic package

XDPE1C2C4A Short

12-phase Dual Loop Voltage Regulator

Potential applications

Potential applications

- Vcore power regulation for Intel™ VR13, VR13HC, VR14 based Microprocessors in server, workstations and high-end desktop applications.
- High Current ASIC, PMBus POLs in AI server and telecom applications

Product validation

Qualified for industrial applications according to the relevant tests of JEDEC47/20/22/78

Description

This XDPE digital dual loop 12 phase controller provides power for AI server, telecom, Intel™ VR13, VR13HC, VR14 server, workstation, and high-end desktop applications that use AVS bus. Voltage on either the first loop or the second loop is provided by a multi-phase buck converter with up to 12 synchronous-rectified channels. The controller's phase configuration is flexible in how the phases are allocated to the 2 loops. Any phase can be assigned to either loop and the phase firing order is fully programmable to offer the ultimate in phase configuration flexibility. Typically, configurations of 12+0, 11+1... 0+12 phases are supported.

Command and monitoring functions are controlled through the PMBus, AVS and SVID interfaces which supports dynamic voltage identification with 1mV/step in AVS mode or 5 mV/step or 10 mV/step in Intel mode, output range up to 3.1 V, offset and trim resolution of 625 uV and accuracy better than 0.5%.

The controller utilizes digital technology to implement all control functions, providing the ultimate system solution in terms of flexibility and stability. Advanced control loop features, such as current mode control, variable frequency operation, Active Transient Response (ATR/FATR), fast DVID response, automatic phase shedding and Pulse Frequency Modulation (PFM) enable optimal response to a highly dynamic load with fast di/dt load transients across a wide range of load current.

The controller supports multi-vendor pin compatible integrated power stages with trivalent PWM interfaces, fast response, integrated current sense, integrated temperature sense, and advanced fault detection capability, interface and signaling.

In addition to supporting power stage fault protection features, the controller also includes a set of sophisticated over-voltage, under-voltage, over-temperature, over-current, and phase fault protections. These attributes provide a complete and advanced protection feature set for microprocessor and power systems.

Table 1 Part number and package summary

Part Number	Package
XDPE1C2C4A	48-lead 6 mm x 6 mm QFN PG-VQFN-48


1 Ordering information

Table 2 **Ordering information**

Base Part Number	Package Type	Form	Quantity	Orderable Part Number	Note
XDPE1C2C4A	QFN 6 mm x 6 mm	Tape and Reel	4000	XDPE1C2C4A0000 XTMA1	Standard Part Number with default configuration
				XDPE1C2C4Axyz XTMA1	Customer Specific Part Number, where x=Firmware ID, and yzz=Customer Config File ID (Codes assigned by Product Marketing)

1.1 Sample programming

The customer can program the parts to their specific system requirements using software/hardware available from Infineon or through other controller programming 3rd Parties (contact Infineon for recommendations). Infineon Field Application Engineers are available to assist with system and configuration file optimization and programming of the controllers. Alternatively, samples can be ordered with a customer specific configuration pre-programmed at the factory, but lead times for these types of samples are significantly longer than for standard default configuration samples. The generic part numbering format is shown below:


Figure 1 **Part number decoding**

XDPE1C2C4A Short

12-phase Dual Loop Voltage Regulator

1 Ordering information




Figure 2 Package top view

2 Package marking




Figure 3 Package marking



3 Environmental qualifications

Table 3 Environmental qualifications

Qualification Level		Industrial	
Moisture Sensitivity		QFN Package	MSL1
ESD	Human Body Model	JS-001 Class 2	
	Charged Device Model	JS-002, Class C3	
RoHS Compliant		Yes	

Revision history

XDPE1C2C4A Short

Revision 2026-08-04, Rev. 1.0

Previous revisions

Revision	Date	Subjects (major changes since last revision)
1.0	2026-08-04	Release of final version

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Published by Infineon Technologies AG, Am Campeon 1-15, 85579 Neubiberg, Germany
Copyright (c) 2026 Infineon Technologies AG and its affiliates. All Rights Reserved.

Important notice

Products which may also include samples and may be comprised of hardware or software or both ("Product(s)") are sold or provided and delivered by Infineon Technologies AG and its affiliates ("Infineon") subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

For the avoidance of doubt, Infineon disclaims all warranties of non-infringement of third-party rights and implied warranties such as warranties of fitness for a specific use/purpose or merchantability.

Infineon shall not be responsible for any information with respect to samples, the application or customer's specific use of any Product or for any examples or typical values given in this document.

The data contained in this document is exclusively intended for technically qualified and skilled customer representatives. It is the responsibility of the customer to evaluate the suitability of the Product for the intended application and the customer's specific use and to verify all relevant technical data contained in this document in the intended application and the customer's specific use. The customer is responsible for properly designing, programming, and testing the functionality and safety of the intended application, as well as complying with any legal requirements related to its use.

Unless otherwise explicitly approved by Infineon, Products may not be used in any application where a failure of the Products or any consequences of the use thereof can reasonably be expected to result in personal injury. However, the foregoing shall not prevent the customer from using any Product in such fields of use that Infineon has explicitly designed and sold it for, provided that the overall responsibility for the application lies with the customer.

Infineon expressly reserves the right to use its content for commercial text and data mining (TDM) according to applicable laws, e.g. Section 44b of the German Copyright Act (UrhG).

If the Product includes security features: Because no computing device can be absolutely secure, and despite security measures implemented in the Product, Infineon does not guarantee that the Product will be free from intrusion, data theft or loss, or other breaches ("Security Breaches"), and Infineon shall have no liability arising out of any Security Breaches.

If this document includes or references software:

The software is owned by Infineon under the intellectual property laws and treaties of the United States, Germany, and other countries worldwide. All rights reserved. Therefore, you may use the software only as provided in the software license agreement accompanying the software. If no software license agreement applies, Infineon hereby grants you a personal, non-exclusive, non-transferable license (without the right to sublicense) under its intellectual property rights in the software (a) for software provided in source code form, to modify and reproduce the software solely for use with Infineon hardware products, only internally within your organization, and (b) to distribute the software in binary code form externally to end users, solely for use on Infineon hardware products. Any other use, reproduction, modification, translation, or compilation of the software is prohibited.

For further information on the Product, technology, delivery terms and conditions, and prices, please contact your nearest Infineon office or visit <https://www.infineon.com>.