

## C167CR

Highly Integrated Microcontroller  
with On-Chip CAN-Module



THE C167CR<sup>1)</sup> is a new derivative of the Infineon C166 Family of full featured single-chip CMOS microcontrollers. It combines high CPU performance with high peripheral functionality and enhanced IO-capabilities.

THE C167CR features a CAN module which meets version 2.0B active of the Controller Area Network specification and was designed to fulfill the requirements of coming generations of automotive and industrial control applications

Device	ROM	CAN
C167CR-LM	–	✓
C167CR-4RM	32 Kbytes	✓
C167CR-16RM	128 Kbytes	✓
C167SR-LM	–	–

25 MHz = standard  
33 MHz = optional

### Key Features

- High Performance 16-bit CPU with 4-Stage Pipeline
- 80 ns Instruction Cycle Time at 25 MHz CPU Clock
- 400 ns Multiplication (16 x 16 bit), 800 ns Division (32/16 bit) at 25 MHz CPU Clock
- Enhanced Boolean Bit Manipulation Facilities
- Additional Instructions to Support HLL and Operating Systems
- Register-Based Design with Multiple Variable Register Banks
- Single-Cycle Context Switching Support
- Clock Generation via On-Chip PLL or via direct clock-input
- Up to 16 Mbytes Linear Address Space for Code and Data
- 4 Kbytes On-Chip SRAM (2 Kbytes Internal RAM, 2 Kbytes Extension RAM)
- Programmable External Bus Characteristics for Different Address Ranges

- 8-bit or 16-bit External Data Bus
- Multiplexed or Demultiplexed External Address/Data Buses
- Five Programmable Chip-Select Signals
- Hold- and Hold-Acknowledge Bus Arbitration Support
- 1024 Bytes On-Chip Special Function Register Area
- Idle and Power Down Modes
- 8-Channel Interrupt-Driven Single-Cycle Data Transfer Facilities via Peripheral Event Controller (PEC)
- 16-Priority-Level Interrupt System with 56 Sources, Sample-Rate down to 40 ns
- 16-Channel 10-bit A/D Converter with 7.76 µs at 25 MHz Conversion Time
- Two 16-Channel Capture/Compare Units
- 4-Channel PWM Unit
- Two Multi-Functional General Purpose Timer Units with five 16-bit Timers
- Two Serial Channels (Synchronous/Asynchronous and High-Speed-Synchronous, 6 Mbit/s at 25 MHz)
- On-Chip CAN Interface 2.0B active with 15 Message Objects (Full-CAN/Basic-CAN)
- Programmable Watchdog Timer
- Up to 111 General Purpose IO Lines, partly with Selectable Input Thresholds and Hysteresis
- On-Chip Bootstrap-Loader
- Supported by a Wealth of Development Tools like C-Compilers, Macro-Assembler Packages, Realtime Operating Systems, Emulators, Evaluation Boards, HLL-Debuggers, Simulators, Logic Analyzer Disassemblers, Programming Boards
- P/PG-MQFP-144 Package
- Full Automotive Temperature Range -40°C to +125°C

Controller Area Network (CAN): License of Robert Bosch GmbH

1) For complete device designations (corresponding to PRO ELECTRON) please refer to the data sheet.


[www.infineon.com/microcontrollers](http://www.infineon.com/microcontrollers)

## Microcontrollers




Never stop thinking

## C167CR Block Diagram



## C167CR Pin Configuration



How to reach us:  
<http://www.infineon.com>

Published by  
 Infineon Technologies AG  
 81726 München, Germany

© Infineon Technologies AG 2006.  
 All Rights Reserved.

### Legal Disclaimer

The information given in this Product Brief shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

### Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

### Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Ordering No. B158-H6845-G7-X-7600  
 Printed in Germany  
 PS 0606 nb