

35CGQ045

PD-94298C

Schottky Rectifier High Efficiency Series Thru-Hole (TO-254AA) 100V, 30A

Features

- Hermetically sealed
- Center tap
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability

Product Summary

- **Part number:** 35CGQ045
- **$I_{F(AV)}$:** 35A
- **V_{RRM} (per leg):** 45V
- **V_F @ 35Apk, $T_J = 125^\circ\text{C}$ (per leg):** 0.94V
- **I_{FSM} @ $t_p = 8.3\text{ms}$ half-sine (per leg):** 200A

Potential Applications

- DC-DC converter
- Protection circuits
- Motor drives



Product Validation

Fully qualified according to MIL-PRF-19500 for space applications

Description

The 35CGQ045 center tap Schottky rectifier has been expressly designed to meet the rigorous requirements of IR HiRel environments. It is packaged in the hermetic isolated TO-254AA package. The device's forward voltage drop and reverse leakage current are optimized for the lowest power loss and the highest circuit efficiency for typical high frequency switching power supplies and resonant power converters. Full MIL-PRF-19500 quality conformance testing is available on source control drawings to TX, TXV and S quality levels.

Ordering Information

Table 1 Ordering options

Part number	Package	Screening Level
35CGQ045	TO-254AA	COTS
35CGQ045SCV	TO-254AA	JANTXV-equivalent
35CGQ045SCX	TO-254AA	JANTX-equivalent
35CGQ045SCS	TO-254AA	S-level

35CGQ045

Schottky Rectifier High Efficiency Series Thru-Hole (TO-254AA)

Table of contents

Table of contents

- Features 1
- Potential Applications..... 1
- Product Validation..... 1
- Description 1
- Ordering Information..... 1
- Table of contents..... 2
- 1 Absolute Maximum Ratings 3
- 2 Device Characteristics 4
 - 2.1 Electrical Characteristics4
 - 2.2 Thermal-Mechanical Specifications4
- 3 Electrical Characteristics Curves..... 5
- 4 Package Outline..... 7
- Revision history..... 8

Absolute Maximum Ratings

1 Absolute Maximum Ratings

Table 2 Absolute Maximum Ratings

Symbol	Parameter	Value	Unit
V_R	DC reverse voltage (per leg)	45	V
V_{RWM}	Working peak reverse voltage (per leg)	45	V
$I_{F(AV)}$	Max. average forward current (per package) ¹ - Refer to Fig. 5	35	A
I_{FSM}	Max. peak one cycle non-repetitive surge current (per leg) ²	200	A
T_J T_{STG}	Operating Junction and Storage Temperature Range	-55 to 150	°C
	Weight	9.3 (Typical)	g

¹ 50% duty cycle @ $T_c = 114^\circ\text{C}$, square waveform

² $t_p = 8.3$ ms half-sine

Device Characteristics

2 Device Characteristics

2.1 Electrical Characteristics

Table 3 Electrical Characteristics

Symbol	Parameter	Max.	Unit	Test Conditions	
V _F	Forward Voltage Drop (Per Leg) See Fig. 1 ¹	0.71	V	@ 17.5A	T _J = -55°C
		0.88	V	@ 35A	
		0.68	V	@ 17.5A	T _J = 25°C
		0.92	V	@ 35A	
		0.65	V	@ 17.5A	T _J = 125°C
		0.94	V	@ 35A	
I _R	Reverse Leakage Current (Per Leg) See Fig. 2 ³	0.1	mA	T _J = 25°C	V _R = rated V _R
		7.0	mA	T _J = 100°C	
		26	mA	T _J = 125°C	
C _J	Junction Capacitance (Per Leg)	1320	pF	V _R = 5V _{DC} (1MHz, 25°C)	
L _S	Series Inductance (Per Leg)	7.8 (Typical)	nH	Measured from anode lead to cathode lead 6mm (0.25 in.) from package	

2.2 Thermal-Mechanical Specifications

Table 4 Thermal-Mechanical Specifications

Symbol	Parameter	Max.	Unit	Test Conditions
$R_{\theta JC}$	Thermal Resistance, Junction to Case (Per Leg)	1.4	$^\circ\text{C}/\text{W}$	DC operation See Fig. 4
$R_{\theta JC}$	Thermal Resistance, Junction to Case (Per Package)	0.7	$^\circ\text{C}/\text{W}$	DC operation
	Die Size (Typical)	170 x 115	mils	

¹ Pulse Width < 300 μs , Duty Cycle < 2%

35CGQ045

Schottky Rectifier High Efficiency Series Thru-Hole (TO-254AA)

Electrical Characteristics Curves

3 Electrical Characteristics Curves




Figure 1 Maximum Forward Voltage Drop Characteristics (Per Leg)




Figure 2 Typical Values of Reverse Current Vs. Reverse Voltage (Per Leg)

Figure 3 Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)

35CGQ045

Schottky Rectifier High Efficiency Series Thru-Hole (TO-254AA)

Electrical Characteristics Curves




Figure 4 Maximum Thermal Impedance Z_{thJC} Characteristics (Per Leg)




Figure 5 Maximum Allowable Case Temperature Vs. Average Forward Current (Per Package)


35CGQ045

Schottky Rectifier High Efficiency Series Thru-Hole (TO-254AA)

Package Outline

4 Package Outline

Note: For the most updated package outline, please see the website: TO-254AA



Revision history**Revision history**

Document version	Date of release	Description of changes
	09/07/2001	Final datasheet (PD-94298)
Rev A	10/04/2001	Updated Vf and Irm–page3
Rev B	09/21/2016	Updated per ECN-1120-04401
Rev C	05/23/2022	Updated per ECN-1120-09098

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-05-23

Published by

**International Rectifier HiRel Products,
Inc.**

**An Infineon Technologies company
El Segundo, California 90245 USA**

**© 2022 Infineon Technologies AG.
All Rights Reserved.**

**Do you have a question about this
document?**

Email: erratum@infineon.com

Document reference

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest International Rectifier HiRel Products, Inc., or Infineon Technologies company, office.

International Rectifier HiRel Components may only be used in life-support devices or systems with the expressed written approval of International Rectifier HiRel Products, Inc., an Infineon Technologies company, if failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety and effectiveness of that device or system.

Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.