

SCHOTTKY RECTIFIER
HIGH EFFICIENCY SERIES

80CLQ150
80 Amp, 150V


Major Ratings and Characteristics

Characteristics	80CLQ150	Units
$I_{F(AV)}$	80	A
V_{RRM} (Per Leg)	150	V
I_{FSM} @ $t_p = 8.3ms$ half-sine (Per Leg)	400	A
V_F @ 40Apk, $T_J = 125^\circ C$ (Per Leg)	0.84	V
T_J, T_{stg} Operating and storage	-55 to 150	$^\circ C$

Description/Features

The 80CLQ150 center tap Schottky rectifier has been expressly designed to meet the rigorous requirements of Hirel environments. It is packaged in the hermetic surface mount SMD-1 ceramic package. The device's forward voltage drop and reverse leakage current are optimized for the lowest power loss and the highest circuit efficiency for typical high frequency switching power supplies and resonant power converters. Full MIL-PRF-19500 quality conformance testing is available on source control drawings to TX, TXV and S quality levels.

- Hermetically Sealed
- Center Tap
- Low Forward Voltage Drop
- High Frequency Operation
- Guard Ring for Enhanced Ruggedness and Long term Reliability
- Surface Mount
- Lightweight



Voltage Ratings

Part number	80CLQ150
V _R Max. DC Reverse Voltage (V) (Per Leg)	150
V _{RWM} Max. Working Peak Reverse Voltage (V) (Per Leg)	

Absolute Maximum Ratings

Parameters	Limits	Units	Conditions
I _{F(AV)} Max. Average Forward Current See Fig. 5	80	A	50% duty cycle @ T _C = 87°C, square waveform
I _{FSM} Max. Peak One Cycle Non - Repetitive Surge Current (Per Leg)	400	A	@ t _p = 8.3 ms half-sine

Electrical Specifications

Parameters	Limits	Units	Conditions
V _{FM} Max. Forward Voltage Drop (Per Leg) See Fig. 1 ①	1.28	V	@ 40A
	1.92	V	@ 80A
	0.96	V	@ 40A
	1.23	V	@ 80A
	0.84	V	@ 40A
	1.16	V	@ 80A
I _{RM} Max. Reverse Leakage Current (Per Leg) See Fig. 2 ①	0.1	mA	T _J = 25°C
	16	mA	T _J = 125°C
C _T Max. Junction Capacitance (Per Leg)	800	pF	V _R = 5V _{DC} (1MHz, 25°C)
L _S Typical Series Inductance (Per Leg)	5.9	nH	Measured from center of cathode pad to center of anode pad

Thermal-Mechanical Specifications

Parameters	Limits	Units	Conditions
T _J Max. Junction Temperature Range	-55 to 150	°C	
T _{stg} Max. Storage Temperature Range	-55 to 150	°C	
R _{thJC} Max. Thermal Resistance, Junction to Case (Per Leg)	1.25	°C/W	DC operation See Fig. 4
R _{thJC} Max. Thermal Resistance, Junction to Case (Per Package)	0.63	°C/W	DC operation
wt Weight (Typical)	2.6	g	
Die Size (Typical)	158X158	mils	
Case Style	SMD-1		

① Pulse Width < 300μs, Duty Cycle < 2%




Fig. 1 - Max. Forward Voltage Drop Characteristics
(Per Leg)




Fig. 2 - Typical Values of Reverse Current
Vs. Reverse Voltage (Per Leg)






Fig. 3 - Typical Junction Capacitance Vs.
Reverse Voltage (Per Leg)

Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)Fig. 5 - Max. Allowable Case Temperature Vs.
Average Forward CurrentInternational
IOR Rectifier

IR WORLD HEADQUARTERS: 101 N, Sepulveda Blvd, El Segundo, California 90245, USA Tel: (310) 252-7105

IR LEOMINSTER : 205 Crawford St., Leominster, Massachusetts 01453, USA Tel: (978) 534-5776

TAC Fax: (310) 252-7903

Visit us at www.irf.com for sales contact information.

Data and specifications subject to change without notice. 02/2014

www.irf.com