



# Feature Overview XC2000 Family

	Core		Flash		SRAM				SB RAM	CAN	ADC	Universal Serial Interface [USIC channels] <sup>1)</sup>	Capture Compare Units [CCU] <sup>2)</sup>			FlexRay	Package	Temperature (T <sub>ambient</sub> )
	Core	Frequency	Program Flash	Data Flash	Σ SRAM	Program [PS RAM]	Data Mem [DS RAM]	Dual Port [DP RAM]					Trace Mem for MCDS	Standby	Channels			

## Feature Overview XC2200 for Body & Convenience

I-Series	C166SV2	128	512-1024	64	90	64	24	2		8	6 max.	24	10 max.	0	1	4	2 max.	LQFP-100/ LQFP-144	-40°C to +125°C
H-Series	C166SV2	100/80	1024-1536	64	106/ 138	112	24	2	4	8	6 max.	24/ 30/40	10 max.	1	1	4	2 max.	LQFP-144/ LQFP-176	-40°C to +125°C
M-Series	C166SV2	80/66	384-768	64	50	32	16	2		8	6 max.	16/24	8 max.	0	1	4	-	LQFP-64/ LQFP-100/ LQFP-144	-40°C to +125°C
(-)-Series	C166SV2	80/66	384-704	64	82	64	16	2		1	5 max.	16/24	6 max.	0	1	4	-	LQFP-100/ LQFP-144	-40°C to +125°C
N-Series	C166SV2	80/66/ 40	128-256	64	34	16	16	2		8	6 max.	9/16	6 max.	0	1	2	-	LQFP-64/ LQFP-100	-40°C to +125°C
L-Series	C166SV2	40/66	32-128	32	12	6	4	2			2 max.	10/19	4	0	1	2	-	VQFN-48/ LQFP-64	-40°C to +125°C
U-Series	C166SV2	40	32/64		8	4	2	2			-	7/10	2	0	1	1	-	TSSOP-38/ VQFN-48	-40°C to +125°C

## Feature Overview XC2300 for Safety

E-Series	C166SV2	80-128	512-1024	64	90	64	24	2		8	3 max.	24 max.	6 max.	0	1	4 max.	2 max.	LQFP-100/ LQFP-144	-40°C to +125°C
C-Series	C166SV2	80-100	768-1024	64	138	112	24	2	4	8	3	24	8	0	1	4	2 max.	LQFP-144	-40°C to +125°C
A-Series	C166SV2	66-80	384-768	64	50	32	16	2		8	3 max.	24 max.	6 max.	0	1	4 max.	-	LQFP-64/ LQFP-100/ LQFP-144	-40°C to +125°C
(-)-Series	C166SV2	66-80	384-512	64	66	48	16	2		1	3 max.	24 max.	6 max.	0	1	2 max.	-	LQFP-100/ LQFP-144	-40°C to +125°C
B-Series	C166SV2	20-80	128-256	64	34	16	16	2		8	3 max.	16 max.	6 max.	0	1	2	-	LQFP-64/ LQFP-100	-40°C to +125°C
D-Series	C166SV2	20-66	32-128	32	12	6	4	2			1 max.	9	4	0	1	2	-	VQFN-48/ LQFP-64	-40°C to +125°C
S-Series	C166SV2	20-40	32-64		8	4	2	2			-	9 max.	2	0	1	1	-	TSSOP-38/ VQFN-48	-40°C to +125°C

1) USIC: can be configured as UART, LIN, SPI/QSPI, I<sup>2</sup>C, I<sup>2</sup>S

2) CCU: used for PWM, D/A

# Feature Overview XC2000 Family

	Core		Flash		SRAM					SB RAM	CAN	ADC	Universal Serial Interface [USIC channels] <sup>1)</sup>	Capture Compare Units [CCU] <sup>2)</sup>			FlexRay	Package	Temperature (T <sub>ambient</sub> )
	Core	Frequency	Program Flash	Data Flash	Σ SRAM	Program [PS RAM]	Data Mem [DS RAM]	Dual Port [DP RAM]	Trace Mem for MCDS	Standby	Channels	Channels (10bit, 1-2μs)		CCU 1	CCU 2	CCU 6			
<b>Feature Overview XC2700 for Powertrain</b>																			
8X-Series	C166SV2	128	1024	64	90	64	24	2			3	24	6	0	1	4	2 max.	LQFP-100/ LQFP-144/ LQFP-176	-40°C to +125°C
7X-Series	C166SV2	100	1024- 1536	64	106/ 138	112	24	2	4	8	3	24/30	6	1	1	4	2 max.	LQFP-144/ LQFP-176	-40°C to +125°C
6X-Series	C166SV2	66	704	64	82	64	16	2		1	2	16/24	4	0	1	4	–	LQFP-100/ LQFP-144	-40°C to +125°C
5X-Series	C166SV2	80	512/768	64	50	32	16	2		8	2	9/16/ 24	6	0	1	4	–	LQFP-64/ LQFP-100/ LQFP-144	-40°C to +125°C
4X-Series	C166SV2	80	256	64	34	16	16	2		8	2	9/16	4	0	1	2	–	LQFP-64/ LQFP-100	-40°C to +125°C
3X-Series	C166SV2	66	128	32	12	6	4	2			2	10/19	4	0	1	2	–	VQFN-48/ LQFP-64	-40°C to +125°C
2X-Series	C166SV2	40	64		8	4	2	2			0	7/10	2	0	1	1	–	TSSOP-38/ VQFN-48	-40°C to +125°C

1) USIC: can be configured as UART, LIN, SPI/QSPI, I<sup>2</sup>C, I<sup>2</sup>S

2) CCU: used for PWM, D/A

How to reach us:  
<http://www.infineon.com>

Published by  
Infineon Technologies AG  
81726 Munich, Germany

© 2009 Infineon Technologies AG  
All Rights Reserved.

**Legal Disclaimer** The information given in this Product Brief shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

**Information** For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

**Warnings** Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office. Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.