



---

The following document contains information on Cypress products. The document has the series name, product name, and ordering part numbering with the prefix “MB”. However, Cypress will offer these products to new and existing customers with the series name, product name, and ordering part number with the prefix “CY”.

#### **How to Check the Ordering Part Number**

1. Go to [www.cypress.com/pcn](http://www.cypress.com/pcn).
2. Enter the keyword (for example, ordering part number) in the **SEARCH PCNS** field and click **Apply**.
3. Click the corresponding title from the search results.
4. Download the Affected Parts List file, which has details of all changes

#### **For More Information**

Please contact your local sales office for additional information about Cypress products and solutions.

#### **About Cypress**

Cypress is the leader in advanced embedded system solutions for the world's most innovative automotive, industrial, smart home appliances, consumer electronics and medical products. Cypress' microcontrollers, analog ICs, wireless and USB-based connectivity solutions and reliable, high-performance memories help engineers design differentiated products and get them to market first. Cypress is committed to providing customers with the best support and development resources on the planet enabling them to disrupt markets by creating new product categories in record time. To learn more, go to [www.cypress.com](http://www.cypress.com).

## F<sup>2</sup>MC-8FX Family, MB95430 Series Voltage Comparator

This application note describes the fundamental of voltage comparator and the register configuration. The related sample codes were given as well.

### 1 Introduction

This application note describes the fundamental of voltage comparator and the register configuration. The related sample codes were given as well.

### 2 Feature of Voltage Comparator

This chapter introduces the features of the voltage comparator.


#### 2.1 Comparator Fundamental

A single comparator is shown in

Figure 1 along with the relationship between the analog input levels and the digital output. When the analog input at CMP\_P is less than the analog input CMP\_N, the output of the comparator is at digital "L" level. When the analog input at CMP\_P is greater than the analog input CMP\_N, the output of the comparator is at digital "H" level.

The shaded areas of the output in Figure 1 represent uncertainty due to input offsets and response time.


Figure 1. Comparator Operation



## 2.2 Block Diagram of Voltage Comparator

Figure 2 shows the block diagram of voltage comparator.

Figure 2. Block Diagram of Voltage Comparator



## 2.3 Pins Associated with the Voltage Comparator

### 2.3.1 Input Pins

For each voltage comparator, there are two analog input pins which are named as CMPn\_P and CMPn\_N, and either of them can be connected to the external reference voltage which depends on the output level desired. Before enabling the voltage comparator, the user has to enable the analog input by clearing the bit CMRn\_VCID. A reset will clear the CMRn\_VCID to default.

Since the input pins are shared by GPIO/VC and internal ADC channel, the right configuration should be done to select the right function of pins, just shown as Table 1.

Table 1. Input Pin Configuration

CMRn_VCID	AIDRH	Pin Status
0(Enable)	0(ADC)	VC and ADC
0(Enable)	1(GPIO)	VC
1(Disable)	0(ADC)	ADC
1(Disable)	1(GPIO)	GPIO

### 2.3.2 Output Pins

The output pins of voltage comparators are shared by several peripherals or GPIOs. The output pins are disabled as default. They can be enabled by set the CMRn\_VCOE to 1.

## 2.4 Edge Detection Circuit

The edge detection circuit detects the level conversion of the comparator output. Except in stop mode, watch time mode or time base mode, a raising edge or a falling edge of voltage comparator output will set the interrupt flag of the related register automatically.

## 2.5 Control Registers (CMR0~CMR3)


These registers are used to turn on and off the voltage comparator (CMR0~CMR3: PD), to enable and disable voltage comparator output (CMR0~CMR3: VCOE), and to enable and disable voltage comparator analog inputs (CMR0~CMR3: VCID).

Except in stop mode, watch mode or time-base timer mode, if CMR0~CMR3: IE has been set to "1", upon detection of a rising edge or falling edge of voltage comparator output, the voltage comparator generates an interrupt request and the interrupt flag bit (CMR0~CMR3: IF) is automatically set to "1" at the same time.

The output status of a voltage comparator channel (ch. 0/1/2/3) can be read through the OS bit in its corresponding voltage comparator control register (CMR0~CMR3).

Figure 3 shows the detailed content of the registers.

Figure 3. Register of Voltage Comparators



## 2.6 Interrupt Vector of Voltage Comparator

If the CMRn\_IE is enabled, the user needs to configure the interrupt vector of voltage comparator first.

Table 2 below shows the interrupt vector.

Table 2. Interrupt Vector

Interrupt source	Interrupt request no.	Interrupt level setting registers		Vector table addresses	
		Register	Setting bit	Upper	Lower
Voltage Comparator channel 0	IRQ10	ILR2	L10	FFE6 <sub>H</sub>	FFE7 <sub>H</sub>
Voltage Comparator channel 1	IRQ11	ILR2	L11	FFE4 <sub>H</sub>	FFE5 <sub>H</sub>
Voltage Comparator channel 2	IRQ12	ILR3	L12	FFE2 <sub>H</sub>	FFE3 <sub>H</sub>
Voltage Comparator channel 3	IRQ13	ILR3	L13	FFE0 <sub>H</sub>	FFE1 <sub>H</sub>

**Note:** In stop mode, watch mode or time-base timer mode, the edge detection circuit stops work, and the interrupt flag bit (IF) of voltage comparator control registers (CMR0~CMR3) will not be updated even if the voltage comparator is turned on.

## 3 Software Operation

### 3.1 Setting Procedure

- Disable interrupt first.
- Enable analog input and disable output.
- Active comparator.
- Wait until comparator becomes stable.
- Clear interrupt flag bit.
- Enable interrupt if necessary.
- Enable output pin if necessary.

## 3.2 Initialization

This routine is the initialization of voltage comparator.

Figure 4. Initialization of Voltage Comparator

```
/*Initialize the voltage comparator*/
CMR0 = 0x00;           // disable the interrupt first
                        // enable analog input
                        // disable analog output
                        // turn off comparator
                        // turn on comparator

CMR0_PD = 1;

__wait_nop();           // several us for comparator
__wait_nop();           // becoming stable
__wait_nop();

CMR0_IF = 0;           // clear flag
CMR0_IE = 1;           // enable interrupt

CMR0_UCOE = 1;         // enable output if necessary
```

To voltage comparator, there is a stable time when it was turned on or the reference voltage changed. Before activating voltage comparator, please preset CMR0~CMR3: IE to 0, in order to avoid any unexpected interrupt request caused by voltage comparator's unstable status during its startup.

## 3.3 Interrupt

The voltage compare interrupt occurs at raising edge or fall edge which depends on the input. So, It is better to confirm the output level first in the ISR.

Figure 5. Interrupt Service Routine

```
__interrupt void UC0_ISR(void)
{
    if(CMR0_IF&CMR0_IE)    // interrupt flag was set
    {
        CMR0_IF = 0;       // clear interrupt flag
        if(CMR0_OS)        // is the "H" level which is expected?
        {;}               // yes
        else
        {;}               // no
    }
}
```

The user should set the interrupt priority and vector in the file vector.c supplied by Cypress, just like this:

Figure 6. Interrupt Priority Setting

```

/*-----
name: InitIrqLevels()
function: Initialize the interrupt priority
-----*/
void InitIrqLevels(void)
{
    //...
    ILR2 = 0xCF;           // IRQ8: Output compare ch1 match
                          // IRQ9: reserved
                          // IRQ10: Voltage comparator ch0
                          // IRQ11: Voltage comparator ch1
    //...
}
/*-----
Prototype
-----*/
__interrupt void VC0_ISR(void);

/*-----
Vector definition
-----*/
#pragma invec VC0_ISR 10 // IRQ10: Voltage comparator ch0

```

All above just take the comparator0 for example. The configuration for comparator 1~3 is almost the same.

## 4 Additional Information

For more Information on Cypress Semiconductor products, visit the following websites:

English version address:

[www.cypress.com/cypress-microcontrollers](http://www.cypress.com/cypress-microcontrollers)

Chinese version address:

[www.cypress.com/cypress-microcontrollers-cn](http://www.cypress.com/cypress-microcontrollers-cn)

### 4.1 Sample Code

Project 1: Voltage Comparator Configuration

```
#include "mb95430.h"
```

```
main ()
```

```
{
```

```

__DI ();
InitLrqLevels ();
__EI ();

/*Initialize the voltage comparator*/
CMR0 = 0x00;                                     // disable the interrupt first
                                                // enable analog input
                                                // disable analog output
                                                // turn off comparator
CMR0_PD = 1;                                     // turn on comparator

__wait_nop ();                                  // several us for comparator
__wait_nop ();                                  // becoming stable
__wait_nop ();

CMR0_IF = 0;                                     // clear flag
CMR0_IE = 1;                                     // enable interrupt

CMR0_VCOE = 1;                                  // enable output if necessary

/*loop*/
while (1)
{;}
}

__interrupt void VC0_ISR (void)
{
    if (CMR0_IF&CMR0_IE)                         // interrupt flag was set
    {
        CMR0_IF = 0;                             // clear interrupt flag
        if (CMR0_OS)                             // is the "H" level which is expected?
        {;}                                       // yes
        else
        {;}                                       // no
    }
}

```



## 5 Document History

Document Title: AN205011 - F<sup>2</sup>MC-8FX Family, MB95430 Series Voltage Comparator

Document Number: 002-05011

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	-	RLIU	03/10/2010	Initial release
			04/12/2010	Updated by review
*A	5243090	RLIU	04/27/2016	Migrated Spansion Application Note MCU-AN-500079-E-11 to Cypress format

## Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

## Products

ARM® Cortex® Microcontrollers	<a href="http://cypress.com/arm">cypress.com/arm</a>
Automotive	<a href="http://cypress.com/automotive">cypress.com/automotive</a>
Clocks & Buffers	<a href="http://cypress.com/clocks">cypress.com/clocks</a>
Interface	<a href="http://cypress.com/interface">cypress.com/interface</a>
Lighting & Power Control	<a href="http://cypress.com/powerpsoc">cypress.com/powerpsoc</a>
Memory	<a href="http://cypress.com/memory">cypress.com/memory</a>
PSoC	<a href="http://cypress.com/psoc">cypress.com/psoc</a>
Touch Sensing	<a href="http://cypress.com/touch">cypress.com/touch</a>
USB Controllers	<a href="http://cypress.com/usb">cypress.com/usb</a>
Wireless/Rf	<a href="http://cypress.com/wireless">cypress.com/wireless</a>

## PSoC® Solutions

[cypress.com/psoc](http://cypress.com/psoc)

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#)

## Cypress Developer Community

[Community](#) | [Forums](#) | [Blogs](#) | [Video](#) | [Training](#)

## Technical Support

[cypress.com/support](http://cypress.com/support)

PSoC is a registered trademark and PSoC Creator is a trademark of Cypress Semiconductor Corp. All other trademarks or registered trademarks referenced herein are the property of their respective owners.



Cypress Semiconductor  
198 Champion Court  
San Jose, CA 95134-1709  
Phone : 408-943-2600  
Fax : 408-943-4730  
Website : [www.cypress.com](http://www.cypress.com)

© Cypress Semiconductor Corporation, 2010-2016. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit [cypress.com](http://cypress.com). Other names and brands may be claimed as property of their respective owners.