

SCHOTTKY RECTIFIER HIGH EFFICIENCY SERIES

30 Amp. 30V

Major Ratings and Characteristics



Characteristics	30SCLJQ030	Units
$I_{F(AV)}$ (Per Leg)	30	A
V_{RRM} (Per Leg)	30	V
I_{FSM} @ $t_p = 8.3ms$ half-sine (Per Leg)	130	A
V_F @ 30Apk, $T_J = 125^\circ C$ (Per Leg)	0.82	V
T_J, T_{stg} Operating and storage	-55 to 150	$^\circ C$

Description/Features

The 30SCLJQ030 center tap Schottky rectifier has been expressly designed to meet the rigorous requirements of IR HiRel environments. It is packaged in the hermetic surface mount SMD-0.5 ceramic package. The device's forward voltage drop and reverse leakage current are optimized for the lowest power loss and the highest circuit efficiency for typical high frequency switching power supplies and resonant power converters. Full MIL-PRF-19500 quality conformance testing is available on source control drawings to TX, TXV and S quality levels.


- Hermetically Sealed
- Center Tap
- Low Forward Voltage Drop
- High Frequency Operation
- Guard Ring for Enhanced Ruggedness and Long term Reliability
- Surface Mount

CASE STYLE



NOTES:

1. DIMENSIONING & TOLERANCING PER ASME Y14.5M-1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
4. DIMENSION INCLUDES METALLIZATION FLASH.
5. DIMENSION DOES NOT INCLUDE METALLIZATION FLASH.



Case Outline and Dimensions - SMD-0.5

Voltage Ratings

Part Number	30SCLJQ030
V_R Max. DC Reverse Voltage (V) (Per Leg)	30
V_{RRM} Max. Working Peak Reverse Voltage (V) (Per Leg)	

Absolute Maximum Ratings

Parameter	Limits	Units	Conditions
$I_{F(AV)}$ Max. Average Forward Current (Per Leg) See Fig. 5	30	A	50% duty cycle @ $T_C = 80^\circ\text{C}$, square waveform
I_{FSM} Max. Peak One Cycle Non - Repetitive Surge Current (Per Leg)	130	A	$t_p = 8.3$ ms half-sine

Electrical Specifications

Parameter	Limits	Units	Conditions
V_{FM} Max. Forward Voltage Drop (Per Leg) See Fig. 1①	0.67	V	$I_F = 15\text{A}$ $T_J = -55^\circ\text{C}$
	0.85	V	$I_F = 30\text{A}$
	0.61	V	$I_F = 15\text{A}$ $T_J = 25^\circ\text{C}$
	0.82	V	$I_F = 30\text{A}$
	0.55	V	$I_F = 15\text{A}$ $T_J = 125^\circ\text{C}$
	0.82	V	$I_F = 30\text{A}$
I_{RM} Max. Reverse Leakage Current (Per Leg) See Fig. 1①	0.27	mA	$T_J = 25^\circ\text{C}$ $V_R = \text{rated } V_R$
	17	mA	$T_J = 100^\circ\text{C}$
	80	mA	$T_J = 125^\circ\text{C}$
C_T Max. Junction Capacitance (Per Leg)	518	pF	$V_R = 5V_{DC}$ (1MHz, 25°C)
L_S Typical Series Inductance (Per Leg)	4.8	nH	Measured from center of cathode pad to center of anode pad

Thermal-Mechanical Specifications

Parameter	Limits	Units	Conditions
T_J Max. Junction Temperature Range	-55 to 150	$^\circ\text{C}$	
T_{stg} Max. Storage Temperature Range	-55 to 150	$^\circ\text{C}$	
R_{thJC} Max. Thermal Resistance, Junction to Case (Per Leg)	3.5	$^\circ\text{C/W}$	DC operation See Fig. 4
R_{thJC} Max. Thermal Resistance, Junction to Case (Per Package)	1.75	$^\circ\text{C/W}$	DC operation
W_t Weight (Typical)	1.0	g	
Die Size (Typical)	70 x 92	mils	
Case Style	SMD-0.5		

① Pulse Width < 300 μs , Duty Cycle < 2%




Fig 1. Max. Forward Voltage Drop Characteristics (Per Leg)




Fig 2. Typical Values of Reverse Current Vs. Reverse Voltage (Per Leg)




Fig 3. Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)




Fig 4. Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)




Fig 5. Max. Allowable Case Temperature Vs. Average Forward Current (Per Leg)

IMPORTANT NOTICE

The information given in this document shall be in no event regarded as guarantee of conditions or characteristic. The data contained herein is a characterization of the component based on internal standards and is intended to demonstrate and provide guidance for typical part performance. It will require further evaluation, qualification and analysis to determine suitability in the application environment to confirm compliance to your system requirements.

With respect to any example hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind including without limitation warranties on non- infringement of intellectual property rights and any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's product and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of any customer's technical departments to evaluate the suitability of the product for the intended applications and the completeness of the product information given in this document with respect to applications.

For further information on the product, technology, delivery terms and conditions and prices, please contact your local sales representative or go to (www.infineon.com/hirel).

WARNING

Due to technical requirements products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.