

AN321

Migrating from Grade 1 version of FM25040A to Grade 1 version of FM25040B

Author: Girija Chougala

Associated Project: No

Associated Part Family: FM25040A-GA, FM25040B-GA

Software Version: None

Related Documents: For a complete list, [click here](#)

AN321 discusses the key differences that need to be considered when migrating from Grade 1 version of FM25040A to Grade 1 version of FM25040B. FM25040A is now obsolete and this application note explains how FM25040B is a replacement for FM25040A.

Introduction

The FM25040B-GA, a 4-Kbit SPI Grade 1 F-RAM™, is a replacement device for FM25040A-GA, which is now obsolete. The two devices are identical in terms of package, pinout, DC / AC parameters, and read / write functionality. This application note discusses the key differences between the two devices that need to be considered when migrating from FM25040A-GA to FM25040B-GA.

Drop-In Replacement or Not?

From a software point of view, the two devices are identical. Both devices are read/write compatible and use the same one-byte address. From a hardware point of view, the key difference between the two devices is the FM25040B-GA's lower operating current. Additionally, FM25040B-GA datasheet adds a power-up ramp rate, power-down ramp rate and first-access time specification.

[Table 1](#) shows the compatibility chart of FM25040A-GA and FM25040B-GA. For a detailed comparison, see [Table 3](#).

Ordering Part Numbers

[Table 2](#) gives the recommended FM25040A-GA ordering part numbers that correspond to the now obsolete FM25040B-GA ordering part numbers.

Table 1. Compatibility Chart

FM25040A-GA Feature or Spec	Is FM25040B-GA compatible?
Package	Yes
Pinout	Yes
Temperature Range	Yes
Operating Voltage	Yes
Operating Current	Yes
Standby Current	Yes
Read / Write Function	Yes
Timing / Frequency	Yes
Data Retention	Yes
Endurance	Yes

Table 2. Recommended Ordering Part Numbers for Migration

FM25040A-GA		FM25040B-GA		Comments
Ordering Part Number	Status	Ordering Part Number	Status	
FM25040A-GA	Obsolete	FM25040B-GA	In production	No hardware or software change is required
FM25040A-GATR		FM25040B-GATR		

Comparison of FM25040A and FM25040B

Table 3 gives a detailed comparison of the two devices.

Table 3. Detailed Comparison

	FM25040A-GA	FM25040B-GA	Comments
Package Types	-GA	-GA	Identical "green" SOIC package
Package Outlines	SOIC-8	SOIC-8	Identical outline and board footprint
Pinout	-	-	Identical
Temperature Range	-40 °C to +125 °C	-40 °C to +125 °C	Identical
Operating Voltage Range	4.5 V to 5.5 V	4.5 V to 5.5 V	Identical
Active Supply Current	500 μ A @ 1 MHz 6.0 mA @ 14 MHz	300 μ A @ 1 MHz 3.0 mA @ 14 MHz	FM25040B-GA offers lower active current.
Standby Current	10 μ A (+85 °C) 30 μ A (+125 °C)	10 μ A (+85 °C) 30 μ A (+125 °C)	Identical
Read / Write Function	-	-	Identical one-byte addressing, Identical op-codes
Clock Frequency	14 MHz	14 MHz	Identical
AC Timing Parameters	-	-	All specification limits are the Identical
Data Retention	9000 hours (+125 °C) after 17 years (+55 °C)	11000 hours (+125 °C) 11 years (+105 °C) 121 years (+85 °C)	FM25040B-GA offers better data retention
Endurance (Write/Read Cycles)	1E+12	1E+13	FM25040B-GA offers better endurance
V _{DD} Power-Up Ramp Rate (t _{VR})	-	30 μ s / V	Power-up ramp rate should be slower than 30 μ s / V for FM25040B-GA
V _{DD} Power-Down Ramp Rate (t _{VF})	-	20 μ s / V	Power-down ramp rate should be slower than 20 μ s / V for FM25040B-GA
Power-Up to First Access (t _{PU})	-	1 ms	After power-up, the first access of FM25040B-GA should be after 1 ms

Critical Considerations

You should consider all the parameter differences mentioned in Table 3 during the migration to FM25040B-GA. This section discusses the critical differences. System designers should also review the [datasheet](#) when migrating to the new part.

V_{DD} Ramp Rate

V_{DD} power-up and power-down ramp rate specifications are added in FM25040B-GA device. Ensure that the power-up ramp rate is slower than 30 μ s / V and power-down ramp rate is slower than 20 μ s / V in your system for proper operation of the device.

Power-Up to First Access

Power-up to first access specification is added in FM25040B-GA device. Ensure that the FM25040B-GA device is accessed only after 1 ms from power-up.

Summary

AN321 discussed the differences between the Grade 1 versions of FM25040A and FM25040B that need to be considered during migration to the FM25040B.

Related Documents

Datasheet

[FM25040B: 4-Kbit \(512 × 8\) Serial \(SPI\) Automotive F-RAM datasheet](#)

Application Note

[AN304 – SPI GUIDE FOR F-RAM](#)

Document History

Document Title: Migrating from Grade 1 version of FM25040A to Grade 1 version of FM25040B - AN321

Document Number: 001-86844

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	3944550	GVCH	03/26/2013	New Spec.
*A	4279208	MEDU	03/05/2014	Updated to Cypress Template. Updated data retention for FM25040B-GA. Updated "V _{DD} Power-Down Ramp Rate" for FM25040B-GA from 100 µs / V to 20 µs / V. Updated "Power-Up to First Access" for FM25040B-GA from 10 ms to 1 ms.
*B	4498653	GVCH	09/22/2014	Changed title from "Differences between Grade 1 versions of FM25040A and FM25040B" to "Migrating from Grade 1 version of FM25040A to Grade 1 version of FM25040B." Updated abstract. Added " Ordering Part Numbers " section. Added title for Table 3 . Added " Related Documents " section.



Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

Products

Automotive	cypress.com/go/automotive
Clocks & Buffers	cypress.com/go/clocks
Interface	cypress.com/go/interface
Lighting & Power Control	cypress.com/go/powerpsoc cypress.com/go/plc
Memory	cypress.com/go/memory
PSoC	cypress.com/go/psoc
Touch Sensing	cypress.com/go/touch
USB Controllers	cypress.com/go/usb
Wireless/RF	cypress.com/go/wireless

PSoC® Solutions

psoc.cypress.com/solutions

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#)

Cypress Developer Community

[Community](#) | [Forums](#) | [Blogs](#) | [Video](#) | [Training](#)

Technical Support

cypress.com/go/support

PSoC is a registered trademark of Cypress Semiconductor Corp. All other trademarks or registered trademarks referenced herein are the property of their respective owners.



Cypress Semiconductor Phone : 408-943-2600
198 Champion Court Fax : 408-943-4730
San Jose, CA 95134-1709 Website : www.cypress.com

© Cypress Semiconductor Corporation, 2013-2014. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

This Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.