

Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.



THIS SPEC IS OBSOLETE

Spec No: 001-16711

Spec Title: IBIS5B-1300 CAMERA RECOMMENDATIONS
-AN6018

Sunset Owner: Evelyn Beard (EYB)

Replaced by: None

Application Note Abstract

This document provides recommendations to avoid column nonuniformities. It also provides supply voltages to eliminate the image lag issue in snapshot shutter mode.

Synchronous (Snapshot) Shutter

Column Nonuniformities

After extensive evaluation, a relation was found between the position of the Y-readout pointer after read out and vertical column nonuniformities in the next frame, visible at higher gain settings. If the Y-readout pointer continues to select a line during the global reset of the next frame, the column reset is corrupted, which is visible after integration as column nonuniformities.

The images in Figure 1 are taken with the same settings (gain and integration time) but have a difference in the position of the Y-readout pointer during global reset. Note that histogram equalization is done on the images to show the effect more clearly. On the left image, the Y-readout pointer is completely shifted out of the pixel array so that the pointer does not select a line during global reset. This results in no column nonuniformities. In the middle and right image, the Y-readout pointer is still selecting a line during global reset and introduces column nonuniformities.

Column nonuniformities, as shown in the images in Figure 1, can also be introduced by different intervals between successive images. The recommended timing helps to solve this.

To make sure that the Y-readout pointer is not selecting a line during global reset, it is recommended to adapt timing in synchronous shutter mode (single slope mode). Figure 2 shows the standard timing, as explained in the data sheets of IBIS5B-1300. Figure 3 shows the adapted timing.

- T_1 Should be minimum one row blanking time. The row blanking time depends on the X-granularity; see the Basic Operation Timing section in the data sheet.
- T_2 During this time, the SS-sequencer applies the control signals to reset the image core and start integration. This takes four granulated SS-sequencer clock periods. The integration time counter starts counting at the first rising edge after the falling edge of SYS_CLOCK.
- T_3 The SS-sequencer puts the image core in a readable state. It takes two granulated SS-sequencer clock periods.
- T_{int} The "real" integration or exposure time.

Figure 1. Test Chart Images with (center, right) and without (left) Column Nonuniformities




Figure 2. Standard Synchronous Shutter Single Slope Integration Timing





Figure 3. Adapted Timing



To make sure that no line is selected during the global reset, upload value 1023 (decimal value; hexadecimal value 3FF) to the YL_REG and YR_REG registers before assertion of the first Y_START. This selects the last line when Y_START is asserted with Y_CLOCK; pulsing the second Y_CLOCK shifts the Y-readout pointer out of the shift register before the global reset occurs. Between the falling edge of the first Y_START and the rising edge of the SS_STOP pulse, upload the YL(R)_REG registers (registers 5 and 6) with the start row of the ROI.

Note that this additional Y_START sequence adds a delay between a trigger event and the actual start of integration. This delay is equal to twice the row blanking time ($2 \times 3.5 \mu\text{s} = 7 \mu\text{s}$ with minimal X-granularity). Indicated as time T_2 in Figure 3, it takes another four SS granular clock periods after SS_START before the pixels actual start to integrate.

Supply Considerations

With the recommended supply voltages in the data sheets (Table 5; p11) the snapshot shutter suffers slightly from image lag at higher gain settings. The supply voltage settings listed in Table 1 remove the image lag issue completely.

Figure 4. Rolling Shutter Image (supply settings listed in Table 1 (left) or in Table 2 (right))





Table 1. Recommended Supply Voltages - Snapshot Shutter

Parameter	Description	Typ	Unit
VDDH	Voltage on HOLD switches	+4.5	V
VDDR_LEFT	Highest reset voltage	+4.5	V
VDDC	Pixel core voltage	+3.3	V
VDDA	Analog supply voltage of the image core	+3.3	V
VDDD	Digital supply voltage of the image core	+3.3	V
GNDA	Analog ground	0	V
GNDD	Digital ground	0	V
GND_AB	Anti-blooming ground	0	V

Table 2. Recommended Supply Voltages -Rolling Shutter

Parameter	Description	Typ	Unit
VDDH	Voltage on HOLD switches	+4.0	V
VDDR_LEFT	Highest reset voltage	+4.0	V
VDDC	Pixel core voltage	+3.3	V
VDDA	Analog supply voltage of the image core	+3.3	V
VDDD	Digital supply voltage of the image core	+3.3	V
GNDA	Analog ground	0	V
GNDD	Digital ground	0	V
GND_AB	Anti-blooming ground	0	V

Rolling Shutter

Supply Considerations

The recommended supply voltages in the data sheets (Table 5; p11) and the settings in Table 1 can result in vertical column non-uniformities in rolling shutter mode (see images in Figure 4; note that histogram equalization is done on the images to show the effect more clearly. Settings for both images are equal).

To avoid these problems, change the value of the supply voltages listed in the data sheets to the values listed in Table 2.

Table 3 lists the recommended supply voltages for dual-shutter mode (both rolling and snapshot shutter). These settings eliminate both the image lag issue in snapshot shutter and the column nonuniformities in rolling shutter mode.

Table 3. Recommended Supply Voltages - Dual Shutter

Parameter	Description	Typ	Unit
VDDH	Voltage on HOLD switches	+4.5	V
VDDR_LEFT	Highest reset voltage	+4.5	V
VDDC	Pixel core voltage	+3.0	V
VDDA	Analog supply voltage of the image core	+3.3	V
VDDD	Digital supply voltage of the image core	+3.3	V
GNDA	Analog ground	0	V
GNDD	Digital ground	0	V
GND_AB	Anti-blooming ground	0	V

Document History

Document Title: IBIS5B-1300 Camera Recommendations

Document Number: 001-16711

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	1340803	YIS	See ECN	New application note
*A	3148590	NPA	01/20/11	Changed IBIS5A-1300 to IBIS5B-1300. Added Application Note Abstract section and Document History table
*B	4113912	MTA	09/04/13	Obsolete specs.

In March of 2007, Cypress recataloged all of its Application Notes using a new documentation number and revision code. This new documentation number and revision code (001-xxxx, beginning with rev. **), located in the footer of the document, will be used in all subsequent revisions.

Cypress Semiconductor
198 Champion Court
San Jose, CA 95134-1709
Phone: 408-943-2600
Fax: 408-943-4730
<http://www.cypress.com>

© Cypress Semiconductor Corporation, 2005-2013. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

This Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.

All product and company names mentioned in this document are the trademarks of their respective holders.

OBESO LIFE