

MB89630 Series, Using A PWM Timer As The Clock Input For The UART

This Application Note gives a short example on how to calculate timer settings for configuring the PWM-Timer so that the UART clock of the MB89630 can be provided by the timer.

1 Introduction

This Application Note gives a short example on how to calculate timer settings for configuring the PWM-Timer so that the UART clock of the MB89630 can be provided by the timer.

2 Background:

The UART block of the MB89630 series controller allows to select its required clock signal from 4 different sources.

The 1st source is a dedicated baud-rate generator belonging to the UART block, which is most suitable if the controller operates with a 10 MHz main clock to derive popular baud rates of 9600-, 4800, 2400- etc. baud.

If the main-clock is chosen to be different, it's most likely that the desired baud rate cannot be generated by this dedicated generator.

In this case, the UART can receive its clock signal from either PWM-Timer 1 or 2, which can be programmed to produce the required clock signal, or finally from an external clock input.

Following, this relationship between main-clock, PWM-timer setting and baud rate will be discussed.

It should be noticed, that if a PWM Timer is used for the UART clock generation, the PWM-Timer must be configured to operate as a simple timer and not to generate a PWM-signal, so the name 'PWM-Timer' might be confusing.

3 Formulas

The output clock frequency of the PWM timer can be calculated according to the following formula:

$$f_{PWM} = \frac{f_{MAIN}}{8 * SC * (COMR + 1)}$$

f_{PWM} : PWM-Timer Output Frequency

f_{MAIN} : Main Clock Frequency

SC : PWM-Timer Input Clock Selector

can be set to {1 | 8 | 16 | 64}

COMR : Timer Value

Can be set to 0..256

The UART baud rate (assuming it is driven by the PWM timer) is given by :

$$BR = \frac{f_{PWM}}{CR}$$

CR : UART Clock Division Ratio
can be set to {16 | 64}

If we rearrange the equations to derive COMR we get:

$$COMR = \frac{f_{MAIN}}{BR * 8 * SC * CR} - 1$$

Example 1:

Let's assume:

Main Clock	$f_{MAIN} = 10 \text{ MHz}$
PWM-Timer Selector	SC = 1
UART Clock Ratio	CR = 16
and the Baud Rate shall be	BR = 9600

COMR = 7.138

Thus, the PWM timer would have to be set to the integer value 7.

If we recalculate the baud rate with this timer value the real baud rate would be 9765.625 baud, which results in a 1.7 % deviation.

The equation can also be used to calculate main-clock frequencies which allow to realize precise baud-rates. The following table lists some of these frequencies to realize a baud rate of 9600 baud.

Main-Clock Frequency	COMR-Setting
(1,2288 MHz)	1
2,4576 MHz	1
3,6864 MHz	2
4,9152 MHz	3
6,144 MHz	4
7,3728 MHz	5
(8,6016 MHz)	6
9,8304 MHz	7
11,0592 MHz	8

4 Document History

Document Title: AN204936 - MB89630 series, Using a PWM Timer as the clock input for the UART

Document Number: 002-04936

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	-	NOFL	02/20/2014	Initial release
*A	5270047	NOFL	10/12/2016	Migrated Spansion Application Note MCU-AN-389014-E-V10 to Cypress format
*B	5877525	AESATMP9	09/08/2017	Updated logo and copyright.

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

Products

ARM® Cortex® Microcontrollers	cypress.com/arm
Automotive	cypress.com/automotive
Clocks & Buffers	cypress.com/clocks
Interface	cypress.com/interface
Internet of Things	cypress.com/iot
Memory	cypress.com/memory
Microcontrollers	cypress.com/mcu
PSoC	cypress.com/psoc
Power Management ICs	cypress.com/pmic
Touch Sensing	cypress.com/touch
USB Controllers	cypress.com/usb
Wireless Connectivity	cypress.com/wireless

PSoC® Solutions

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#) | [PSoC 6](#)

Cypress Developer Community

[Forums](#) | [WICED IOT Forums](#) | [Projects](#) | [Videos](#) | [Blogs](#) | [Training](#) | [Components](#)

Technical Support

cypress.com/support

All other trademarks or registered trademarks referenced herein are the property of their respective owners.



Cypress Semiconductor
198 Champion Court
San Jose, CA 95134-1709

© Cypress Semiconductor Corporation, 2013-2017. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spanion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spanion, the Spanion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.