

Product Brief

AURIX™ TC3Ex

High-performance chassis, powertrain, body and autonomous driving microcontroller

Infineon releases its second generation AURIX [™] microcontroller in embedded flash 40 nm technology. It comes back with an increase in performance, memory sizes, connectivity and more scalability to address the new automotive trends and challenges. This family has more than 20 products to provide the most scalable portfolio of safety microcontrol-ler. In terms of performance, T3Ex offers 4 cores running at 300 MHz and up to 1.5 MBytes embedded RAM, and consuming below 2 W. Its mirrored embedded flash banks offers A/B swap capabilities.

Safety is the core know-how of Infineon, and all products provide safety mechanism (including but not limited to lock-step cores, LBIST, ECC RAM) to ensure a safety platform supporting ASIL-D ISO 26262. The TC3Ex has 2 lock-stepped cores and 2 non lock-stepped cores, providing up to 1350 DMIPS in ASIL-D and 2700 DMIPS in ASIL-B.

In terms of security, this product has an HSM compliant eVita full, ensuring the implementation of future proofed security measure. On top of this, it offers extensive connectivity with up to 20 CAN FD, 4 channels FlexRay, 24 LINs, 6 QSPI and new high-speed communicating interfaces such as Gbit Ethernet, which are critical to address new domain control and connected gateway ECUs.

The AURIXTM TC3xx family features a dedicated 8-bit standby mode controller, with its own voltage domain to, not only support low power modes, but also to perform certain operations such as analog measurements, CAN and LIN communication, RTC and basic processing while the rest of microcontroller is in standby.

Finally to ensure the scalability, the whole family shares its core architecture (TriCore[™] based), allowing a maximum of software re-use. The TC3Ex is upward compatible with the higher performance TC39x and downward compatible to TC38x, TC37x, TC36x and TC33x. This product offers as well the capability to be coupled to either and ASIC or another TC3Ex through a dedicated high-speed interface (HSSL) in order to increase the performances of the ECU. The HSSL is an LVDS based interconnection with low latency and speed up to 320 Mbit/s.

Key features

- > 4 TriCore ™ running at 300 MHz with
 2 additional checker cores delivering
 2700 DMIPS
- > up to 12 MB flash and up to 1.5 MB SRAM
- > 1 Gbit Ethernet and up to 20 CAN FD
- > ISO 26262 ASIL-D support
- > eVita full HSM (ECC256 and SHA2)
- > Standby mode controller
- > AUTOSAR 4.2 support
- > 165°C junction temperature

Key benefits


- >Best-in-class performance
- enabling ASIL-D designs
- > Upward and downward scalable to
- the rest of AURIX[™] TC3xx family > A/B swap software update over the air support
- > Easy migration from AURIX™
- TC2xx thanks to high software and hardware compatibility

Key applications

- > Domain controllers
- > Sensor fusion and autonomous
- driving computers
- > Chassis and powertrain
- > High end gateways and body
- domain controllers

AURIX™ TC3Ex

High-performance chassis, powertrain, body and autonomous driving microcontroller



Product table

Туре	Description	Ordering code
SAK-TC3E7QF-192F300S	4x 300 MHz TriCoreTM, 12 MB Flash, 1.5 MB SRAM, 1 Gbit/s Ethernet, 12 CAN FD, eVita Full HSM, LFBGA-292	on request
SAK-TC3E7QX-192F300S	4x 300 MHz TriCoreTM, 12 MB Flash, 1.5 MB SRAM, 1 Gbit/s Ethernet, 20 CAN FD, eVita Full HSM, LFBGA-292	on request
SAK-TC3E7QG-160F300S	4x 300 MHz TriCoreTM, 10 MB Flash, 1.5 MB SRAM, 1 Gbit/s Ethernet, 20 CAN FD, eVita Full HSM, LFBGA-292	on request

www.infineon.com/aurixtc3ex

Published by Infineon Technologies AG 81726 Munich, Germany

© 2019 Infineon Technologies AG. All Rights Reserved. Please note!

THIS DOCUMENT IS FOR INFORMATION PURPOSES ONLY AND ANY INFORMATION GIVEN HEREIN SHALL IN NO EVENT BE REGARDED AS A WARRANTY, GUARANTEE OR DESCRIPTION OF ANY FUNCTIONALITY, CONDITIONS AND/OR QUALITY OF OUR PRODUCTS OR ANY SUITABILITY FOR A PARTICULAR PURPOSE. WITH REGARD TO THE TECHNICAL SPECIFICATIONS OF OUR PRODUCTS, WE KINDLY ASK YOU TO REFER TO THE RELEVANT PRODUCT DATA SHEETS PROVIDED BY US, OUR CUSTOMERS AND THEIR TECHNICAL DEPARTMENTS ARE REQUIRED TO EVALUATE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED APPLICATION.

WE RESERVE THE RIGHT TO CHANGE THIS DOCUMENT AND/OR THE INFORMATION GIVEN HEREIN AT ANY TIME.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any lifeendangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.

Order Number: B158-I0537-V1-7600-EU-EC-P Date: 03 / 2019