



---

The following document contains information on Cypress products. The document has the series name, product name, and ordering part numbering with the prefix “MB”. However, Cypress will offer these products to new and existing customers with the series name, product name, and ordering part number with the prefix “CY”.

#### **How to Check the Ordering Part Number**

1. Go to [www.cypress.com/pcn](http://www.cypress.com/pcn).
2. Enter the keyword (for example, ordering part number) in the **SEARCH PCNS** field and click **Apply**.
3. Click the corresponding title from the search results.
4. Download the Affected Parts List file, which has details of all changes

#### **For More Information**

Please contact your local sales office for additional information about Cypress products and solutions.

#### **About Cypress**

Cypress is the leader in advanced embedded system solutions for the world's most innovative automotive, industrial, smart home appliances, consumer electronics and medical products. Cypress' microcontrollers, analog ICs, wireless and USB-based connectivity solutions and reliable, high-performance memories help engineers design differentiated products and get them to market first. Cypress is committed to providing customers with the best support and development resources on the planet enabling them to disrupt markets by creating new product categories in record time. To learn more, go to [www.cypress.com](http://www.cypress.com).

## FR, MB91460, Clock Monitor

The Clock Monitor is a module that outputs internal clock signals to a terminal to externally monitor them. The Clock Monitor provides a function to divide the frequency of a clock signal before it outputs to the terminal, thus allowing the clock signal to be used as an event at which external circuits act in synchronization with a MCU function.

### Contents

1	Introduction.....	1	3	Software Example .....	5
1.1	Key Features .....	1	3.1	Basic Functionality of the Clock Monitor .....	5
2	Clock Monitor.....	2	4	Additional Information.....	5
2.1	Block Diagrams.....	2		Document History.....	6
2.2	Operation .....	2			
2.3	Registers.....	3			

## 1 Introduction

The Clock Monitor is a module that outputs internal clock signals to a terminal to externally monitor them. The Clock Monitor provides a function to divide the frequency of a clock signal before it outputs to the terminal, thus allowing the clock signal to be used as an event at which external circuits act in synchronization with a MCU function.

Not all devices are having this feature. Please refer datasheet of corresponding device to check availability of this function.

### 1.1 Key Features

- Divide an internal clock signal to output it to a terminal (MONCLK)
- Maximum frequency that can be monitored on a terminal (MONCLK) is 50MHz
- A dedicated MONCLK pin is available and no port function registers are required to set for enabling it.
- Division ratios: CLK/1, CLK/2, CLK/3, ..., CLK/16
- Programmable mark level (output “L” or “H” before enabling the clock output)
- Glitch free output enable


## 2 Clock Monitor

The basic functionality of the clock monitor is explained

### 2.1 Block Diagrams

Figure 1 shows the internal block diagram of a Clock Monitor.

Figure 1. Clock Monitor



### 2.2 Operation

Due to the glitch free switching mechanism it is necessary to follow these rules when switching the clock source (CMCFG3:0) or the pre-scalar ratio (CMPRE3:0):

- The CMPRE3:0 registers can only be written if the CMSEL3:0 registers are currently 0x00.
- The CMPRE3:0 registers can only be written if the CMSEL3:0 registers are written to 0x00 within the same write access.
- Between 2 write accesses to CMPRE/CMCFG there must be at least 2 cycles of the divided monitor clock.
- For changing the selector value, the MONCLK must be disabled.

## 2.3 Registers

### 2.3.1 Monitor Configuration Register (CMCFG)

This register selects output settings of an Internal Clock Signal

Table 1. CMCFG

Bit No.	Name	Explanation	Value	Operation
7,6,5,4	CMPRE3-CMPRE0	Select an output frequency prescaler	0000	Source clock (selected by CMSEL) divided by 1 (Initial)
			0001	Source clock (selected by CMSEL) divided by 2
			...	...
			...	...
			1110	Source clock (selected by CMSEL) divided by 15
			1111	Source clock (selected by CMSEL) divided by 16
3,2,1,0	CMSEL3-CMSEL0	Select a clock source	0000	MONCLK output disabled (high impedance) (Initial)
			0001	OSCMAN
			0010	OSCSUB
			0011	CLKRC
			0100	CLKSUBRC
			0101	CLKMAIN
			0110	CLKSUB
			0111	CLKMOD
			1000	Clock modulator observer output*
			1001	PLL output after 1/g divider (Auto Gear)
			1010	PLL output after 1/m divider
			1011	CLKCAN
			1100	CLKPLLFB
			1101	CLKB
			1110	CLKP
			1111	CLKT

\*Silicon evaluation purposes only, not available for customer applications.

### 2.3.2 Clock Source Configuration Register (CSCFG)

Table 2. CSCFG

Bit No.	Name	Explanation	Value	Operation for Channel (2n+0) or (2n+1)
7	EDSUEN	EDSU/MPU Enable	0	EDSU/MPU is (clock) disabled [Initial value]
			1	EDSU/MPU is (clock) enabled
6	PLLLOCK	PLL Lock	0	PLL is in the un-locked state
			1	PLL is in the locked state
5	RCSEL	CLKRC Selector	0	CLKRC is set to 100kHz [Initial value]
			1	CLKRC is set to 2MHz
4	MONCKI	Clock Monitor MONCLK inverter	0	MONCLK mark level is low [Initial value]
			1	MONCLK mark level is high
3	CSC3	Clock Source Selection for LCD Controller	0	LCD Controller is sourced by Sub Oscillator
			1	LCD Controller is sourced by RC Oscillator (100kHz)
2	CSC2	Clock Source Selection for Sub clock calibration	0	Sub clock Calibration is sourced by Sub Oscillator
			1	Sub clock Calibration is sourced by RC Oscillator(100kHz)
1,0	CSC1, CSC0	Clock Source Selection for RTC	00	Real Time Clock is sourced by Main Oscillator
			01	Real Time Clock is sourced by Sub Oscillator
			10	Real Time Clock is sourced by RC Oscillator(100kHz)
			11	Setting prohibited

### 3 Software Example

Example for Clock Monitor

#### 3.1 Basic Functionality of the Clock Monitor

The following example sets clock source and clock divider.

```
/*                      SAMPLE CODE                      */
/*-----*/

void InitClockMonitor(unsigned char divider, unsigned char clk_source)
{
    /* disable MonClk output */
    CMCFG = (CMCFG & 0xF0);
    while (CMCFG & 0x0F) {
        HWWD_CL = 0;
    }
    /* Set Pre scalar value */
    CMCFG = (CMCFG & 0x0F) | (divider << 4);

    /* Enable MonClk output */
    CMCFG = CMCFG | (clk_source & 0x0F);
}
```

**Note:** Maximum frequency that can be monitored on a terminal (MONCLK) is 50MHz

### 4 Additional Information

Information about Cypress Microcontrollers can be found on the following Internet page:

<http://www.cypress.com/cypress-microcontrollers>

The software examples related to this application note is:

*91460\_monclk*

It can be found on the following Internet page:

<http://www.cypress.com/cypress-mcu-product-softwareexamples>

## Document History

Document Title: AN205318 - FR, MB91460, Clock Monitor

Document Number:002-05318

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	-	NOFL	06/02/2008	V1.0, First draft, HPi
			06/03/2008	V1.1, Updated introduction and Key feature section, HPi
*A	5090796	NOFL	04/12/2016	Converted Spansion Application Note "MCU-AN-300067-E-V11" to Cypress format
*B	5842136	AESATP12	08/02/2017	Updated logo and copyright.

## Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

## Products

ARM® Cortex® Microcontrollers	<a href="http://cypress.com/arm">cypress.com/arm</a>
Automotive	<a href="http://cypress.com/automotive">cypress.com/automotive</a>
Clocks & Buffers	<a href="http://cypress.com/clocks">cypress.com/clocks</a>
Interface	<a href="http://cypress.com/interface">cypress.com/interface</a>
Internet of Things	<a href="http://cypress.com/iot">cypress.com/iot</a>
Memory	<a href="http://cypress.com/memory">cypress.com/memory</a>
Microcontrollers	<a href="http://cypress.com/mcu">cypress.com/mcu</a>
PSoC	<a href="http://cypress.com/psoc">cypress.com/psoc</a>
Power Management ICs	<a href="http://cypress.com/pmic">cypress.com/pmic</a>
Touch Sensing	<a href="http://cypress.com/touch">cypress.com/touch</a>
USB Controllers	<a href="http://cypress.com/usb">cypress.com/usb</a>
Wireless Connectivity	<a href="http://cypress.com/wireless">cypress.com/wireless</a>

## PSoC® Solutions

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#) | [PSoC 6](#)

## Cypress Developer Community

[Forums](#) | [WICED IOT Forums](#) | [Projects](#) | [Videos](#) | [Blogs](#) | [Training](#) | [Components](#)

## Technical Support

[cypress.com/support](http://cypress.com/support)

All other trademarks or registered trademarks referenced herein are the property of their respective owners.



Cypress Semiconductor  
198 Champion Court  
San Jose, CA 95134-1709

© Cypress Semiconductor Corporation, 2008-2017. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit [cypress.com](http://cypress.com). Other names and brands may be claimed as property of their respective owners.