
SCU System Control Units

AURIX™ TC3xx Microcontroller Training V1.0 2020-09



SCU System Control Units





Highlights

The SCU comprises various units, which handle reset operations (incl. effects and triggers), power management control (e.g. reducing power consumption) and many other miscellaneous submodules such as watchdogs.

Key Features

Watchdog timers

Reset operations and sources

Power management control

Emergency stop

Customer Benefits

- Robust failure detection and recovery
- Scalable reset concept based on different triggers
- Minimize power use during operation
- Fast reaction to emergency events without the SW intervention

WDT - Watchdog Timers



- The WatchDog Timers (WDTs) provide a highly reliable and secure way of detecting and recovering from software or hardware failure
- They can be used to abort any accidental malfunction of a CPU or internal module within a user-specified time period
- Additionally, each of the WDTs incorporates an End-of-Initialization (ENDINIT) feature which protects the critical registers from unintended writes
- To protect these functions a sophisticated scheme is implemented that requires a password and guard bits during the accesses to the WDT control registers. Any write access that does not provide the correct values for the password and guard bits is regarded as malfunction and results in an alarm
- On top of the general WDTs, a Safety Watchdog Timer is provided. It is independent from the CPU watchdogs and it also provides temporal protection against unintended writes to critical system registers which could impact the safety-critical systems
- These feature ensures that the system runs in a robust and safe manner (e.g. Trigger an alarm, a reset or stopping the CPU in case of malfunction)

RCU – Reset types and effects




- AURIX™ TC3xx has a scalable reset concept, where different types of reset are encapsulated one into the other. The **Cold Power-On Reset** is the highest reset type, where the Embedded Voltage Regulator (EVR), internal clocks and RAMs are reset, additionally to the modules affected by the **Application Reset**, **System Reset** and **Warm Power-On Reset**
- SW Module Reset and Debug Reset enable the user to directly trigger a reset of the connected modules

Reset Type	Additional Modules affected by Cold Power-On Reset	Additional Modules affected by Warm Power-On Reset	Additional Modules affected by System Reset	Modules affected by Application Reset
Cold Power-On Reset	 > Embedded Voltage Regulator > Internal clocks > RAMs: - DSPRs/PSPRs - LMU/BMU 	 JTAG interface OCDS MCDS SMU – Fault Signaling Protocol Pin 	 Flash memory Clock source PLL External Service Requests pins 	 All CPUs All Peripherals SCU Port pins in reset RAMs: Dcache invalid
Warm Power-On Reset	A higher			- Pcache invalid
System Reset	A higher reset encapsulates a lower reset			
Application Reset				
SW Module Reset	Available for all CPUs, DMA channel, QSPI, CAN, ASCLIN, Ethernet, GTM, SENT, ADC, HSSL, CCU6			
Debug Reset	OCDS and MCDS reset, all CPUs and peripherals (except SCU) are put into reset			

RCU – Reset types and sources




Reset Type	Source of reset	
Cold Power-on Reset	 Startup Temporary power fail on any of the 3 supplies (VEXT< 3.0 V; VDDP3 <3.0V; VDD < 1.125 V) 	
Warm Power-on Reset	PORST pad asserted	
System Reset	 > ESR0/ESR1 > SMU > STMx > Watchdog (SMU) > Software reset 	
Application Reset	 > ESR0/ESR1 > SMU > STMx > Software reset > Tuning protection 	
SW Module Reset	> Configurable by registers	
Debug Reset	OCDS request triggerJTAG reset	



PMC – Single source power supply concept



- AURIX™ devices support different supply modes:
 - Single 5 V source supply
 - Single 3.3 V source supply
 - Dual supply modes
- AURIX™ contains 2 separate parallel Embedded Voltage Regulators (EVR33 and EVRC) generating 3.3 V and 1.3 V supply voltages from the external supply
- All supply and generated voltages are monitored internally against overshoot and brownout conditions based on programmable thresholds
- The reaction to these situations is triggering either a cold Power-On Reset or an alarm
- This approach reduces the complexity of the system, since additional regulators are not needed to obtain the 3.3 V or 1.3 V voltages



PMC – Idle, Sleep & Standby modes




- The power management scheme allows activation of power down modes so that the system operates with the minimum required power for the corresponding application state
- A progressive reduction in power consumption is achieved by invoking Idle, Sleep or Standby modes
- The Idle mode is specific to each individual CPU, while the Sleep and Standby modes influence the complete system

Mode/Current	Description	Entry/Exit
CPUx Run	Normal operation	-
CPUx Idle	The CPU clock is disabled. All peripherals remain active.	Entry: via Software, SMU Exit: on CPUx Interrupt, Trap, Reset
System Sleep	Peripheral clocks are gated if configured by control registers. All CPUs are set to IDLE	Entry: via Software Exit: on CPUx Interrupt, Trap, Reset
System Standby	Main domain is powered off. Standby RAM may be active	Entry: via Software, NMI Exit: on edge detection on NMI/pins, PORST assertion In case of separate standby supply pin: entry & exit are done on the VEXT supply ramp-down, respectively ramp-up

Emergency Stop



- The emergency stop feature provides a fast reaction to an emergency event without the intervention of the software. As reaction to the emergency event, selected output ports can be immediately placed into a defined state (e.g. bring the actuators in a known state)
- An emergency stop can be triggered by the following:
 - A transition on the port which is configured as the Emergency Stop input
 - An alarm event or command from the Safety Management Unit that is configured to generate a port emergency stop
- The emergency stop control logic for the ports operates in two modes:
 - Synchronous mode (default): the emergency case is activated by hardware and released by software
 - Asynchronous mode: both the activation and releasing of the emergency case are done by hardware



Trademarks

All referenced product or service names and trademarks are the property of their respective owners.



Edition 2020-09 Published by Infineon Technologies AG 81726 Munich, Germany

© 2020 Infineon Technologies AG. All Rights Reserved.

Do you have a question about this document?
Email: erratum@infineon.com

Document reference AURIX_Training_2_System_Control_Units

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.