

AN214

Migrating from FM24C16A to FM24C16B

Author: Girija Chougala

Associated Project: No

Associated Part Family: FM24C16A, FM24C16B

Software Version: None

Related Documents: For a complete list, [click here](#)

AN214 discusses the key differences that need to be considered when migrating from FM24C16A to FM24C16B. FM24C16A is now obsolete and this application note explains how FM24C16B is a replacement for FM24C16A.

Introduction

The FM24C16B, a 16-Kbit I²C F-RAM™, is a replacement device for FM24C16A, which is now obsolete. The two devices are identical in terms of pinout, package composition and dimensions, read/write functionality, Write Protect operation, and address pin functionality. This application note discusses the key differences between the two devices that need to be considered when migrating from FM24C16A to FM24C16B.

Drop-In Replacement or Not?

For all designs, FM24C16B is a drop-in replacement for FM24C16A. From a software point of view, the two devices are identical. From a hardware point of view the key difference is the lower active current in FM24C16B. Additionally, FM24C16B datasheet adds a power-up and power-down ramp rate specification of 30 μs/V and a power-up to first-access specification of 1 ms.

Table 1 shows the compatibility chart of FM24C16A and FM24C16B. For a detailed comparison, see Table 3.

Table 1. Compatibility Chart

FM24C16A Feature or Spec	Is FM24C16B compatible?
Package	Yes
Pinout	Yes
Temperature Range	Yes
Operating Voltage	Yes
Operating Current	Yes
Standby Current	Yes
Read / Write Function	Yes
Timing / Frequency	Yes
Data Retention	Refer to Table 3
Endurance	Yes

Ordering Part Numbers

Table 2 gives the recommended FM24C16B ordering part numbers that correspond to the now obsolete FM24C16A ordering part numbers.

Table 2. Recommended Ordering Part Numbers for Migration

FM24C16A		FM24C16B		Comments
Ordering Part Number	Status	Ordering Part Number	Status	
FM24C16A-G	Obsolete	FM24C16B-G	In production	No hardware or software change is required.
FM24C16A-GTR		FM24C16B-GTR		

Comparison of FM24C16A and FM24C16B

Table 3 gives a detailed comparison of the two devices.

Table 3. Detailed Comparison

	FM24C16A	FM24C16B	Comments
Package Types	-G	-G	Identical, "green" SOIC package
Package Outlines	SOIC-8	SOIC-8	Identical outline and board footprint
Pinout	-	-	Identical
Temperature Range	-40 °C to +85 °C	-40 °C to +85 °C	Identical
Operating Voltage Range	4.5 V to 5.5 V	4.5 V to 5.5 V	Identical
Active Supply Current	150 µA @ 100 kHz 1000 µA @ 1 MHz	100 µA @ 100 kHz 400 µA @ 1 MHz	FM24C16B offers lower active current at all clock rates
Standby Current	10 µA	10 µA	Identical
Read / Write Function	-	-	Identical 1-byte addressing, Identical Slave IDs
Clock Frequency	1 MHz	1 MHz	Identical
Data Retention	45 years (+85 °C)	10 years (+85 °C) 38 years (+75 °C) 151 years (+65 °C)	Data retention is lower.
Endurance (Write/Read Cycles)	1E+12	1E+14	FM24C16B has better endurance
V_{DD} Power-Up Ramp Rate (t_{VR})	-	30 µs / V	Power-up ramp rate should be slower than 30 µs / V for FM24C16B
V_{DD} Power-Down Ramp Rate (t_{VF})	-	30 µs / V	Power-down ramp rate should be slower than 30 µs / V for FM24C16B
Power-Up to First Access (t_{PU})	-	1 ms	After power-up, the first access of FM24C16B should be after 1 ms

Critical Considerations

You should consider all the parameter differences mentioned in Table 3 during the migration to FM24C16B. This section discusses the critical differences. System designers should also review the [datasheet](#) when migrating to the new part.

V_{DD} Ramp Rate

V_{DD} power-up and power-down ramp rate specifications are added in FM24C16B device. Ensure that the power-up and power-down ramp rates are slower than 30 µs / V in your system.

Power-Up to First Access

Power-up to first access specification is added in FM24C16B device. Ensure that the FM24C16B device is accessed only after 1 ms from power-up.

Summary

AN214 discussed the differences between FM24C16A and FM24C16B that need to be considered during migration.

Related Documents

Datasheet

[FM24C16B: 16-Kbit \(2 K × 8\) Serial \(I²C\) F-RAM datasheet](#)

Document History

Document Title: Migrating from FM24C16A to FM24C16B - AN214

Document Number: 001-86821

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	3944550	GVCH	03/26/2013	New Spec.
*A	4278231	MEDU	03/05/2014	Updated to Cypress Template. Added data retention spec to FM24C16B at 85 °C. Updated "Power-up to First Access" for FM24C16B from 10 ms to 1 ms. Updated "V _{DD} Power-down Ramp Rate" for FM24C16B from 100 µs / V to 30 µs / V. Removed V _{IH(max)} spec from Table 2.
*B	4498650	GVCH	09/10/2014	Changed title from "Differences between FM24C16A and FM24C16B" to "Migrating from FM24C16A to FM24C16B." Updated abstract. Added " Ordering Part Numbers " section. Added title for Table 3 . Added " Related Documents " section.

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

Products

Automotive	cypress.com/go/automotive
Clocks & Buffers	cypress.com/go/clocks
Interface	cypress.com/go/interface
Lighting & Power Control	cypress.com/go/powerpsoc cypress.com/go/plc
Memory	cypress.com/go/memory
PSoC	cypress.com/go/psoc
Touch Sensing	cypress.com/go/touch
USB Controllers	cypress.com/go/usb
Wireless/RF	cypress.com/go/wireless

PSoC® Solutions

psoc.cypress.com/solutions

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#)

Cypress Developer Community

[Community](#) | [Forums](#) | [Blogs](#) | [Video](#) | [Training](#)

Technical Support

cypress.com/go/support

PSoC is a registered trademark of Cypress Semiconductor Corp. All other trademarks or registered trademarks referenced herein are the property of their respective owners.



Cypress Semiconductor Phone : 408-943-2600
198 Champion Court Fax : 408-943-4730
San Jose, CA 95134-1709 Website : www.cypress.com

© Cypress Semiconductor Corporation, 2013-2014. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

This Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.