


40V HiRel Silicon Schottky Diode

BAS40-05(ES)

Features

- General-purpose diodes for high-speed switching
- Circuit protection
- Voltage clamping
- High-level detecting and mixing
- Hermetically sealed microwave package




Product validation

-  **ESA Space Qualified**
ESCC Detail Spec. No.: 5512/020
Type Variant No. 05

Description

ESD: Electrostatic discharge sensitive device,
observe handling precautions!

Table 1 **Product information**

Type	Comment	Pin Configuration
BAS40-05(ES)	For flight use	
BAS40-05(P) ¹	Not for flight use ¹	

¹ (P) parts have the same fit, form and function as (ES) parts,
no screening acc. to Chart F3 in ESCC Generic Specification No. 5010

Table of contents

Features	1
Product validation	1
Description	1
Table of contents	2
1 Maximum ratings	3
2 Thermal characteristics	4
3 Electrical characteristics	5
4 Package outlines	6

Maximum ratings

1 Maximum ratings

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Reverse Voltage	V_R	-	-	40	V	
Forward Current	I_F	-	-	120	mA	
Surge Forward Current	I_{FSM}	-	-	175	mA	$t \leq 10\text{ms}$, Duty Cycle=10%
Power Dissipation ¹	P_{tot}	-	-	250	mW	$T_C \leq 125^\circ\text{C}$
Operating and storage temperature	T_{op}	-55	-	150	$^\circ\text{C}$	
Junction temperature	T_j	-	-	150	$^\circ\text{C}$	

¹ For $T_C > 125^\circ\text{C}$ derating is required.

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction -case	$R_{th,JC}$	-	-	100	K/W	
Soldering temperature	T_{sol}	-	-	250	°C	Duration 5 seconds maximum and the same terminal shall not be resoldered until 3 minutes have elapsed.

3 Electrical characteristics

at $T_A=25^\circ\text{C}$, unless otherwise specified

Table 4 Static characteristics


Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Reverse Current 1	I_{R1}	-	-	2	μA	$V_R = 40\text{V}$
Reverse Current 2	I_{R2}	-	-	0.1	μA	$V_R = 32\text{V}$
Forward Voltage 1	V_{F1}	0.29	0.33	0.39	V	$I_{F1} = 1.0\text{mA}$
Forward Voltage 2	V_{F2}	0.41	0.45	0.54	V	$I_{F2} = 10\text{mA}$
Forward Voltage 3	V_{F3}	0.55	0.68	0.75	V	$I_{F3} = 40\text{mA}$
Differential Forward Resistance ¹	R_{FD}	8	9	12	Ω	$I_{F2} = 10\text{mA}, I_{F3} = 15\text{mA}$

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Total Capacitance	C_T	2.4	3.1	4.0	pF	$V_R = 0\text{V}, f = 1.0\text{MHz}, V_{in} = 15\text{mV}$

¹ $R_{FD} = \frac{\Delta V_F}{5 \cdot 10^{-3} \text{A}}$

4 Package outlines



Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 3, January 2022

Published by

Infineon Technologies AG

81726 München, Germany

© 2022 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Infineon Technologies Components may only be used in life-support devices or systems with the expressed written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.